

TC7MPN3125FTG

Low Voltage/Low Power 2-Bit × 2 Dual Supply Bus Transceiver

The TC7MPN3125FTG is a dual supply, advanced high-speed CMOS 4-bit dual supply voltage interface bus transceiver fabricated with silicon gate CMOS technology.


It is also designed with over voltage tolerant inputs and outputs up to 3.6 V.

Designed for use as an interface between a 1.2-V, 1.5-V, 1.8-V, or 2.5-V bus and a 1.8-V, 2.5-V or 3.6-V bus in mixed 1.2-V, 1.5-V, 1.8-V or 2.5-V/1.8-V, 2.5-V or 3.6-V supply systems.

The A-port interfaces with the 1.2-V, 1.5-V, 1.8-V or 2.5-V bus, the B-port with the 1.8-V, 2.5-V, 3.3-V bus.

The direction of data transmission is determined by the level of the DIR input. The enable input ($\overline{OE}$) can be used to disable the device so that the buses are effectively isolated.

All inputs are equipped with protection circuits against static discharge or transient excess voltage.



Weight: 0.013 g (typ.)


Features

- Bidirectional interface between 1.2-V and 1.8-V, 1.2-V and 2.5-V, 1.2-V and 3.3-V, 1.5-V and 2.5-V, 1.5-V and 3.3-V, 1.8-V and 2.5-V, 1.8-V and 3.3-V or 2.5-V and 3.3-V buses.
- High-speed operation: $t_{pd} = 13.7$ ns (max) ($V_{CCA} = 2.5 \pm 0.2$ V, $V_{CCB} = 3.3 \pm 0.3$ V)
 $t_{pd} = 14.8$ ns (max) ($V_{CCA} = 1.8 \pm 0.15$ V, $V_{CCB} = 3.3 \pm 0.3$ V)
 $t_{pd} = 16.0$ ns (max) ($V_{CCA} = 1.5 \pm 0.1$ V, $V_{CCB} = 3.3 \pm 0.3$ V)
 $t_{pd} = 61$ ns (max) ($V_{CCA} = 1.2 \pm 0.1$ V, $V_{CCB} = 3.3 \pm 0.3$ V)
 $t_{pd} = 18.5$ ns (max) ($V_{CCA} = 1.8 \pm 0.15$ V, $V_{CCB} = 2.5 \pm 0.2$ V)
 $t_{pd} = 19.7$ ns (max) ($V_{CCA} = 1.5 \pm 0.15$ V, $V_{CCB} = 2.5 \pm 0.2$ V)
 $t_{pd} = 60$ ns (max) ($V_{CCA} = 1.2 \pm 0.15$ V, $V_{CCB} = 2.5 \pm 0.2$ V)
 $t_{pd} = 58$ ns (max) ($V_{CCA} = 1.2 \pm 0.1$ V, $V_{CCB} = 1.8 \pm 0.15$ V)
- Output current: $IO_{HB}/IO_{LB} = \pm 3$ mA (min) ($V_{CCB} = 3.0$ V)
 $IO_{HB}/IO_{LB} = \pm 2$ mA (min) ($V_{CCB} = 2.3$ V)
 $IO_{HB}/IO_{LB} = \pm 0.5$ mA (min) ($V_{CCB} = 1.65$ V)
 $IO_{HA}/IO_{LA} = \pm 9$ mA (min) ($V_{CCA} = 2.3$ V)
 $IO_{HA}/IO_{LA} = \pm 3$ mA (min) ($V_{CCA} = 1.65$ V)
 $IO_{HA}/IO_{LA} = \pm 1$ mA (min) ($V_{CCA} = 1.4$ V)
- Latch-up performance: ± 300 mA
- ESD performance: Machine model $> \pm 200$ V
Human body model $> \pm 2000$ V
- Ultra-small package: VQON16
- Low current consumption: Using the new circuit significantly reduces current consumption when $\overline{OE} = "H"$.
Suitable for battery-driven applications such as PDAs and cellular phones.
- Floating A-bus and B-bus are permitted. (when $\overline{OE} = "H"$)
3.6-V tolerant function and power-down protection provided on all inputs and outputs.


Note 1: Do not apply a signal to any bus pins when it is in the output mode. Damage may result.

Note: When mounting VQON package, the type of recommended flux is RA or RMA.

Pin Assignment (top view)



IEC Logic Symbol



Truth Table

Inputs		Function		Outputs
1OE	1DIR	Bus 1A1-1A2	Bus 1B1-1B2	
L	L	Output	Input	A = B
L	H	Input	Output	B = A
H	X	Z		Z


Inputs		Function		Outputs
2OE	2DIR	Bus 2A1-2A2	Bus 2B1-2B2	
L	L	Output	Input	A = B
L	H	Input	Output	B = A
H	X	Z		Z

X: Don't care


Z: High impedance

Marking

FTG (VQON16-P-0303-0.50)



Block Diagram



Maximum Ratings

Characteristics	Symbol	Rating	Unit
Power supply voltage (Note 2)	V_{CCA}	-0.5 to 4.6	V
	V_{CCB}	-0.5 to 4.6	
DC input voltage (DIR, $\overline{OE}$)	V_{IN}	-0.5 to 4.6	V
DC bus I/O voltage	$V_{I/OA}$	-0.5 to 4.6 (Note 3)	V
		-0.5 to $V_{CCA} + 0.5$ (Note 4)	
	$V_{I/OB}$	-0.5 to 4.6 (Note 3)	
		-0.5 to $V_{CCB} + 0.5$ (Note 4)	
Input diode current	I_{IK}	-50	mA
Output diode current	$I_{I/OK}$	± 50 (Note 5)	mA
DC output current	I_{OUTA}	± 25	mA
	I_{OUTB}	± 6	
DC V_{CC} /ground current per supply pin	I_{CCA}	± 50	mA
	I_{CCB}	± 50	
Power dissipation	P_D	180	mW
Storage temperature	T_{stg}	-65 to 150	°C

Note 2: Don't supply a voltage to V_{CCB} pin when V_{CCA} is in the OFF state.

Note 3: Output in OFF state

Note 4: High or Low stats. I_{OUT} absolute maximum rating must be observed.

Note 5: $V_{OUT} < GND$, $V_{OUT} > V_{CC}$

Recommended Operating Conditions

Characteristics	Symbol	Rating	Unit
Power supply voltage (Note 6)	V_{CCA}	1.1 to 2.7	V
	V_{CCB}	1.65 to 3.6	
Input voltage (DIR, $\overline{OE}$)	V_{IN}	0 to 3.6	V
Bus I/O voltage	$V_{I/OA}$	0 to 3.6 (Note 7)	V
		0 to V_{CCA} (Note 8)	
	$V_{I/OB}$	0 to 3.6 (Note 7)	
		0 to V_{CCB} (Note 8)	
Output current	I_{OUTA}	± 9 (Note 9)	mA
		± 3 (Note 10)	
		± 1 (Note 11)	
	I_{OUTB}	± 3 (Note 12)	
		± 2 (Note 13)	
		± 0.5 (Note 14)	
Operating temperature	T_{opr}	-40 to 85	°C
Input rise and fall time	dt/dv	0 to 10 (Note 15)	ns/V

Note 6: Don't use in $V_{CCA} > V_{CCB}$

Note 7: Output in OFF state

Note 8: High or low state

Note 9: $V_{CCB} = 2.3$ to 2.7 V

Note 10: $V_{CCB} = 1.65$ to 1.95 V

Note 11: $V_{CCB} = 1.4$ to 1.6 V

Note 12: $V_{CCA} = 3.0$ to 3.6 V

Note 13: $V_{CCA} = 2.3$ to 2.7 V

Note 14: $V_{CCA} = 1.65$ to 1.95 V

Note 15: $V_{IN} = 0.8$ to 2.0 V, $V_{CCA} = 2.5$ V, $V_{CCB} = 3.0$ V

Electrical Characteristics

DC Characteristics ($2.3\text{ V} \leq V_{CCA} \leq 2.7\text{ V}$, $2.7\text{ V} < V_{CCB} \leq 3.6\text{ V}$)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		2.3 to 2.7	2.7 to 3.6	1.6	—	V
	V _{IHB}	Bn		2.3 to 2.7	2.7 to 3.6	2.0	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		2.3 to 2.7	2.7 to 3.6	—	0.7	V
	V _{ILB}	Bn		2.3 to 2.7	2.7 to 3.6	—	0.8	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	2.3 to 2.7	2.7 to 3.6	V _{CCA} − 0.2	—	V
			I _{OHA} = −9 mA	2.3	2.7 to 3.6	1.7	—	
	V _{OHB}		I _{OHB} = −100 μA	2.3 to 2.7	2.7 to 3.6	V _{CCB} − 0.2	—	
			I _{OHB} = −3 mA	2.3 to 2.7	3.0	2.2	—	
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	2.3 to 2.7	2.7 to 3.6	—	0.2	V
			I _{OLA} = 9 mA	2.3	2.7 to 3.6	—	0.6	
	V _{OLB}		I _{OLB} = 100 μA	2.3 to 2.7	2.7 to 3.6	—	0.2	
			I _{OLB} = 3 mA	2.3 to 2.7	3.0	—	0.55	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		2.3 to 2.7	2.7 to 3.6	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		2.3 to 2.7	2.7 to 3.6	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		2.3 to 2.7	2.7 to 3.6	—	±1.0	μA
Power-off leakage current	I _{OFF1}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF2}			2.3 to 2.7	0	—	2.0	
	I _{OFF3}			2.3 to 2.7	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		2.3 to 2.7	2.7 to 3.6	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		2.3 to 2.7	2.7 to 3.6	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		2.3 to 2.7	2.7 to 3.6	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		2.3 to 2.7	2.7 to 3.6	—	±2.0	
	I _{CCTB}	V _{INB} = V _{CCB} − 0.6 V per input		2.3 to 2.7	2.7 to 3.6	—	750.0	μA

DC Characteristics ($1.65\text{ V} \leq V_{CCA} < 2.3\text{ V}$, $2.7\text{ V} < V_{CCB} \leq 3.6\text{ V}$)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		1.65 to 2.3	2.7 to 3.6	0.65 × V _{CCA}	—	V
	V _{IHB}	Bn		1.65 to 2.3	2.7 to 3.6	2.0	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		1.65 to 2.3	2.7 to 3.6	—	0.35 × V _{CCA}	V
	V _{ILB}	Bn		1.65 to 2.3	2.7 to 3.6	—	0.8	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	1.65 to 2.3	2.7 to 3.6	V _{CCA} − 0.2	—	V
			I _{OHA} = −3 mA	1.65	2.7 to 3.6	1.25	—	
	V _{OHB}		I _{OHB} = −100 μA	1.65 to 2.3	2.7 to 3.6	V _{CCB} − 0.2	—	
			I _{OHB} = −3 mA	1.65 to 2.3	3.0	2.2	—	
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	1.65 to 2.3	2.7 to 3.6	—	0.2	V
			I _{OLA} = 3 mA	1.65	2.7 to 3.6	—	0.3	
	V _{OLB}		I _{OLB} = 100 μA	1.65 to 2.3	2.7 to 3.6	—	0.2	
			I _{OLB} = 3 mA	1.65 to 2.3	3.0	—	0.55	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.65 to 2.3	2.7 to 3.6	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.65 to 2.3	2.7 to 3.6	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		1.65 to 2.3	2.7 to 3.6	—	±1.0	μA
Power-off leakage current	I _{OFF1}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF2}			1.65 to 2.3	0	—	2.0	
	I _{OFF3}			1.65 to 2.3	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.65 to 2.3	2.7 to 3.6	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.65 to 2.3	2.7 to 3.6	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.65 to 2.3	2.7 to 3.6	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.65 to 2.3	2.7 to 3.6	—	±2.0	
	I _{CCTB}	V _{INB} = V _{CCB} − 0.6 V per input		1.65 to 2.3	2.7 to 3.6	—	750.0	μA

DC Characteristics (1.4 V ≤ V_{CCA} < 1.65 V, 2.7 V < V_{CCB} ≤ 3.6 V)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		1.4 to 1.65	2.7 to 3.6	$0.65 \times V_{\text{CCA}}$	—	V
	V _{IHB}	Bn		1.4 to 1.65	2.7 to 3.6	2.0	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		1.4 to 1.65	2.7 to 3.6	—	$0.30 \times V_{\text{CCA}}$	V
	V _{ILB}	Bn		1.4 to 1.65	2.7 to 3.6	—	0.8	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	1.4 to 1.65	2.7 to 3.6	V _{CCA} − 0.2	—	V
	I _{OHA} = −1 mA		1.4	2.7 to 3.6	1.05	—		
	V _{OHB}		I _{OHB} = −100 μA	1.4 to 1.65	2.7 to 3.6	V _{CCB} − 0.2	—	
	I _{OHB} = −3 mA		1.4 to 1.65	3.0	2.2	—		
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	1.4 to 1.65	2.7 to 3.6	—	0.2	V
	I _{OLA} = 1 mA		1.4	2.7 to 3.6	—	0.35		
	V _{OLB}		I _{OLB} = 100 μA	1.4 to 1.65	2.7 to 3.6	—	0.2	
			I _{OLB} = 3 mA	1.4 to 1.65	3.0	—	0.55	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.4 to 1.65	2.7 to 3.6	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.4 to 1.65	2.7 to 3.6	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		1.4 to 1.65	2.7 to 3.6	—	±1.0	μA
Power-off leakage current	I _{OFF1}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF2}			1.4 to 1.65	0	—	2.0	
	I _{OFF3}			1.4 to 1.65	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.4 to 1.65	2.7 to 3.6	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.4 to 1.65	2.7 to 3.6	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.4 to 1.65	2.7 to 3.6	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.4 to 1.65	2.7 to 3.6	—	±2.0	
	I _{CCTB}	V _{INB} = V _{CCB} − 0.6 V per input		1.4 to 1.65	2.7 to 3.6	—	750.0	μA

DC Characteristics (1.1 V ≤ V_{CCA} < 1.4 V, 2.7 V < V_{CCB} ≤ 3.6 V)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		1.1 to 1.4	2.7 to 3.6	0.65 × V _{CCA}	—	V
	V _{IHB}	Bn		1.1 to 1.4	2.7 to 3.6	2.0	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		1.1 to 1.4	2.7 to 3.6	—	0.30 × V _{CCA}	V
	V _{ILB}	Bn		1.1 to 1.4	2.7 to 3.6	—	0.8	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	1.1 to 1.4	2.7 to 3.6	V _{CCA} − 0.2	—	V
	V _{OHB}		I _{OHB} = −100 μA	1.1 to 1.4	2.7 to 3.6	V _{CCB} − 0.2	—	
			I _{OHB} = −3 mA	1.1 to 1.4	3.0	2.2	—	
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	1.1 to 1.4	2.7 to 3.6	—	0.2	V
	V _{OLB}		I _{OLB} = 100 μA	1.1 to 1.4	2.7 to 3.6	—	0.2	
			I _{OLB} = 3 mA	1.1 to 1.4	3.0	—	0.55	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.1 to 1.4	2.7 to 3.6	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.1 to 1.4	2.7 to 3.6	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		1.1 to 1.4	2.7 to 3.6	—	±1.0	μA
Power-off leakage current	I _{OFF}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF}			1.1 to 1.4	0	—	2.0	
	I _{OFF}			1.1 to 1.4	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.1 to 1.4	2.7 to 3.6	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.1 to 1.4	2.7 to 3.6	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.1 to 1.4	2.7 to 3.6	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.1 to 1.4	2.7 to 3.6	—	±2.0	
	I _{CCTB}	V _{INB} = V _{CCA} − 0.6 V per input		1.1 to 1.4	2.7 to 3.6	—	750.0	

DC Characteristics ($1.65\text{ V} \leq V_{CCA} < 2.3\text{ V}$, $2.3\text{ V} \leq V_{CCB} \leq 2.7\text{ V}$)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		1.65 to 2.3	2.3 to 2.7	0.65 × V _{CCA}	—	V
	V _{IHB}	Bn		1.65 to 2.3	2.3 to 2.7	1.6	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		1.65 to 2.3	2.3 to 2.7	—	0.35 × V _{CCA}	V
	V _{ILB}	Bn		1.65 to 2.3	2.3 to 2.7	—	0.7	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	1.65 to 2.3	2.3 to 2.7	V _{CCA} − 0.2	—	V
			I _{OHA} = −3 mA	1.65	2.3 to 2.7	1.25	—	
	V _{OHB}		I _{OHB} = −100 μA	1.65 to 2.3	2.3 to 2.7	V _{CCB} − 0.2	—	
			I _{OHB} = −2 mA	1.65 to 2.3	2.3	1.7	—	
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	1.65 to 2.3	2.3 to 2.7	—	0.2	V
			I _{OLA} = 3 mA	1.65	2.3 to 2.7	—	0.3	
	V _{OLB}		I _{OLB} = 100 μA	1.65 to 2.3	2.3 to 2.7	—	0.2	
			I _{OLB} = 2 mA	1.65 to 2.3	2.3	—	0.6	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.65 to 2.3	2.3 to 2.7	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.65 to 2.3	2.3 to 2.7	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		1.65 to 2.3	2.3 to 2.7	—	±1.0	μA
Power-off leakage current	I _{OFF1}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF2}			1.65 to 2.3	0	—	2.0	
	I _{OFF3}			1.65 to 2.3	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.65 to 2.3	2.3 to 2.7	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.65 to 2.3	2.3 to 2.7	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.65 to 2.3	2.3 to 2.7	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.65 to 2.3	2.3 to 2.7	—	±2.0	

DC Characteristics ($1.4\text{ V} \leq V_{CCA} < 1.65\text{ V}$, $2.3\text{ V} \leq V_{CCB} \leq 2.7\text{ V}$)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		1.4 to 1.65	2.3 to 2.7	0.65 × V _{CCA}	—	V
	V _{IHB}	Bn		1.4 to 1.65	2.3 to 2.7	1.6	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		1.4 to 1.65	2.3 to 2.7	—	0.30 × V _{CCA}	V
	V _{ILB}	Bn		1.4 to 1.65	2.3 to 2.7	—	0.7	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	1.4 to 1.65	2.3 to 2.7	V _{CCA} − 0.2	—	V
			I _{OHA} = −1 mA	1.4	2.3 to 2.7	1.05	—	
	V _{OHB}		I _{OHB} = −100 μA	1.4 to 1.65	2.3 to 2.7	V _{CCB} − 0.2	—	
			I _{OHB} = −2 mA	1.4 to 1.65	2.3	1.7	—	
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	1.4 to 1.65	2.3 to 2.7	—	0.2	V
			I _{OLA} = 1 mA	1.4	2.3 to 2.7	—	0.35	
	V _{OLB}		I _{OLB} = 100 μA	1.4 to 1.65	2.3 to 2.7	—	0.2	
			I _{OLB} = 2 mA	1.4 to 1.65	2.3	—	0.6	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.4 to 1.65	2.3 to 2.7	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.4 to 1.65	2.3 to 2.7	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		1.4 to 1.65	2.3 to 2.7	—	±1.0	μA
Power-off leakage current	I _{OFF1}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF2}			1.4 to 1.65	0	—	2.0	
	I _{OFF3}			1.4 to 1.65	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.4 to 1.65	2.3 to 2.7	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.4 to 1.65	2.3 to 2.7	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.4 to 1.65	2.3 to 2.7	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.4 to 1.65	2.3 to 2.7	—	±2.0	

DC Characteristics (1.1 V ≤ V_{CCA} < 1.4 V, 2.3 V ≤ V_{CCB} ≤ 2.7 V)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		1.1 to 1.4	2.3 to 2.7	0.65 × V _{CCA}	—	V
	V _{IHB}	Bn		1.1 to 1.4	2.3 to 2.7	1.6	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		1.1 to 1.4	2.3 to 2.7	—	0.30 × V _{CCA}	V
	V _{ILB}	Bn		1.1 to 1.4	2.3 to 2.7	—	0.7	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	1.1 to 1.4	2.3 to 2.7	V _{CCA} − 0.2	—	V
	V _{OHB}		I _{OHB} = −100 μA	1.1 to 1.4	2.3 to 2.7	V _{CCB} − 0.2	—	
			I _{OHB} = −2 mA	1.1 to 1.4	2.3	1.7	—	
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	1.1 to 1.4	2.3 to 2.7	—	0.2	V
	V _{OLB}		I _{OLB} = 100 μA	1.1 to 1.4	2.3 to 2.7	—	0.2	
			I _{OLB} = 2 mA	1.1 to 1.4	2.3	—	0.6	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.1 to 1.4	2.3 to 2.7	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.1 to 1.4	2.3 to 2.7	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		1.1 to 1.4	2.3 to 2.7	—	±1.0	μA
Power-off leakage current	I _{OFF}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF}			1.1 to 1.4	0	—	2.0	
	I _{OFF}			1.1 to 1.4	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.1 to 1.4	2.3 to 2.7	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.1 to 1.4	2.3 to 2.7	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.1 to 1.4	2.3 to 2.7	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.1 to 1.4	2.3 to 2.7	—	±2.0	

DC Characteristics (1.1 V ≤ V_{CCA} < 1.4 V, 1.65 V ≤ V_{CCB} < 2.3 V)

Characteristics	Symbol	Test Condition		V _{CCA} (V)	V _{CCB} (V)	Ta = −40 to 85°C		Unit
						Min	Max	
H-level input voltage	V _{IHA}	DIR, $\overline{\text{OE}}$, An		1.1 to 1.4	1.65 to 2.3	$0.65 \times V_{\text{CCA}}$	—	V
	V _{IHB}	Bn		1.1 to 1.4	1.65 to 2.3	$0.65 \times V_{\text{CCB}}$	—	
L-level input voltage	V _{ILA}	DIR, $\overline{\text{OE}}$, An		1.1 to 1.4	1.65 to 2.3	—	$0.30 \times V_{\text{CCA}}$	V
	V _{ILB}	Bn		1.1 to 1.4	1.65 to 2.3	—	$0.35 \times V_{\text{CCB}}$	
H-level output voltage	V _{OHA}	V _{IN} = V _{IH} or V _{IL}	I _{OHA} = −100 μA	1.1 to 1.4	1.65 to 2.3	V _{CCA} − 0.2	—	V
	V _{OHB}		I _{OHB} = −100 μA	1.1 to 1.4	1.65 to 2.3	V _{CCB} − 0.2	—	
			I _{OHB} = −0.5 mA	1.1 to 1.4	1.65	1.25	—	
L-level output voltage	V _{OLA}	V _{IN} = V _{IH} or V _{IL}	I _{OLA} = 100 μA	1.1 to 1.4	1.65 to 2.3	—	0.2	V
	V _{OLB}		I _{OLB} = 100 μA	1.1 to 1.4	1.65 to 2.3	—	0.2	
			I _{OLB} = 0.5 mA	1.1 to 1.4	1.65	—	0.3	
3-state output OFF state current	I _{OZA}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.1 to 1.4	1.65 to 2.3	—	±2.0	μA
	I _{OZB}	V _{IN} = V _{IH} or V _{IL} V _{OUT} = 0 to 3.6 V		1.1 to 1.4	1.65 to 2.3	—	±2.0	
Input leakage current	I _{IN}	V _{IN} (DIR, $\overline{\text{OE}}$) = 0 to 3.6 V		1.1 to 1.4	1.65 to 2.3	—	±1.0	μA
Power-off leakage current	I _{OFF1}	V _{IN} , V _{OUT} = 0 to 3.6 V		0	0	—	2.0	μA
	I _{OFF2}			1.1 to 1.4	0	—	2.0	
	I _{OFF3}			1.1 to 1.4	Open	—	2.0	
Quiescent supply current	I _{CCA}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.1 to 1.4	1.65 to 2.3	—	2.0	μA
	I _{CCB}	V _{INA} = V _{CCA} or GND V _{INB} = V _{CCB} or GND		1.1 to 1.4	1.65 to 2.3	—	2.0	
	I _{CCA}	V _{CCA} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.1 to 1.4	1.65 to 2.3	—	±2.0	μA
	I _{CCB}	V _{CCB} ≤ (V _{IN} , V _{OUT}) ≤ 3.6 V		1.1 to 1.4	1.65 to 2.3	—	±2.0	

AC Characteristics (Ta = -40 to 85°C, Input: t_r = t_f = 2.0 ns)**V_{CCA} = 2.5 ± 0.2 V, V_{CCB} = 3.3 ± 0.3 V**

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time (Bn → An)	t _{pLH} t _{pHL}	Figure 1, Figure 2	1.0	5.4	ns
3-state output enable time ($\overline{\text{OE}}$ → An)	t _{pZL} t _{pZH}	Figure 1, Figure 3	1.0	8.4	
3-state output disable time ($\overline{\text{OE}}$ → An)	t _{pLZ} t _{pHZ}	Figure 1, Figure 3	1.0	6.7	
Propagation delay time (An → Bn)	t _{pLH} t _{pHL}	Figure 1, Figure 2	1.0	13.7	ns
3-state output enable time ($\overline{\text{OE}}$ → Bn)	t _{pZL} t _{pZH}	Figure 1, Figure 3	1.0	16.6	
3-state output disable time ($\overline{\text{OE}}$ → Bn)	t _{pLZ} t _{pHZ}	Figure 1, Figure 3	1.0	7.2	
Output to output skew	t _{osLH} t _{osHL}	(Note 16)	—	0.5	ns

Note 16: Parameter guaranteed by design.

(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)**V_{CCA} = 1.8 ± 0.15 V, V_{CCB} = 3.3 ± 0.3 V**

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time (Bn → An)	t _{pLH} t _{pHL}	Figure 1, Figure 2	1.0	8.9	ns
3-state output enable time ($\overline{\text{OE}}$ → An)	t _{pZL} t _{pZH}	Figure 1, Figure 3	1.0	13.4	
3-state output disable time ($\overline{\text{OE}}$ → An)	t _{pLZ} t _{pHZ}	Figure 1, Figure 3	1.0	10.9	
Propagation delay time (An → Bn)	t _{pLH} t _{pHL}	Figure 1, Figure 2	1.0	14.8	ns
3-state output enable time ($\overline{\text{OE}}$ → Bn)	t _{pZL} t _{pZH}	Figure 1, Figure 3	1.0	18.9	
3-state output disable time ($\overline{\text{OE}}$ → Bn)	t _{pLZ} t _{pHZ}	Figure 1, Figure 3	1.0	8.7	
Output to output skew	t _{osLH} t _{osHL}	(Note 16)	—	0.5	ns

Note 16: Parameter guaranteed by design.

(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)

$V_{CCA} = 1.5 \pm 0.1 \text{ V}$, $V_{CCB} = 3.3 \pm 0.3 \text{ V}$

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time ($B_n \rightarrow A_n$)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	10.3	ns
3-state output enable time ($\overline{OE} \rightarrow A_n$)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	18.5	
3-state output disable time ($\overline{OE} \rightarrow A_n$)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	13.0	
Propagation delay time ($A_n \rightarrow B_n$)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	16.0	ns
3-state output enable time ($\overline{OE} \rightarrow B_n$)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	22.8	
3-state output disable time ($\overline{OE} \rightarrow B_n$)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	10.2	
Output to output skew	t_{osLH} t_{osHL}	(Note 16)	—	1.5	ns

Note 16: Parameter guaranteed by design.

($t_{osLH} = |t_{pLHm} - t_{pLHn}|$, $t_{osHL} = |t_{pHLm} - t_{pHLn}|$)

$V_{CCA} = 1.2 \pm 0.1 \text{ V}$, $V_{CCB} = 3.3 \pm 0.3 \text{ V}$

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time ($B_n \rightarrow A_n$)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	61	ns
3-state output enable time ($\overline{OE} \rightarrow A_n$)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	95	
3-state output disable time ($\overline{OE} \rightarrow A_n$)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	44	
Propagation delay time ($A_n \rightarrow B_n$)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	29	ns
3-state output enable time ($\overline{OE} \rightarrow B_n$)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	63	
3-state output disable time ($\overline{OE} \rightarrow B_n$)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	23	
Output to output skew	t_{osLH} t_{osHL}	(Note 16)	—	1.5	ns

Note 16: Parameter guaranteed by design.

($t_{osLH} = |t_{pLHm} - t_{pLHn}|$, $t_{osHL} = |t_{pHLm} - t_{pHLn}|$)

$$V_{CCA} = 1.8 \pm 0.15 \text{ V}, V_{CCB} = 2.5 \pm 0.2 \text{ V}$$

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time (Bn → An)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	9.1	ns
3-state output enable time ($\overline{OE}$ → An)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	13.5	
3-state output disable time ($\overline{OE}$ → An)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	11.8	
Propagation delay time (An → Bn)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	18.5	ns
3-state output enable time ($\overline{OE}$ → Bn)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	23.6	
3-state output disable time ($\overline{OE}$ → Bn)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	6.9	
Output to output skew	t_{osLH} t_{osHL}	(Note 16)	—	0.5	ns

Note 16: Parameter guaranteed by design.

$$(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)$$

$$V_{CCA} = 1.5 \pm 0.1 \text{ V}, V_{CCB} = 2.5 \pm 0.2 \text{ V}$$

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time (Bn → An)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	10.8	ns
3-state output enable time ($\overline{OE}$ → An)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	18.3	
3-state output disable time ($\overline{OE}$ → An)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	14.2	
Propagation delay time (An → Bn)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	19.7	ns
3-state output enable time ($\overline{OE}$ → Bn)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	26.6	
3-state output disable time ($\overline{OE}$ → Bn)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	8.3	
Output to output skew	t_{osLH} t_{osHL}	(Note 16)	—	1.5	ns

Note 16: Parameter guaranteed by design.

$$(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)$$

$$V_{CCA} = 1.2 \pm 0.1 \text{ V}, V_{CCB} = 2.5 \pm 0.2 \text{ V}$$

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time (Bn → An)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	60	ns
3-state output enable time ($\overline{OE}$ → An)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	95	
3-state output disable time ($\overline{OE}$ → An)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	45	
Propagation delay time (An → Bn)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	33	ns
3-state output enable time ($\overline{OE}$ → Bn)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	66	
3-state output disable time ($\overline{OE}$ → Bn)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	20	
Output to output skew	t_{osLH} t_{osHL}	(Note 16)	—	1.5	ns

Note 16: Parameter guaranteed by design.

$$(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)$$

$$V_{CCA} = 1.2 \pm 0.1 \text{ V}, V_{CCB} = 1.8 \pm 0.15 \text{ V}$$

Characteristics	Symbol	Test Condition	Min	Max	Unit
Propagation delay time (Bn → An)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	58	ns
3-state output enable time ($\overline{OE}$ → An)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	92	
3-state output disable time ($\overline{OE}$ → An)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	47	
Propagation delay time (An → Bn)	t_{pLH} t_{pHL}	Figure 1, Figure 2	1.0	43	ns
3-state output enable time ($\overline{OE}$ → Bn)	t_{pZL} t_{pZH}	Figure 1, Figure 3	1.0	78	
3-state output disable time ($\overline{OE}$ → Bn)	t_{pLZ} t_{pHZ}	Figure 1, Figure 3	1.0	20	
Output to output skew	t_{osLH} t_{osHL}	(Note 16)	—	1.5	ns

Note 16: Parameter guaranteed by design.

$$(t_{osLH} = |t_{pLHm} - t_{pLHn}|, t_{osHL} = |t_{pHLm} - t_{pHLn}|)$$

Dynamic Switching Characteristics (Ta = 25°C, Input: $t_r = t_f = 2.0$ ns, $C_L = 30$ pF)

Characteristics		Symbol	Test Condition	V _{CCA} (V)	V _{CCB} (V)	Typ.	Unit
Quiet output maximum dynamic V _{OL}	A → B	V _{OLP}	V _{IH} = V _{CC} , V _{IL} = 0 V (Note 17)	2.5	3.3	0.35	V
	B → A			1.8	3.3	0.35	
				1.8	2.5	0.25	
				2.5	3.3	0.6	
				1.8	3.3	0.25	
				1.8	2.5	0.25	
Quiet output minimum dynamic V _{OL}	A → B	V _{OLV}	V _{IH} = V _{CC} , V _{IL} = 0 V (Note 17)	2.5	3.3	−0.35	V
	B → A			1.8	3.3	−0.35	
				1.8	2.5	−0.25	
				2.5	3.3	−0.6	
				1.8	3.3	−0.25	
				1.8	2.5	−0.25	
Quiet output maximum dynamic V _{OH}	A → B	V _{OHP}	V _{IH} = V _{CC} , V _{IL} = 0 V (Note 17)	2.5	3.3	3.95	V
	B → A			1.8	3.3	3.95	
				1.8	2.5	2.95	
				2.5	3.3	3.3	
				1.8	3.3	2.3	
				1.8	2.5	2.3	
Quiet output minimum dynamic V _{OH}	A → B	V _{OHV}	V _{IH} = V _{CC} , V _{IL} = 0 V (Note 17)	2.5	3.3	2.65	V
	B → A			1.8	3.3	2.65	
				1.8	2.5	2.05	
				2.5	3.3	1.7	
				1.8	3.3	1.3	
				1.8	2.5	1.3	

Note 17: Parameter guaranteed by design.

Capacitive Characteristics (Ta = 25°C)


Characteristics	Symbol	Test Circuit		V _{CCA} (V)	V _{CCB} (V)	Typ.	Unit
Input capacitance	C _{IN}	DIR, $\overline{OE}$		2.5	3.3	7	pF
Bus I/O capacitance	C _{I/O}	An, Bn		2.5	3.3	8	pF
Power dissipation capacitance (Note 18)	C _{PDA}	$\overline{OE} = "L"$	A → B (DIR = "H")	2.5	3.3	3	pF
			B → A (DIR = "L")	2.5	3.3	16	
		$\overline{OE} = "H"$	A → B (DIR = "H")	2.5	3.3	0	
			B → A (DIR = "L")	2.5	3.3	0	
	C _{PDB}	$\overline{OE} = "L"$	A → B (DIR = "H")	2.5	3.3	16	
			B → A (DIR = "L")	2.5	3.3	5	
		$\overline{OE} = "H"$	A → B (DIR = "H")	2.5	3.3	0	
			B → A (DIR = "L")	2.5	3.3	0	

Note 18: C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.

Average operating current can be obtained by the equation:

$$I_{CC}(\text{opr}) = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC}/4 \text{ (per bit)}$$

AC Test Circuit



Symbol	V _{CC} (output)			
	3.3 ± 0.3 V 2.5 ± 0.2 V	1.8 ± 0.15 V	1.5 ± 0.1 V	1.2 ± 0.1 V
R _{L1/2A}	500 Ω	1 kΩ	2 kΩ	10 kΩ
C _{LA}	30 pF	30 pF	15 pF	15 pF
R _{L1B}	—	—	—	—
R _{L2B}	1 kΩ	1 kΩ	1 kΩ	1 kΩ
C _{LB}	30 pF	30 pF	30 pF	30 pF

Figure 1

AC Waveform




Figure 2 t_{pLH} , t_{pHL}





Figure 3 t_{pLZ} , t_{pHZ} , t_{pZL} , t_{pZH}

Symbol	V_{CC}		
	$3.3 \pm 0.3 \text{ V}$	$2.5 \pm 0.2 \text{ V}$ $1.8 \pm 0.15 \text{ V}$	$1.5 \pm 0.1 \text{ V}$ $1.2 \pm 0.1 \text{ V}$
V_{IH}	2.7 V	V_{CC}	V_{CC}
V_M	1.5 V	$V_{CC}/2$	$V_{CC}/2$
V_X	$V_{OL} + 0.3 \text{ V}$	$V_{OL} + 0.15 \text{ V}$	$V_{OL} + 0.1 \text{ V}$
V_Y	$V_{OH} - 0.3 \text{ V}$	$V_{OH} - 0.15 \text{ V}$	$V_{OH} - 0.1 \text{ V}$

Package Dimensions

VQON16-P-0303-0.50

Unit: mm



Weight: 0.013 g (typ.)

RESTRICTIONS ON PRODUCT USE

030619EBA

- The information contained herein is subject to change without notice.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document are subject to the foreign exchange and foreign trade laws.
- TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations.