

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
AJ	16	A1		REVISED PER ECO-11-005030	11MAR11	RK

- 1

ZINC PER QQ-Z-363.
- 2

POLYMETHYLPENTENE, GENERAL PURPOSE.
- 3

BERYLLIUM COPPER PER QQ-C-530.
- 4

BRASS PER ASTM-B-453.
- 5




BRASS PER ASTM-B-16.
- 6

NICKEL PLATE PER QQ-N-290,
3.81 μm [.000150] MINIMUM THICK.
- 7


TIN PLATE PER ASTM-B-545,
3.81 μm [.000150] MINIMUM THICK.
- 8

GOLD PLATE PER MIL-G-45204,
0.76 μm [.000030] MINIMUM THICK.
9.

SEE INSTRUCTION SHEET 408-2769.



RECOMMENDED PANEL CUTOUT



PCB CONFIGURATION

4.11 [.162]	3.48 [.137]	5222092-3
4.11 [.162]	2.16 [.085]	5222092-1
B	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. ALCORTA - 21APR2005	TE Connectivity	
		CHK J. HAVENER - 21APR2005		
DIMENSIONS: mm [INCHES]		APVD J. LIPPERT - 21APR2005	NAME	
		PRODUCT SPEC	JACK, RIGHT ANGLE, PCB 75 OHM, SERIES BNC	
		APPLICATION SPEC	—	
		WEIGHT	—	
MATERIAL SEE NOTES 1-5		FINISH SEE NOTES 6-8	RESTRICTED TO	
		CUSTOMER DRAWING	—	