



PART NUMBER	REV	FIRST USED
1852049 -1	B	122500-1
1852049 -2	B	565435-5



DIST			
66			

AMP 1756 REV 3-92 13-JUN-06 13:52:26 us016926

1852049	⇓	1852049
---------	---	---------

/home/us016926/DMTECmod

TERMINAL NAME: .250 FEMALE FINGER TYPE LOCKING CONNECTOR									
AMP TERM PN		MFR TERM PN		YAZAKI TERMINAL		CUST CRIMP SPECS			
1572708		7116-2642		PAD LTR	CRIMP HEIGHT			WIRE SIZE	
				A	1.95 ±0.05 [.077 ±.002IN]			3 OR 12 AWG	
				B	NOT			USED	
				C	NOT			USED	
				D	NOT			USED	
				CRIMP	SIZE		TYPE	RANGE	
				WIRE	3.2 [.126 IN]		F	3mm ² OR 12 AWG	
				INSUL	4.42 [.174 IN]		F	3.81 MAX	
WIRE STRIP LENGTH		TERM APPL SPEC		FEED		APPL INSTRUCTION		SET UP GAGE	LAYOUT
5.16-5.94		NONE		21.72		408-8039		458638-1	L4015

						129
						128
						127
2	2	-	C	9-354778-0	PIN, WIRE DISC (.2945)A	126
1	1	-	A	986950-1	WASHER, FLAT PRECISION	125
1	1	-	A	217238-1	GENERAL INSTRUCTION PACKAGE	124
1	1	-	-	4088039	EF APPL INST 408-8039	123
REF	REF	-	A	1-21046-6	RING, RETAINING, EXT (5/16)FD ADJ ROD	122
						121
REF	REF	-	A	1-21030-6	PIN, DOWEL (Ø.187x1.25)HSG	120
REF	REF	-	A	1-21030-1	PIN, DOWEL (Ø.187x.50)LEVER	119
REF	REF	-	A	21045-3	RING, RET "C" (Ø.187)FD PIN	118
						117
REF	REF	-	A	21899-4	WASHER, FLAT (Ø5/16)SCR ADJ	116
						115
REF	REF	-	A	18028-2	WASHER, FLAT (M4)COUNTER	114
						113
REF	REF	-	A	21024-5	WASHER, LOCK (NO.10)FD ROD GDE	112
						111
7	7	-	A	21024-4	WASHER, LOCK (NO.8)SHEAR BL	110
REF	REF	-	A	22593-1	NUT, HEX (1/4-20) MAGNET	109
2	2	-	A	21018-4	NUT, HEX (4-40) DRAG	108
REF	REF	-	A	21018-5	NUT, HEX (6-32)FD ADJ PL	107
						106
2	2	-	A	21022-2	NUT, HEX SL (8-32)DRAG STUD	105
REF	REF	-	A	9-21000-9	SCR, SHC (8-32x.44)COUNTER	104
REF	REF	-	A	3-21081-3	SCR, SHC (1/4-20X1.25)MAGNET	103
2	2	-	A	2-21006-6	SCR, SKT SET (4-40x.62)DRAG	102
1	1	-	A	21009-2	SCR, SKT SET (1/4-20x.25)RAM	101
2	2	-	A	21017-2	SCR, DRIVE (#2x.19)ID PLATE	100
1	1	-	A	1-21002-7	SCR, BHC (6-32x.38)CAM	99
1	1	-	B	461264-1	PLATE, IDENTIFICATION	98
REF	REF	-	A	6-23715-5	SCR, PAN HD (6-32x1.50)FEED ADJ	97
REF	REF	-	A	994991-5	SCR, OVAL HD (M4X14)COUNTER	96
2	2	-	A	2-21002-2	SCR, BHC (8-32x.50)STRIPPER	95
REF	REF	-	A	2-21002-9	SCR, BHC (10-32x.75)HSG CAP	94
1	1	-	A	22733-8	SCR, BHC (8-32x.38 LW)ANVIL	93
4	4	-	A	3-21002-3	SCR, BHC (1/4-20x.50)ST GD PL	92
REF	REF	-	A	2-22733-8	SCR, BHC (1/4-20x.62)BASE PL	91
						90
						89
						88
5	5	-	A	2-21000-7	SCR, SHC (8-32x.50)SLUG BLADE	87
						86
2	2	-	A	2-21000-9	SCR, SHC (8-32x.75)R STP GUIDE	85
REF	REF	-	A	3-21000-7	SCR, SHC (10-32x.75)FEED ROD GDE	84
						83
REF	REF	-	A	3-21000-6	SCR, SHC (10-32x.62)FEED ADJ PL	82
REF	REF	-	A	3-21000-4	SCR, SHC (10-32x.38)PIVOT BLOCK	81
2	2	-	A	2-21002-9	SCR, BHC (10-32x.75)SHEAR PL	80
REF	-	-	A	455745-1	GUARD, WINDOW	79
-	REF	-	A	679532-1	INSERT, GUARD	78
						77
						76
						75
1	1	-	A	690603-1	SPRING, ASSIST	74
1	1	-	A	23030-1	SCR, SKT CAP (6-32x.25)CP DSC	73
REF	REF	-	A	458109-1	WASHER, FLAT (SPECIAL)	72
REF	REF	-	A	690517-1	SPACER	71
	-2	-1	U/M	DWG SIZE	PART NO	ITEM NO
QTY	REQD	PER	ASSY		PARTS LIST	

-1	LEADMAKER & BENCH MODEL G				MECH POST FEED		
-2	BENCH MODEL K				MECH POST FEED		
1 							

THIS DRAWING IS A CONTROLLED DOCUMENT.

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT 20 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

1852049

D

C

B

A