





HONEYWELL
PART NUMBER
426EN10-8
FAA-PMA 

REV DOCUMENT CHANGED BY CHECK
5 0006596 KSR 15JUL04 AK



- NOTES
- 1 - CORROSION RESISTANT STEEL ENCLOSURE
 - 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
 - 3 - TO ADJUST ROLLER DIRECTION, REMOVE ROLLER GUIDE LOCK RING, SCREW ROLLER GUIDE DOWN AS FAR AS POSSIBLE, THEN UNSCREW TO DESIRED DIRECTION. SECURE BY REPLACING GUIDE LOCK RING
 - 4 - COINCIDENCE OF OPERATION AND RELEASING POINTS: .010 OF PLUNGER TRAVEL
 - 5 - CIRCUIT DIAGRAM, CATALOG LISTING, FED MFG CODE, DATE CODE AND FAA-PMA ARE SHOWN ON NAMEPLATE
 - 6 - REPLACEMENT MOUNTING HARDWARE: PACKET 19PA8
 - 7 - REPLACEMENT ROLLER GUIDE AND LOCKRING PACKET 15PA104
 - 8 - REPLACEMENT LOCKRING: PACKET 15PA137
 - 9 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-S-8805
 - 10 - RATING APPLIES TO CIRCUITS 1-12
 - 11 - RATING APPLIES TO CIRCUITS 13-18
 - 12 - FOR MANUFACTURING DETAIL SEE ASSEMBLY DRAWING 426EN10-8 FOR FAA-PMA

CHARACTERISTICS		ELECTRICAL DATA			
		CONTACT ARRANGEMENT 6X SPDT			
LOAD		28 VDC			
		SEA LEVEL	50,000 FT.		
RES		10	11	10	11
IND		.5	4	.5	2.5
MOTOR		4			

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:
NO PLACE X ± 0.040
ONE PLACE .X ± 0.030
TWO PLACE .XX ± 0.015
THREE PLACE .XXX ± 0.005
FOUR PLACE .XXXX ± 0.0005
ANGLES ± 2°

THIRD ANGLE PROJECTION 

DRAWN	KSR	15JUL04	Honeywell
CHECK	AK	15JUL04	
THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - ENCLOSED
INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			
SIZE C	TYPE I	DRAWING NAME 426EN10-8	REV 5
SCALE FULL	WEIGHT 32 OZ MAX	SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[426EN10-8](#)