

MICRO SWITCH
a Honeywell Division


FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

16HM4

CATALOG LISTING
16HM4
PAGE 1 OF 1
REPLACES
RELEASE NO. PR-16881
CHECK
REVISIONS
A PR-16881
MAM
16 NOV 88
B CO-1
71228
TSM
5 NOV 91
C CO-1
80788
SAD
26 APR 95
D 0004537
KR
01 APR 04
CHECK
17 NOV 88
TSK
CHECK
16 NOV 88
DRAWN
DDM/CAD



- NOTES**
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS
 - 2 - FOR USE IN TEMPERATURE RANGE -85°F TO +500°F (-65°C TO 260°C) (DOWN TO -300°F (-184°C) IF WIRE LEADS ARE NOT FLEXED)
 - 3 - SWITCH IS HERMETICALLY SEALED PER ENCLOSURE DESIGN SYMBOL 5 MIL-PRF-8805/8
 - 4 - ALL EXPOSED PARTS ARE OF CORROSION RESISTANT MATERIALS
 - 5 WEIGHT OF SWITCH ONLY IS 0.014 LB MAX. WEIGHT OF CONDUCTOR GROUP ONLY IS 0.013 LB MAX PER FOOT
 - 6 - DO NOT APPLY MORE THAN 1 1/2 INCH LBS OF TORQUE WHEN TIGHTENING MOUNTING SCREWS
 - 7 - SILVER CAD OXIDE MOVABLE CONTACT. HONEYWELL DOES NOT RECOMMEND THE USE OF SILVER CAD OXIDE CONTACTS WITH NON-ARCING LOADS. NON-ARCING LOADS ARE GENERALLY LESS THAN 12 VOLTS AND/OR 0.5 AMPS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	ELECTRICAL DATA			SCALE 2 : 1	DO NOT SCALE PRINT
OPERATING FORCE — — — — 7 OZ MAX	CONTACT ARRANGEMENT			UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — 1 OZ MIN	S P D T				
DIFFERENTIAL TRAVEL — — — .0003—.006	LINE VOLTAGE	INDUCTIVE LOAD	RESISTIVE LOAD	ONE PLACE (.0)	±.030
OVERTRAVEL — — — — .003 MIN	28 VDC	1 AMP	3 AMP	TWO PLACE (.00)	±.015
	115 VAC (400 CYCLE)	1 AMP	1 AMP	THREE PLACE (.000)	±.005
				ANGLES	±
				WEIGHT	/5\

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[16HM4](#)