


22AT55-4-M
PAGE 1 OF 1
M
DRAWING NUMBER
ISSUE 8
RELEASE NO. SR 11414
REPLACES
8 JAN 64
CHECK
7 JAN 64
E D
CHECK
10 JUN 83
F
10 FEB 89
F
17 DEC 98
G
207106
MDM
JAN 03
DRAWN
OMW
7 JAN 64
RASTER
FO-30378-001



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
	CONTACT ARRANGEMENT S P D T (4)	DO NOT SCALE PRINT
250 VAC —————	————— 5 AMP	UNLESS OTHERWISE NOTED
30 VOLTS DC RATING		DIMENSIONS ARE IN INCHES
INDUCTIVE ———— SEA LEVEL ————	3 AMP	TOLERANCES ARE:
50,000 FT ————	2.5 AMP	ONE PLACE (.0) ±.030
RESISTIVE ———— SEA LEVEL ————	5 AMP	TWO PLACE (.00) ±.015
50,000 FT ————	5 AMP	THREE PLACE (.000) ±.003
MAXIMUM INRUSH ————	24 AMP	ANGLES ±
		WEIGHT .55 LB MAX

- NOTES
- 1 - SWITCHES DO NOT NECESSARY OPERATE SIMULTANEOUSLY
 - 2 - UNIT INCLUDES 11SM1-T TYPE BASIC SWITCH (4)
 - 3 - LEAD WIRES MARKED AT APPROXIMATELY 3.0 INTERVALS WITH SWITCH NUMBER AND CIRCUIT IDENTIFICATION (1 - NO), (1 - NC), (1 - C), (2 - NC), (2 - C), (2 - NO), (3 - C), (3 - NC), (3 - NO), (4 - C), (4 - NC), AND (4 - NO)
 - 4 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET PER MIL-PRF-8805
 - 5 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA312-AT