

Description:

This NPN transistor in a TO-3 package is designed for high voltage switching applications.



Applications:

- Off Line Power Supplies
- Converter Circuits
- Pulse Width Modulated Regulators Specification Feature:
- High Voltage Capability
- Fast Switching Speeds
- Low Saturation Voltage

Absolute maximum Ratings:

Collector-Emitter Voltage, V_{CEO}	: 400V
Collector-Emitter Voltage, V_{CEX}	: 450V
Collector-Emitter Voltage, V_{CEV}	: 650V
Emitter-Base Voltage, V_{EB}	: 8V
Collector Current, Continuous I_C	: 15A
Base Current Peak, I_{CM}	: 20A
Total Device Dissipation ($T_C = +25^\circ\text{C}$), P_D	: 175W
Derate Above 25°C	: 1.0W/ $^\circ\text{C}$
Operating Junction Temperature Range, T_J	: -65°C to $+200^\circ\text{C}$
Storage Temperature Range, T_{stg}	: -65°C to $+200^\circ\text{C}$
Thermal Resistance, Junction-to-Case, R_{thJC}	: 1.0°C/W
Maximum Lead Temperature (During Soldering, 1/8" from case, 5sec), T_L	: $+275^\circ\text{C}$

Electrical Characteristics: ($T_A = +25^\circ\text{C}$ Unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Max	Unit
OFF Characteristics					
Collector-Emitter Sustaining Voltage	V _{CEO (SUS)}	I _C = 200mA, I _B = 0	400	-	V
Collector Cut-off Current	I _{CEV}	V _{CE} = 650V, V _{EB(OFF)} = -1.5V	-	0.1	mA
		V _{CE} = 650V, V _{EB (OFF)} = 1.5V, T _C = +100°C	-	1.0	
Emitter Cut-off Current	I _{EBO}	V _{EB} = 8V, I _C = 0	-	2.0	
ON Characteristics (Note 1)					
DC Current Gain	h _{FE}	I _C = 15A, V _{CE} = 3V	8	-	-
Collector-Emitter Saturation Voltage	V _{CE(sat)}	I _C = 15A, I _B = 3A	-	1.5	V
Base-Emitter Saturation Voltage	V _{BE(sat)}	I _C = 15A, V _{CE} = 3A		1.5	
Dynamic Characteristics					
Current Gain-Bandwidth Product	f _T	V _{CE} = 20V, I _C = 20mA, f = 100MHz	3	-	MHz
Output Capacitance	C _{ob}	V _{CB} = 10V, I _E = 0, f = 1MHz	-	500	pF


Bipolar Transistor



Switching Characteristics

Delay Time	t_d	$V_{CC} = 200V, I_C = 15A, I_{B1} = I_{B2} = 3A$ Duty Cycle $\leq 2\%$ $V_{BB} = 6V, R_L = 13.5\Omega$	-	0.2	μs
Rise Time	t_r		-	0.6	
Storage Time	t_s		-	2.5	
Fall Time	t_f		-	0.6	

Notes: 1. Pulse Test: Pulse Width 300 μs , Duty Cycle $\leq 2\%$.



Dim	Min	Max
A	38.75	39.96
B	19.28	22.23
C	7.96	9.28
D	11.18	12.19
E	25.2	26.67
F	0.92	1.09
G	1.38	1.62
H	29.9	30.4
I	16.64	17.3
J	3.88	4.36
K	10.67	11.18

Dimensions : Millimetres

Part Number Table

Description	Part Number
Transistor, Bipolar, Metal, TO-3, NPN	2N6678

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.