

PRODUCT NUMBER

71600-YXXXLF

LEAD FREE, SEE NOTE 6

COLOR OPTION, SEE NOTE 1

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2

OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5



LEFT POLARIZING
NOTE 5

CENTRAL KEY
NOTE 5

RIGHT POLARIZING
NOTE 5

NOTES:


- HOUSING MATERIAL : GLASS FILLED THERMOPLASTIC. UL94V-0 COLOR: GREY
= STANDARD COLOR GREY
B = OPTION COLOR BLACK
- PIN MATERIAL : PHOSPHOR BRONZE
- PRODUCT PACKAGED IN TUBES.
- TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$
- 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.




mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family 2.54MM IDC
lfr	ecn no	dr	date	tolerances unless otherwise specified			title
AP	F12-0046	LMU	12.04.25	angles	X.X ±0.3	mm	QUICKIE III FEM 0.76μm Au
AR	B-17851	LMU	14.06.05	linear	X.XX ±0.13		
AS	F-26816	LMU	17.06.06		X.XXX ±0.05	scale 5:1	
AL	F06-0270	LMU	06.09.12	dr	D.LE	01.01.24	dwg no
AM	F06-0274	LMU	06.09.25	enrg	P.NZ	01.01.24	sheet 1 of 2 size
AN	F09-0233	LMU	09.12.15	chr	JF.N	01.01.24	71600 A3
sheet	revision	AS	AG	appd	P.NZ	01.01.24	type
index	sheet	1	2				CUSTOMER Drawing

STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	


624
304
204 / 224
004
DASHES NOT AVAILABLE




WITHOUT STRAIN RELIEF




WITH LOW PROFILE STRAIN RELIEF




WITH STANDARD STRAIN RELIEF




WITH LATCHING STRAIN RELIEF



LOW PROFILE
STRAIN RELIEF



STANDARD
STRAIN RELIEF



LATCHING STRAIN RELIEF
FOR SLIM HEADER

71600-6YY(B)LF	●					●
71600-3YY(B)LF		●	●			
71600-2YY(B)LF	●			●		
71600-1YY(B)LF	●			●		
71600-0YY(B)LF	●		●			
PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
	STRAIN RELIEF					

mat'l. code	surface	tolerance	projection	product family
ISO 1302	ISO 406	ISO 1101	QUICKIE	
ltr	ecn no	dr	date	tolerances unless otherwise specified
AF	B-17851	LMU	14.06.05	angles
AG	F-26816	LMU	17.06.06	linear
AB	F03019	DLE	03.01.23	dr
AC	F05-0180	LMU	05.04.22	engr
AD	F06-0270	LMU	06.09.12	chr
AE	F06-0274	LMU	06.09.25	appd
sheet index	revision sheet			

