

DO NOT
SCALE FROM
THIS PRINT






FIG 2
(SAME AS FIG 1 EXCEPT INSULATOR)



CLM-1XX-XX-XX-D-XX



No OF POSITIONS / ROW
-02 THRU -50

LEAD STYLE SPEC
-02: SURFACE MOUNT
(USE C-117-01-X)

PLATING SPECIFICATION
-F: 3μ" FLASH SELECTIVE GOLD IN CONTACT
AREA MATTE TIN ON TAIL
(PRE-PLATED CONTACT)
-L: 10μ" LIGHT SELECTIVE GOLD IN CONTACT
AREA MATTE TIN ON TAIL
(PRE-PLATED CONTACT)
-G: 10μ" GOLD IN CONTACT AREA 3μ" ON TAIL
(POST-PLATED CONTACT)
-H: 30μ" HEAVY GOLD IN CONTACT AREA
3μ" ON TAIL
(POST-PLATED CONTACT)
-LM: 10μ" LIGHT SELECTIVE GOLD IN CONTACT
AREA MATTE TIN ON TAIL
(PRE-PLATED CONTACT)
-FM: 3μ" FLASH SELECTIVE GOLD IN CONTACT
AREA MATTE TIN ON TAIL
(PRE-PLATED CONTACT)

OPTION
-P: PICK & PLACE PAD
(AVAILABLE ON POS 7 THRU 50 ONLY)
(SEE FIG 3, SHT 2)(USE LMP-04)
-TR: TAPE & REEL
-BE: BOTTOM ENTRY ONLY
(SEE FIG 2)(USE CLM-XX-DBE-XX)
-PA: PICK & PLACE PAD W/ ALIGNMENT PINS
(SEE FIG 4, SHT 2)
-A: ALIGNMENT PIN (USE CLM-XX-D-XX)
(AVAILABLE ON POS 3 THRU 50 ONLY)
(SEE FIG 5, SHT 2)
-K: POLYIMIDE FILM PAD
(AVAILABLE ON POS 7 THRU 50 ONLY)
(.005 [.13] THICKNESS)(SEE FIG 6, SHT 2)
(USE K-DOT-.138-.250-.005)

BODY SPEC
-D: DOUBLE ROW
(USE CLM-XX-D)



- NOTES:
1. Ⓢ REPRESENTS CRITICAL DIMENSION.
 2. MINIMUM PUSHOUT FORCE: .5 LB.
 3. WILL LOSE A POSITION FOR EVERY CUT MADE ON A SOCKET STRIP.
 4. POSITIONS -05 THROUGH -50 ARE TO BE TUBED. POSITIONS -02 THRU -04 TO BE LAYER PACKAGED ONLY.
 5. SHEAR TAILS TO DIMENSIONS SHOWN, .003 MAX SHEAR BURR.
 6. PARTS TO BE SYMMETRICAL ABOUT Q.
 7. CUT FLASH TO BE .010 [.25] MAX WITH NO FLASH ALLOWED IN HOLES OR EXTENDING BELOW LEADS.
 8. ENDWALL AFTER CUTTING: .0155±.0025 [.398±.064]
 9. COPLANARITY TO BE .0040 FOR POSITIONS 2-25 & .0060 FOR POSITIONS 26-50.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:	
DECIMALS	ANGLES
.XX: ±.01 [.3]	2°
.XXX: ±.005 [.13]	
.XXXX: ±.0020 [.051]	
MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 2:1	
BODY: LCP, UL 94 VO	
COLOR: BLACK	
TERMINAL: PHOS BRONZE	
C:\EnterpriseVault\DWG\MISC\MKTG\CLM-1XX-XX-XX-D-XX-MKT.SLDDRW	


PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322


DESCRIPTION:	LOW PROFILE 1MM x 1MM DOUBLE ROW BODY
DWG. NO.	CLM-1XX-XX-XX-D-XX
BY: G. PURVIS	08/10/94
SHEET 1 OF 2	

FIG 3
-P: PICK & PLACE PAD
AVAILABLE ON POSITIONS 7 THRU 50 ONLY



NOTE: "N" = USED MEASURED DIMENSION (REF)
"Q" = {("N" - .225[5.72]) / 2} ±.020[.51]

FIG 5
-A: MOLDED ALIGNMENT PIN



-PACKAGING
(SEE NOTE 4)

BH

TABLE 2 (INCLUDES -D & -D-BE)		
OPTION	TUBE	PLUG
-P, -A-P	PT-CLX001-D	TP-33
-NONE -A, -A-K, -K	PT-1-24-01-50	TP-33

NOTE: ALL -PA OPTION PARTS SHIP
IN EIA-960 TRAYS.

BH

FIG 4
-PA: PICK & PLACE PAD WITH ALIGNMENT PINS





TABLE 1

POS / ROW	"A"	"M"	"P"
4-15	.140[3.58] REF	USED MEASURED DIMENSION(REF)	{("M" - "A") / 2} ±.010[.25]
16-50	.280[7.11] REF		



TABLE 3

POSITIONS		PAD
EVEN	4-14	PPP-39-E-4-15
	16-50	PPP-39-E-16-50
ODD	5-15	PPP-39-O-4-15
	17-49	PPP-39-O-16-50

FIG 6
-K: POLYAMIDE FILM PAD
AVAILABLE ON POSITIONS 7 THRU 50 ONLY



NOTE: "R" = USED MEASURED DIMENSION (REF)
"S" = {("R" - .138[3.50]) / 2} ±.020[.51]



PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 4:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:
LOW PROFILE 1MM x 1MM DOUBLE ROW BODY

DWG. NO. **CLM-1XX-XX-XX-D-XX**

BY: G. PURVIS 08/10/94 SHEET 2 OF 2