


THE INFORMATION CONTAINED HEREIN IS CONSIDERED
"PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE
COPIED, REPRODUCED OR DISCLOSED WITHOUT THE
WRITTEN APPROVAL OF BEL FUSE INC.

ELECTRICAL CHARACTERISTICS @ 25°C

RoHS



SCHEMATIC



URNS RATIO

Tx SIDE:

1CT : 1CT

Rx SIDE:

1CT : 1CT

POLARITY :

Rx 4°&37°, 7°&34°, 14°&27°, 17°&24°

Tx 1°&40°, 10°&31°, 11°&30°, 20°&21°

IN PHASE

QCL

350μH MIN. @ 100kHz, 100mV

WITH 8mA D.C. BIAS.

INSERTION LOSS

@ 100kHz - 80MHz 1.0 dB MAX

RETURN LOSS

MEASURED UNDER A

@ 0.1MHz - 30MHz 18 dB MIN.

100 Ω ENVIRONMENT

@ 30MHz - 60MHz 18-20 LOG(f/30MHz)

@ 60MHz - 80MHz 12 dB MIN.

COMMON TO DIFFERENTIAL

@ 0.1MHz TO 100MHz 40 dB MIN.

MODE REJECTION

COMMON TO COMMON

@ 0.1MHz TO 100MHz 35 dB MIN.

MODE REJECTION

@ 100MHz TO 500MHz 20 dB MIN.

CROSSTALK

@ 0.1MHz TO 100MHz 32 dB MIN.

HIPOT

PER HAND-WORK-03

NOTES :

THIS PRODUCT HAS BEEN SUPPLYING TO
JAPAN CUSTOMERS. PCN PROCESS NEEDS
TO COMPLY WITH 4M CRITERIA.

REV. : D


PAGE : 2

ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM.	[] METRIC DIM. AS REF.
Alice Pang	2015-07-16	ELECTRICAL SPECIFICATION S558-5999-Q9-F	X5585999Q9-F	TOL. IN INCH	UNIT : INCH [mm]
DRAWN BY	DATE		FILE NAME	.X	SCALE : N/A
ZC Guo	2015-07-16		X5585999Q9FD.DWG	.XX	SIZE : A4
				.XXX	



THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.



RoHS



NOTES :

1. STANDARD MARKING REFER TO DOC. HAND-WORK-04.
2. PACKAGE CODE: "RRS001".
3. THIS PRODUCT HAS BEEN SUPPLYING TO JAPAN CUSTOMERS. PCN PROCESS NEEDS TO COMPLY WITH 4M CRITERIA.

SUGGESTED PCB PAD LAYOUT



ORIGINATED BY	DATE	TITLE	PART NO. / DRAWING NO.	STANDARD DIM.	[] METRIC DIM. AS REF.	REV. : H	PAGE : 3
Lawrence Tsang	2017-02-15	MECHANICAL DRAWING S558-5999-Q9-F	X5585999Q9-F	TOL. IN INCH	UNIT : INCH [mm]	 POWER PROTECT CONNECT	
DRAWN BY	DATE		FILE NAME	.X	SCALE : N/A		
ZC Guo	2017-02-15		X5585999Q9FH.DWG	.XX ±0.01 .XXX ±0.005	SIZE : A4		