

# LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V, LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV QUADRUPLE OPERATIONAL AMPLIFIERS

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005


- 2-kV ESD Protection for:
  - LM224K, LM224KA
  - LM324K, LM324KA
  - LM2902K, LM2902KV, LM2902KAV
- Wide Supply Ranges
  - Single Supply . . . 3 V to 32 V  
(26 V for LM2902)
  - Dual Supplies . . .  $\pm 1.5$  V to  $\pm 16$  V  
( $\pm 13$  V for LM2902)
- Low Supply-Current Drain Independent of Supply Voltage . . . 0.8 mA Typ
- Common-Mode Input Voltage Range Includes Ground, Allowing Direct Sensing Near Ground
- Low Input Bias and Offset Parameters
  - Input Offset Voltage . . . 3 mV Typ  
A Versions . . . 2 mV Typ
  - Input Offset Current . . . 2 nA Typ
  - Input Bias Current . . . 20 nA Typ  
A Versions . . . 15 nA Typ
- Differential Input Voltage Range Equal to Maximum-Rated Supply Voltage . . . 32 V  
(26 V for LM2902)
- Open-Loop Differential Voltage Amplification . . . 100 V/mV Typ
- Internal Frequency Compensation

## description/ordering information


These devices consist of four independent high-gain frequency-compensated operational amplifiers that are designed specifically to operate from a single supply over a wide range of voltages. Operation from split supplies also is possible if the difference between the two supplies is 3 V to 32 V (3 V to 26 V for the LM2902), and  $V_{CC}$  is at least 1.5 V more positive than the input common-mode voltage. The low supply-current drain is independent of the magnitude of the supply voltage.

Applications include transducer amplifiers, dc amplification blocks, and all the conventional operational-amplifier circuits that now can be more easily implemented in single-supply-voltage systems. For example, the LM124 can be operated directly from the standard 5-V supply that is used in digital systems and provides the required interface electronics, without requiring additional  $\pm 15$ -V supplies.

LM124 . . . D, J, OR W PACKAGE  
LM124A . . . J PACKAGE  
LM224, LM224A, LM224K, LM224KA . . . D OR N PACKAGE  
LM324, LM324K . . . D, N, NS, OR PW PACKAGE  
LM324A . . . D, DB, N, NS, OR PW PACKAGE  
LM324KA . . . D, N, NS, OR PW PACKAGE  
LM2902 . . . D, N, NS, OR PW PACKAGE  
LM2902K . . . D, DB, N, NS, OR PW PACKAGE  
LM2902KV, LM2902KAV . . . D OR PW PACKAGE  
(TOP VIEW)



LM124, LM124A . . . FK PACKAGE  
(TOP VIEW)



NC – No internal connection

**LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V,  
LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV  
QUADRUPLE OPERATIONAL AMPLIFIERS**

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

**description/ordering information (continued)**

**ORDERING INFORMATION**

| $T_A$         | $V_{IOmax}$<br>AT 25°C | MAX<br>TESTED<br>$V_{CC}$ | PACKAGE†   |              | ORDERABLE<br>PART NUMBER | TOP-SIDE<br>MARKING |
|---------------|------------------------|---------------------------|------------|--------------|--------------------------|---------------------|
| 0°C to 70°C   | 7 mV                   | 30 V                      | PDIP (N)   | Tube of 25   | LM324N                   | LM324N              |
|               |                        |                           |            |              | LM324KN                  | LM324KN             |
|               |                        |                           | SOIC (D)   | Tube of 50   | LM324D                   | LM324               |
|               |                        |                           |            | Reel of 2500 | LM324DR                  |                     |
|               |                        |                           |            | Tube of 50   | LM324KD                  | LM324K              |
|               |                        |                           |            | Reel of 2500 | LM324KDR                 |                     |
|               |                        |                           | SOP (NS)   | Reel of 2000 | LM324NSR                 | LM324               |
|               |                        |                           |            | Tube of 50   | LM324KNS                 | LM324K              |
|               |                        |                           |            | Reel of 2000 | LM324KNSR                |                     |
|               |                        |                           | TSSOP (PW) | Tube of 90   | LM324PW                  | L324                |
|               |                        |                           |            | Reel of 2000 | LM324PWR                 |                     |
|               |                        |                           |            | Tube of 90   | LM324KPW                 | L324K               |
|               |                        |                           |            | Reel of 2000 | LM324KPWR                |                     |
|               | 3 mV                   | 30 V                      | PDIP (N)   | Tube of 25   | LM324AN                  | LM324AN             |
|               |                        |                           |            | Tube of 25   | LM324KAN                 | LM324KAN            |
|               |                        |                           | SOIC (D)   | Tube of 50   | LM324AD                  | LM324A              |
|               |                        |                           |            | Reel of 2500 | LM324ADR                 |                     |
|               |                        |                           |            | Tube of 50   | LM324KAD                 | LM324KA             |
|               |                        |                           |            | Reel of 2500 | LM324KADR                |                     |
|               |                        |                           | SOP (NS)   | Reel of 2000 | LM324ANSR                | LM324A              |
|               |                        |                           |            | Tube of 50   | LM324KANS                | LM324KA             |
|               |                        |                           |            | Reel of 2000 | LM324KANSR               |                     |
|               |                        |                           | SSOP (DB)  | Reel of 2000 | LM324ADBR                | LM324A              |
|               |                        |                           | TSSOP (PW) | Tube of 90   | LM324APW                 | L324A               |
|               |                        |                           |            | Reel of 2000 | LM324APWR                |                     |
|               |                        |                           |            | Tube of 90   | LM324KAPW                | L324KA              |
|               |                        |                           |            | Reel of 2000 | LM324KAPWR               |                     |
| –25°C to 85°C | 5 mV                   | 30 V                      | PDIP (N)   | Tube of 25   | LM224N                   | LM224N              |
|               |                        |                           |            |              | LM224KN                  | LM224KN             |
|               |                        |                           | SOIC (D)   | Tube of 50   | LM224D                   | LM224               |
|               |                        |                           |            | Reel of 2500 | LM224DR                  |                     |
|               |                        |                           |            | Tube of 50   | LM224KD                  | LM224K              |
|               |                        |                           |            | Reel of 2500 | LM224KDR                 |                     |
|               | 3 mV                   | 30 V                      | PDIP (N)   | Tube of 25   | LM224AN                  | LM224AN             |
|               |                        |                           |            | Tube of 25   | LM224KAN                 | LM224KAN            |
|               |                        |                           | SOIC (D)   | Tube of 50   | LM224AD                  | LM224A              |
|               |                        |                           |            | Reel of 2500 | LM224ADR                 |                     |
|               |                        |                           |            | Tube of 50   | LM224KAD                 | LM224KA             |
|               |                        |                           |            | Reel of 2500 | LM224KADR                |                     |

† Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).



POST OFFICE BOX 655303 • DALLAS, TEXAS 75265

**LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V,  
LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV  
QUADRUPLE OPERATIONAL AMPLIFIERS**


SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

**ORDERING INFORMATION (CONTINUED)**

| $T_A$          | $V_{IOmax}$<br>AT 25°C | MAX<br>TESTED<br>$V_{CC}$ | PACKAGE†   |              | ORDERABLE<br>PART NUMBER | TOP-SIDE<br>MARKING |
|----------------|------------------------|---------------------------|------------|--------------|--------------------------|---------------------|
| –40°C to 125°C | 7 mV                   | 26 V                      | PDIP (N)   | Tube of 25   | LM2902N                  | LM2902N             |
|                |                        |                           |            | Tube of 25   | LM2902KN                 | LM2902KN            |
|                |                        |                           | SOIC (D)   | Tube of 50   | LM2902D                  | LM2902              |
|                |                        |                           |            | Reel of 2500 | LM2902DR                 |                     |
|                |                        |                           |            | Tube of 50   | LM2902KD                 | LM2902K             |
|                |                        |                           |            | Reel of 2500 | LM2902KDR                |                     |
|                |                        |                           | SOP (NS)   | Reel of 2000 | LM2902NSR                | LM2902              |
|                |                        |                           |            | Tube of 50   | LM2902KNS                | LM2902K             |
|                |                        |                           |            | Reel of 2000 | LM2902KNSR               |                     |
|                |                        |                           | SSOP (DB)  | Tube of 80   | LM2902KDB                | L2902K              |
|                |                        |                           |            | Reel of 2000 | LM2902KDBR               |                     |
|                |                        |                           | TSSOP (PW) | Tube of 90   | LM2902PW                 | L2902               |
|                |                        |                           |            | Reel of 2000 | LM2902PWR                |                     |
|                |                        |                           |            | Tube of 90   | LM2902KPW                | L2902K              |
|                |                        |                           |            | Reel of 2000 | LM2902KPWR               |                     |
| –55°C to 125°C | 5 mV                   | 30 V                      | SOIC (D)   | Reel of 2500 | LM2902KVQDR              | L2902KV             |
|                |                        |                           | TSSOP (PW) | Reel of 2000 | LM2902KVQPWR             | L2902KV             |
|                |                        |                           | SOIC (D)   | Reel of 2500 | LM2902KAVQDR             | L2902KA             |
|                |                        |                           | TSSOP (PW) | Reel of 2000 | LM2902KAVQPWR            | L2902KA             |
|                | 2 mV                   | 30 V                      | CDIP (J)   | Tube of 25   | LM124J                   | LM124J              |
|                |                        |                           | CFP (W)    | Tube of 25   | LM124W                   | LM124W              |
|                | 5 mV                   | 30 V                      | LCCC (FK)  | Tube of 55   | LM124FK                  | LM124FK             |
|                |                        |                           | SOIC (D)   | Tube of 50   | LM124D                   | LM124               |
|                |                        |                           |            | Reel of 2500 | LM124DR                  |                     |
|                |                        |                           | CDIP (J)   | Tube of 25   | LM124AJ                  | LM124AJ             |
|                | 2 mV                   | 30 V                      | LCCC (FK)  | Tube of 55   | LM124AFK                 | LM124AFK            |
|                |                        |                           |            |              |                          |                     |

† Package drawings, standard packing quantities, thermal data, symbolization, and PCB design guidelines are available at [www.ti.com/sc/package](http://www.ti.com/sc/package).


**symbol (each amplifier)**



LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V,  
LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV  
QUADRUPLE OPERATIONAL AMPLIFIERS

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

schematic (each amplifier)



| COMPONENT COUNT<br>(total device) |    |
|-----------------------------------|----|
| Epi-FET                           | 1  |
| Transistors                       | 95 |
| Diodes                            | 4  |
| Resistors                         | 11 |
| Capacitors                        | 4  |

† ESD protection cells - available on LM324K and LM324KA only

**LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V,  
LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV  
QUADRUPLE OPERATIONAL AMPLIFIERS**

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

**absolute maximum ratings over operating free-air temperature range (unless otherwise noted)<sup>†</sup>**

|                                                                                                                                     |                | LM2902         | ALL OTHER DEVICES | UNIT               |
|-------------------------------------------------------------------------------------------------------------------------------------|----------------|----------------|-------------------|--------------------|
| Supply voltage, $V_{CC}$ (see Note 1)                                                                                               |                | $\pm 13$ or 26 | $\pm 16$ or 32    | V                  |
| Differential input voltage, $V_{ID}$ (see Note 2)                                                                                   |                | $\pm 26$       | $\pm 32$          | V                  |
| Input voltage, $V_I$ (either input)                                                                                                 |                | -0.3 to 26     | -0.3 to 32        | V                  |
| Duration of output short circuit (one amplifier) to ground at (or below) $T_A = 25^\circ\text{C}$ , $V_{CC} \leq 15$ V (see Note 3) |                | Unlimited      | Unlimited         |                    |
| Package thermal impedance, $\theta_{JA}$ (see Notes 4 and 5)                                                                        | D package      | 86             | 86                | $^\circ\text{C/W}$ |
|                                                                                                                                     | DB package     | 96             | 96                |                    |
|                                                                                                                                     | N package      | 80             | 80                |                    |
|                                                                                                                                     | NS package     | 76             | 76                |                    |
|                                                                                                                                     | PW package     | 113            | 113               |                    |
| Package thermal impedance, $\theta_{JC}$ (see Notes 6 and 7)                                                                        | FK package     |                | 5.61              | $^\circ\text{C/W}$ |
|                                                                                                                                     | J package      |                | 15.05             |                    |
|                                                                                                                                     | W package      |                | 14.65             |                    |
| Operating virtual junction temperature, $T_J$                                                                                       |                | 150            | 150               | $^\circ\text{C}$   |
| Case temperature for 60 seconds                                                                                                     | FK package     |                | 260               | $^\circ\text{C}$   |
| Lead temperature 1.6 mm (1/16 inch) from case for 60 seconds                                                                        | J or W package | 300            | 300               | $^\circ\text{C}$   |
| Storage temperature range, $T_{stg}$                                                                                                |                | -65 to 150     | -65 to 150        | $^\circ\text{C}$   |

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

- NOTES:
1. All voltage values (except differential voltages and  $V_{CC}$  specified for the measurement of  $I_{OS}$ ) are with respect to the network GND.
  2. Differential voltages are at  $IN+$ , with respect to  $IN-$ .
  3. Short circuits from outputs to  $V_{CC}$  can cause excessive heating and eventual destruction.
  4. Maximum power dissipation is a function of  $T_J(\text{max})$ ,  $\theta_{JA}$ , and  $T_A$ . The maximum allowable power dissipation at any allowable ambient temperature is  $P_D = (T_J(\text{max}) - T_A)/\theta_{JA}$ . Operating at the absolute maximum  $T_J$  of  $150^\circ\text{C}$  can affect reliability.
  5. The package thermal impedance is calculated in accordance with JESD 51-7.
  6. Maximum power dissipation is a function of  $T_J(\text{max})$ ,  $\theta_{JC}$ , and  $T_C$ . The maximum allowable power dissipation at any allowable case temperature is  $P_D = (T_J(\text{max}) - T_C)/\theta_{JC}$ . Operating at the absolute maximum  $T_J$  of  $150^\circ\text{C}$  can affect reliability.
  7. The package thermal impedance is calculated in accordance with MIL-STD-883.

## ESD protection

| TEST CONDITIONS  |                                                                | TYP     | UNIT |
|------------------|----------------------------------------------------------------|---------|------|
| Human-Body Model | LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV | $\pm 2$ | kV   |



# LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V, LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV QUADRUPLE OPERATIONAL AMPLIFIERS

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

electrical characteristics at specified free-air temperature,  $V_{CC} = 5\text{ V}$  (unless otherwise noted)

| PARAMETER |                                                 |                                                | TEST CONDITIONS† | TA‡        | LM124<br>LM224    |      |      | LM324<br>LM324K   |      |      | UNIT |
|-----------|-------------------------------------------------|------------------------------------------------|------------------|------------|-------------------|------|------|-------------------|------|------|------|
|           |                                                 |                                                |                  |            | MIN               | TYP§ | MAX  | MIN               | TYP§ | MAX  |      |
| VIO       | Input offset voltage                            | VCC = 5 V to MAX,<br>VIC = VICRmin, VO = 1.4 V |                  | 25°C       | 3                 |      | 5    | 3                 |      | 7    | mV   |
|           |                                                 |                                                |                  | Full range |                   |      | 7    |                   |      | 9    |      |
| IIO       | Input offset current                            | VO = 1.4 V                                     |                  | 25°C       | 2                 |      | 30   | 2                 |      | 50   | nA   |
|           |                                                 |                                                |                  | Full range |                   |      | 100  |                   |      | 150  |      |
| IIB       | Input bias current                              | VO = 1.4 V                                     |                  | 25°C       | –20               |      | –150 | –20               |      | –250 | nA   |
|           |                                                 |                                                |                  | Full range |                   |      | –300 |                   |      | –500 |      |
| VICR      | Common-mode input voltage range                 | VCC = 5 V to MAX                               |                  | 25°C       | 0 to<br>VCC – 1.5 |      |      | 0 to<br>VCC – 1.5 |      |      | V    |
|           |                                                 |                                                |                  | Full range | 0 to<br>VCC – 2   |      |      | 0 to<br>VCC – 2   |      |      |      |
| VOH       | High-level output voltage                       | RL = 2 kΩ                                      |                  | 25°C       | VCC – 1.5         |      |      | VCC – 1.5         |      |      | V    |
|           |                                                 | RL = 10 kΩ                                     |                  | 25°C       |                   |      |      |                   |      |      |      |
|           |                                                 | VCC = MAX                                      | RL = 2 kΩ        | Full range | 26                |      | 26   |                   |      |      |      |
|           |                                                 |                                                | RL ≥ 10 kΩ       | Full range | 27                | 28   | 27   |                   | 28   |      |      |
| VOL       | Low-level output voltage                        | RL ≤ 10 kΩ                                     |                  | Full range | 5                 |      | 20   | 5                 |      | 20   | mV   |
| AVD       | Large-signal differential voltage amplification | VCC = 15 V, VO = 1 V to 11 V,<br>RL ≥ 2 kΩ     |                  | 25°C       | 50                | 100  | 25   |                   | 100  | V/mV |      |
|           |                                                 |                                                |                  | Full range | 25                |      | 15   |                   |      |      |      |
| CMRR      | Common-mode rejection ratio                     | VIC = VICRmin                                  |                  | 25°C       | 70                | 80   | 65   |                   | 80   | dB   |      |
| kSVR      | Supply-voltage rejection ratio (ΔVCC/ΔVIO)      |                                                |                  | 25°C       | 65                | 100  | 65   |                   | 100  | dB   |      |
| VO1/VO2   | Crosstalk attenuation                           | f = 1 kHz to 20 kHz                            |                  | 25°C       | 120               |      |      | 120               |      | dB   |      |
| IO        | Output current                                  | VCC = 15 V,<br>VID = 1 V,<br>VO = 0            | Source           | 25°C       | –20               | –30  | –60  | –20               | –30  | –60  | mA   |
|           |                                                 |                                                |                  | Full range | –10               |      | –10  |                   |      |      |      |
|           |                                                 | VCC = 15 V,<br>VID = –1 V,<br>VO = 15 V        | Sink             | 25°C       | 10                |      | 20   | 10                |      | 20   |      |
|           |                                                 |                                                |                  | Full range | 5                 |      | 5    |                   |      |      |      |
|           |                                                 | VID = –1 V, VO = 200 mV                        | 25°C             | 12         |                   | 30   | 12   |                   | 30   | μA   |      |
| IOS       | Short-circuit output current                    | VCC at 5 V, VO = 0,<br>GND at –5 V             |                  | 25°C       | ±40               |      | ±60  | ±40               |      | ±60  | mA   |
| ICC       | Supply current (four amplifiers)                | VO = 2.5 V, No load                            |                  | Full range | 0.7               |      | 1.2  | 0.7               |      | 1.2  | mA   |
|           |                                                 | VCC = MAX, VO = 0.5 VCC, No load               |                  | Full range | 1.4               |      | 3    | 1.4               |      | 3    |      |

<sup>†</sup> All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise specified. MAX  $V_{CC}$  for testing purposes is 26 V for LM2902 and 30 V for the others.

<sup>‡</sup> Full range is –55°C to 125°C for LM124, –25°C to 85°C for LM224, and 0°C to 70°C for LM324.

<sup>§</sup> All typical values are at  $T_A = 25^\circ\text{C}$ .

**LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V,  
LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV**  
**QUADRUPLE OPERATIONAL AMPLIFIERS**

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

**electrical characteristics at specified free-air temperature,  $V_{CC} = 5\text{ V}$  (unless otherwise noted)**

| PARAMETER                        |                                                                      | TEST CONDITIONS†                                                                                   |                        | T <sub>A</sub> ‡ | LM2902 |                            |                       | LM2902V                    |                       |      | UNIT  |    |
|----------------------------------|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|------------------------|------------------|--------|----------------------------|-----------------------|----------------------------|-----------------------|------|-------|----|
|                                  |                                                                      |                                                                                                    |                        |                  | MIN    | TYP§                       | MAX                   | MIN                        | TYP§                  | MAX  |       |    |
| V <sub>IO</sub>                  | Input offset voltage                                                 | V <sub>CC</sub> = 5 V to MAX,<br>V <sub>IC</sub> = V <sub>ICRmin</sub> ,<br>V <sub>O</sub> = 1.4 V | Non-A-suffix devices   | 25°C             |        | 3                          | 7                     |                            | 3                     | 7    | mV    |    |
|                                  |                                                                      |                                                                                                    |                        | Full range       |        |                            | 10                    |                            | 10                    |      |       |    |
|                                  |                                                                      | A-suffix devices                                                                                   | 25°C                   |                  |        |                            |                       | 1                          | 2                     |      |       |    |
|                                  |                                                                      |                                                                                                    | Full range             |                  |        |                            |                       |                            | 4                     |      |       |    |
| ΔV <sub>IO</sub> /ΔT             | Input offset voltage temperature drift                               | R <sub>S</sub> = 0 Ω                                                                               |                        | Full range       |        |                            |                       |                            | 7                     |      | μV/°C |    |
| I <sub>IO</sub>                  | Input offset current                                                 | V <sub>O</sub> = 1.4 V                                                                             |                        | 25°C             |        | 2                          | 50                    |                            | 2                     | 50   | nA    |    |
|                                  |                                                                      |                                                                                                    |                        | Full range       |        |                            | 300                   |                            | 150                   |      |       |    |
| ΔI <sub>IO</sub> /ΔT             | Input offset current temperature drift                               |                                                                                                    |                        | Full range       |        |                            |                       |                            | 10                    |      | pA/°C |    |
| I <sub>IB</sub>                  | Input bias current                                                   | V <sub>O</sub> = 1.4 V                                                                             |                        | 25°C             |        | –20                        | –250                  |                            | –20                   | –250 | nA    |    |
|                                  |                                                                      |                                                                                                    |                        | Full range       |        |                            | –500                  |                            | –500                  |      |       |    |
| V <sub>ICR</sub>                 | Common-mode input voltage range                                      | V <sub>CC</sub> = 5 V to MAX                                                                       |                        | 25°C             |        | 0 to V <sub>CC</sub> – 1.5 |                       | 0 to V <sub>CC</sub> – 1.5 |                       | V    |       |    |
|                                  |                                                                      |                                                                                                    |                        | Full range       |        | 0 to V <sub>CC</sub> – 2   |                       | 0 to V <sub>CC</sub> – 2   |                       |      |       |    |
| V <sub>OH</sub>                  | High-level output voltage                                            | R <sub>L</sub> = 2 kΩ                                                                              |                        | 25°C             |        |                            |                       |                            |                       | V    |       |    |
|                                  |                                                                      | R <sub>L</sub> = 10 kΩ                                                                             |                        | 25°C             |        |                            | V <sub>CC</sub> – 1.5 |                            | V <sub>CC</sub> – 1.5 |      |       |    |
|                                  |                                                                      | V <sub>CC</sub> = MAX                                                                              | R <sub>L</sub> = 2 kΩ  | Full range       |        | 22                         |                       |                            | 26                    |      |       |    |
|                                  |                                                                      |                                                                                                    | R <sub>L</sub> ≥ 10 kΩ | Full range       |        | 23                         | 24                    |                            | 27                    |      |       |    |
| V <sub>OL</sub>                  | Low-level output voltage                                             | R <sub>L</sub> ≤ 10 kΩ                                                                             |                        | Full range       |        | 5                          | 20                    |                            | 5                     | 20   | mV    |    |
| A <sub>VD</sub>                  | Large-signal differential voltage amplification                      | V <sub>CC</sub> = 15 V, V <sub>O</sub> = 1 V to 11 V,<br>R <sub>L</sub> ≥ 2 kΩ                     |                        | 25°C             |        | 25                         | 100                   |                            | 25                    | 100  | V/mV  |    |
|                                  |                                                                      |                                                                                                    |                        | Full range       |        | 15                         |                       |                            | 15                    |      |       |    |
| CMRR                             | Common-mode rejection ratio                                          | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                              |                        | 25°C             |        | 50                         | 80                    |                            | 60                    | 80   | dB    |    |
| k <sub>SVR</sub>                 | Supply-voltage rejection ratio (ΔV <sub>CC</sub> /ΔV <sub>IO</sub> ) |                                                                                                    |                        | 25°C             |        | 50                         | 100                   |                            | 60                    | 100  | dB    |    |
| V <sub>O1</sub> /V <sub>O2</sub> | Crosstalk attenuation                                                | f = 1 kHz to 20 kHz                                                                                |                        | 25°C             |        |                            | 120                   |                            |                       | 120  | dB    |    |
| I <sub>O</sub>                   | Output current                                                       | V <sub>CC</sub> = 15 V,<br>V <sub>ID</sub> = 1 V,<br>V <sub>O</sub> = 0                            | Source                 | 25°C             |        | –20                        | –30                   | –60                        | –20                   | –30  | –60   | mA |
|                                  |                                                                      |                                                                                                    |                        | Full range       |        | –10                        |                       |                            | –10                   |      |       |    |
|                                  |                                                                      | V <sub>CC</sub> = 15 V,<br>V <sub>ID</sub> = –1 V,<br>V <sub>O</sub> = 15 V                        | Sink                   | 25°C             |        | 10                         | 20                    |                            | 10                    | 20   |       |    |
|                                  |                                                                      |                                                                                                    |                        | Full range       |        | 5                          |                       |                            | 5                     |      |       |    |
|                                  |                                                                      | V <sub>ID</sub> = –1 V, V <sub>O</sub> = 200 mV                                                    |                        | 25°C             |        |                            | 30                    |                            | 12                    | 40   | μA    |    |
| I <sub>OS</sub>                  | Short-circuit output current                                         | V <sub>CC</sub> at 5 V,<br>GND at –5 V                                                             | V <sub>O</sub> = 0,    | 25°C             |        | ±40                        | ±60                   |                            | ±40                   | ±60  | mA    |    |
| I <sub>CC</sub>                  | Supply current (four amplifiers)                                     | V <sub>O</sub> = 2.5 V,                                                                            | No load                | Full range       |        | 0.7                        | 1.2                   |                            | 0.7                   | 1.2  | mA    |    |
|                                  |                                                                      | V <sub>CC</sub> = MAX,<br>V <sub>O</sub> = 0.5 V <sub>CC</sub> ,                                   | No load                | Full range       |        | 1.4                        | 3                     |                            | 1.4                   | 3    |       |    |

† All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise specified. MAX  $V_{CC}$  for testing purposes is 26 V for LM2902 and 32 V for LM2902V.

‡ Full range is  $-40^\circ\text{C}$  to  $125^\circ\text{C}$  for LM2902.

§ All typical values are at  $T_A = 25^\circ\text{C}$ .

# LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V, LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV QUADRUPLE OPERATIONAL AMPLIFIERS

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

electrical characteristics at specified free-air temperature,  $V_{CC} = 5\text{ V}$  (unless otherwise noted)

| PARAMETER                                                                                | TEST CONDITIONS†                                                                                 | T <sub>A</sub> ‡ | LM124A                        |      |      | LM224A                        |      |      | LM324A,<br>LM324KA            |      |      | UNIT |
|------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|------------------|-------------------------------|------|------|-------------------------------|------|------|-------------------------------|------|------|------|
|                                                                                          |                                                                                                  |                  | MIN                           | TYP§ | MAX  | MIN                           | TYP§ | MAX  | MIN                           | TYP§ | MAX  |      |
| V <sub>IO</sub> Input offset voltage                                                     | V <sub>CC</sub> = 5 V to 30 V,<br>V <sub>IC</sub> = V <sub>ICRmin</sub> , V <sub>O</sub> = 1.4 V | 25°C             |                               |      | 2    |                               |      | 2    |                               |      | 3    | mV   |
|                                                                                          |                                                                                                  | Full range       |                               |      | 4    |                               |      | 4    |                               |      | 5    |      |
| I <sub>IO</sub> Input offset current                                                     | V <sub>O</sub> = 1.4 V                                                                           | 25°C             |                               |      | 10   |                               |      | 2    |                               |      | 30   | nA   |
|                                                                                          |                                                                                                  | Full range       |                               |      | 30   |                               |      | 30   |                               |      | 75   |      |
| I <sub>IB</sub> Input bias current                                                       | V <sub>O</sub> = 1.4 V                                                                           | 25°C             |                               |      | –50  |                               |      | –15  |                               |      | –80  | nA   |
|                                                                                          |                                                                                                  | Full range       |                               |      | –100 |                               |      | –100 |                               |      | –200 |      |
| V <sub>ICR</sub> Common-mode input<br>voltage range                                      | V <sub>CC</sub> = 30 V                                                                           | 25°C             | 0 to<br>V <sub>CC</sub> – 1.5 |      |      | 0 to<br>V <sub>CC</sub> – 1.5 |      |      | 0 to<br>V <sub>CC</sub> – 1.5 |      |      | V    |
|                                                                                          |                                                                                                  | Full range       | 0 to<br>V <sub>CC</sub> – 2   |      |      | 0 to<br>V <sub>CC</sub> – 2   |      |      | 0 to<br>V <sub>CC</sub> – 2   |      |      |      |
| V <sub>OH</sub> High-level output voltage                                                | R <sub>L</sub> = 2 kΩ<br>V <sub>CC</sub> = 30 V                                                  | 25°C             |                               |      |      |                               |      |      |                               |      |      | V    |
|                                                                                          |                                                                                                  | Full range       | 26                            |      |      | 26                            |      |      | 26                            |      |      |      |
| V <sub>OL</sub> Low-level output voltage                                                 | R <sub>L</sub> ≤ 10 kΩ<br>V <sub>CC</sub> = 30 V                                                 | Full range       | 27                            |      |      | 27                            |      |      | 27                            |      |      | mV   |
|                                                                                          |                                                                                                  | Full range       |                               |      | 20   |                               |      | 5    |                               |      | 20   |      |
| A <sub>VD</sub> Large-signal differential<br>voltage amplification                       | V <sub>CC</sub> = 15 V, V <sub>O</sub> = 1 V to 11 V,<br>R <sub>L</sub> ≥ 2 kΩ                   | 25°C             | 50                            | 100  |      | 50                            | 100  |      | 25                            | 100  |      | V/mV |
|                                                                                          |                                                                                                  | Full range       | 25                            |      |      | 25                            |      |      | 15                            |      |      |      |
| CMRR Common-mode rejection ratio                                                         | V <sub>IC</sub> = V <sub>ICRmin</sub>                                                            | 25°C             | 70                            |      |      | 70                            | 80   |      | 65                            | 80   |      | dB   |
| k <sub>SVR</sub> Supply-voltage rejection ratio<br>(ΔV <sub>CC</sub> /ΔV <sub>IO</sub> ) |                                                                                                  | 25°C             | 65                            |      |      | 65                            | 100  |      | 65                            | 100  |      | dB   |
| V <sub>O1</sub> /V <sub>O2</sub> Crosstalk attenuation                                   | f = 1 kHz to 20 kHz                                                                              | 25°C             |                               | 120  |      |                               | 120  |      |                               | 120  |      | dB   |
| I <sub>O</sub> Output current                                                            | V <sub>CC</sub> = 15 V,<br>V <sub>ID</sub> = 1 V,<br>V <sub>O</sub> = 0                          | 25°C             | –20                           |      |      | –20                           | –30  | –60  | –20                           | –30  | –60  | mA   |
|                                                                                          |                                                                                                  | Full range       | –10                           |      |      | –10                           |      |      | –10                           |      |      |      |
|                                                                                          | V <sub>CC</sub> = 15 V,<br>V <sub>ID</sub> = –1 V,<br>V <sub>O</sub> = 15 V                      | 25°C             | 10                            |      |      | 10                            | 20   |      | 10                            | 20   |      |      |
|                                                                                          |                                                                                                  | Full range       | 5                             |      |      | 5                             |      |      | 5                             |      |      |      |
| I <sub>OS</sub> Short-circuit output current                                             | V <sub>CC</sub> at 5 V,<br>V <sub>O</sub> = 0                                                    | 25°C             | 12                            |      |      | 12                            | 30   |      | 12                            | 30   |      | μA   |
|                                                                                          |                                                                                                  | Full range       |                               |      | ±60  |                               |      | ±60  |                               |      | ±60  |      |
| I <sub>CC</sub> Supply current<br>(four amplifiers)                                      | V <sub>O</sub> = 2.5 V,<br>V <sub>CC</sub> = 30 V,<br>No load                                    | 25°C             | 0.7                           | 1.2  |      | 0.7                           | 1.2  |      | 0.7                           | 1.2  |      | mA   |
|                                                                                          |                                                                                                  | Full range       | 1.4                           | 3    |      | 1.4                           | 3    |      | 1.4                           | 3    |      |      |

† All characteristics are measured under open-loop conditions, with zero common-mode input voltage, unless otherwise specified.

‡ Full range is –55°C to 125°C for LM124A, –25°C to 85°C for LM224A, and 0°C to 70°C for LM324A.

§ All typical values are at T<sub>A</sub> = 25°C.



**LM124, LM124A, LM224, LM224A, LM324, LM324A, LM2902, LM2902V,  
LM224K, LM224KA, LM324K, LM324KA, LM2902K, LM2902KV, LM2902KAV**  
**QUADRUPLE OPERATIONAL AMPLIFIERS**

SLOS066R – SEPTEMBER 1975 – REVISED JANUARY 2005

operating conditions,  $V_{CC} = \pm 15\text{ V}$ ,  $T_A = 25^\circ\text{C}$

| PARAMETER |                                | TEST CONDITIONS                                                                          | TYP | UNIT                         |
|-----------|--------------------------------|------------------------------------------------------------------------------------------|-----|------------------------------|
| SR        | Slew rate at unity gain        | $R_L = 1\text{ M}\Omega$ , $C_L = 30\text{ pF}$ , $V_I = \pm 10\text{ V}$ (see Figure 1) | 0.5 | $\text{V}/\mu\text{s}$       |
| $B_1$     | Unity-gain bandwidth           | $R_L = 1\text{ M}\Omega$ , $C_L = 20\text{ pF}$ (see Figure 1)                           | 1.2 | MHz                          |
| $V_n$     | Equivalent input noise voltage | $R_S = 100\text{ }\Omega$ , $V_I = 0\text{ V}$ , $f = 1\text{ kHz}$ (see Figure 2)       | 35  | $\text{nV}/\sqrt{\text{Hz}}$ |




Figure 1. Unity-Gain Amplifier




Figure 2. Noise-Test Circuit

**PACKAGING INFORMATION**

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| 5962-7704301VCA  | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| 77043012A        | ACTIVE                | LCCC         | FK              | 20   | 1           | TBD                     | POST-PLATE       | N / A for Pkg Type           |
| 7704301CA        | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| 7704301DA        | ACTIVE                | CFP          | W               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| 77043022A        | ACTIVE                | LCCC         | FK              | 20   | 1           | TBD                     | POST-PLATE       | N / A for Pkg Type           |
| 7704302CA        | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| JM38510/11005BCA | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| LM124AFKB        | ACTIVE                | LCCC         | FK              | 20   | 1           | TBD                     | POST-PLATE       | N / A for Pkg Type           |
| LM124AJ          | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| LM124AJB         | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| LM124D           | ACTIVE                | SOIC         | D               | 14   | 50          | TBD                     | CU NIPDAU        | Level-3-245C-168 HR          |
| LM124DR          | ACTIVE                | SOIC         | D               | 14   | 2500        | TBD                     | CU NIPDAU        | Level-3-245C-168 HR          |
| LM124FKB         | ACTIVE                | LCCC         | FK              | 20   | 1           | TBD                     | POST-PLATE       | N / A for Pkg Type           |
| LM124J           | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| LM124JB          | ACTIVE                | CDIP         | J               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| LM124N           | OBSOLETE              | PDIP         | N               | 14   |             | TBD                     | Call TI          | Call TI                      |
| LM124W           | ACTIVE                | CFP          | W               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| LM124WB          | ACTIVE                | CFP          | W               | 14   | 1           | TBD                     | A42 SNPB         | N / A for Pkg Type           |
| LM224AD          | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224ADE4        | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224ADR         | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224ADRE4       | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224AN          | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM224ANE4        | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM224D           | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224DE4         | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224DG4         | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224DR          | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224DRE4        | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224DRG4        | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224KAD         | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM224KADE4       | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup>               |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|--------------------------------------------|
| LM224KADR        | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM224KADRE4      | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM224KAN         | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM224KANE4       | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM224KD          | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM224KDE4        | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM224KDR         | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM224KDRE4       | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM224KN          | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM224KNE4        | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM224N           | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM2902D          | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902DE4        | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902DG4        | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902DR         | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902DRE4       | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902DRG4       | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KAVQDR     | ACTIVE                | SOIC         | D               | 14   | 1           | Pb-Free (RoHS)          | CU NIPDAU        | Level-2-250C-1 YEAR/<br>Level-1-235C-UNLIM |
| LM2902KAVQPWR    | ACTIVE                | TSSOP        | PW              | 14   | 2000        | TBD                     | CU NIPDAU        | Level-1-250C-UNLIM                         |
| LM2902KD         | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KDB        | ACTIVE                | SSOP         | DB              | 14   | 80          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KDBE4      | ACTIVE                | SSOP         | DB              | 14   | 80          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KDBR       | ACTIVE                | SSOP         | DB              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KDBRE4     | ACTIVE                | SSOP         | DB              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KDE4       | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KDR        | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup>               |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|--------------------------------------------|
| LM2902KDRE4      | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KN         | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM2902KNE4       | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM2902KNSR       | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KNSRE4     | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KPW        | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KPWE4      | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KPWR       | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KPWRE4     | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902KVQDR      | ACTIVE                | SOIC         | D               | 14   | 2500        | Pb-Free (RoHS)          | CU NIPDAU        | Level-2-250C-1 YEAR/<br>Level-1-235C-UNLIM |
| LM2902KVQPWR     | ACTIVE                | TSSOP        | PW              | 14   | 2000        | TBD                     | CU NIPDAU        | Level-1-250C-UNLIM                         |
| LM2902N          | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM2902NE4        | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type                         |
| LM2902NSR        | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902NSRG4      | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902PW         | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902PWE4       | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902PWG4       | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902PWLE       | OBSOLETE              | TSSOP        | PW              | 14   |             | TBD                     | Call TI          | Call TI                                    |
| LM2902PWR        | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902PWRE4      | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902PWRG4      | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM2902QN         | OBSOLETE              | PDIP         | N               | 14   |             | TBD                     | Call TI          | Call TI                                    |
| LM324AD          | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM324ADBLE       | OBSOLETE              | SSOP         | DB              | 14   |             | TBD                     | Call TI          | Call TI                                    |
| LM324ADBR        | ACTIVE                | SSOP         | DB              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM324ADBRE4      | ACTIVE                | SSOP         | DB              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |
| LM324ADE4        | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM                         |

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| no Sb/Br)        |                       |              |                 |      |             |                         |                  |                              |
| LM324ADR         | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324ADRE4       | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324AN          | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM324ANE4        | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM324ANSR        | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324ANSRE4      | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324APW         | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324APWE4       | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324APWG4       | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324APWLE       | OBSOLETE              | TSSOP        | PW              | 14   |             | TBD                     | Call TI          | Call TI                      |
| LM324APWR        | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324APWRE4      | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324APWRG4      | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324D           | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324DE4         | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324DG4         | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324DR          | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324DRE4        | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324DRG4        | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAD         | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KADE4       | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KADG4       | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KADR        | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KADRE4      | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KADRG4      | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAN         | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free                 | CU NIPDAU        | N / A for Pkg Type           |

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| (RoHS)           |                       |              |                 |      |             |                         |                  |                              |
| LM324KANE4       | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM324KANS        | PREVIEW               | SO           | NS              | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KANSR       | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KANSRE4     | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAPW        | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAPWE4      | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAPWG4      | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAPWR       | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAPWRE4     | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KAPWRG4     | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KD          | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KDE4        | ACTIVE                | SOIC         | D               | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KDR         | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KDRE4       | ACTIVE                | SOIC         | D               | 14   | 2500        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KN          | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM324KNE4        | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM324KNS         | PREVIEW               | SO           | NS              | 14   | 50          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KNSR        | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KNSRE4      | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KPW         | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KPWE4       | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KPWR        | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324KPWRE4      | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324N           | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |
| LM324NE4         | ACTIVE                | PDIP         | N               | 14   | 25          | Pb-Free (RoHS)          | CU NIPDAU        | N / A for Pkg Type           |

| Orderable Device | Status <sup>(1)</sup> | Package Type | Package Drawing | Pins | Package Qty | Eco Plan <sup>(2)</sup> | Lead/Ball Finish | MSL Peak Temp <sup>(3)</sup> |
|------------------|-----------------------|--------------|-----------------|------|-------------|-------------------------|------------------|------------------------------|
| LM324NSR         | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324NSRE4       | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324NSRG4       | ACTIVE                | SO           | NS              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324PW          | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324PWE4        | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324PWG4        | ACTIVE                | TSSOP        | PW              | 14   | 90          | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324PWLE        | OBSOLETE              | TSSOP        | PW              | 14   |             | TBD                     | Call TI          | Call TI                      |
| LM324PWR         | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324PWRE4       | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324PWRG4       | ACTIVE                | TSSOP        | PW              | 14   | 2000        | Green (RoHS & no Sb/Br) | CU NIPDAU        | Level-1-260C-UNLIM           |
| LM324Y           | OBSOLETE              | XCEPT        | Y               | 0    |             | TBD                     | Call TI          | Call TI                      |

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.


**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.


J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |




4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.



W (R-GDFP-F14)

CERAMIC DUAL FLATPACK




- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package can be hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only.
  - E. Falls within MIL STD 1835 GDFP1-F14 and JEDEC MO-092AB

FK (S-CQCC-N\*\*)

LEADLESS CERAMIC CHIP CARRIER

28 TERMINAL SHOWN




- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package can be hermetically sealed with a metal lid.
  - D. The terminals are gold plated.
  - E. Falls within JEDEC MS-004


## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE



| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |




4040049/E 12/2002

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.

## D (R-PDSO-G14)

## PLASTIC SMALL-OUTLINE PACKAGE




- NOTES:
- All linear dimensions are in inches (millimeters).
  - This drawing is subject to change without notice.
  - Body dimensions do not include mold flash or protrusion not to exceed 0.006 (0,15).
  - Falls within JEDEC MS-012 variation AB.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN




- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

## DB (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE

28 PINS SHOWN




- NOTES: A. All linear dimensions are in millimeters.  
 B. This drawing is subject to change without notice.  
 C. Body dimensions do not include mold flash or protrusion not to exceed 0,15.  
 D. Falls within JEDEC MO-150

## PW (R-PDSO-G\*\*)

## PLASTIC SMALL-OUTLINE PACKAGE

14 PINS SHOWN



- NOTES:
- All linear dimensions are in millimeters.
  - This drawing is subject to change without notice.
  - Body dimensions do not include mold flash or protrusion not to exceed 0,15.
  - Falls within JEDEC MO-153

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

| <b>Products</b>  |                                                                    | <b>Applications</b> |                                                                          |
|------------------|--------------------------------------------------------------------|---------------------|--------------------------------------------------------------------------|
| Amplifiers       | <a href="http://amplifier.ti.com">amplifier.ti.com</a>             | Audio               | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                   |
| Data Converters  | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>     | Automotive          | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>         |
| DSP              | <a href="http://dsp.ti.com">dsp.ti.com</a>                         | Broadband           | <a href="http://www.ti.com/broadband">www.ti.com/broadband</a>           |
| Interface        | <a href="http://interface.ti.com">interface.ti.com</a>             | Digital Control     | <a href="http://www.ti.com/digitalcontrol">www.ti.com/digitalcontrol</a> |
| Logic            | <a href="http://logic.ti.com">logic.ti.com</a>                     | Military            | <a href="http://www.ti.com/military">www.ti.com/military</a>             |
| Power Mgmt       | <a href="http://power.ti.com">power.ti.com</a>                     | Optical Networking  | <a href="http://www.ti.com/opticalnetwork">www.ti.com/opticalnetwork</a> |
| Microcontrollers | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a> | Security            | <a href="http://www.ti.com/security">www.ti.com/security</a>             |
|                  |                                                                    | Telephony           | <a href="http://www.ti.com/telephony">www.ti.com/telephony</a>           |
|                  |                                                                    | Video & Imaging     | <a href="http://www.ti.com/video">www.ti.com/video</a>                   |
|                  |                                                                    | Wireless            | <a href="http://www.ti.com/wireless">www.ti.com/wireless</a>             |

Mailing Address: Texas Instruments  
Post Office Box 655303 Dallas, Texas 75265

Copyright © 2006, Texas Instruments Incorporated