

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild <a href="general-regarding-numbers-n

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



February 1990 Revised May 2005

MM74HCT573 • MM74HCT574 Octal D-Type Latch • 3-STATE Octal D-Type Flip-Flop

General Description

The MM74HCT573 octal D-type latches and MM74HCT574 octal D-type flip-flop advanced silicon-gate CMOS technology, which provides the inherent benefits of low power consumption and wide power supply range, but are LS-TTL input and output characteristic and pin-out compatible. The 3-STATE outputs are capable of driving 15 LS-TTL loads. All inputs are protected from damage due to static discharge by internal diodes to V_{CC} and ground.

When the MM74HCT573 Latch Enable input is HIGH, the Q outputs will follow the D inputs. When the Latch Enable goes LOW, data at the D inputs will be retained at the outputs until Latch Enable returns HIGH again. When a high logic level is applied to the Output Control input, all outputs go to a high impedance state, regardless of what signals are present at the other inputs and the state of the storage

The MM74HCT574 are positive edge triggered flip-flops. Data at the D inputs, meeting the setup and hold time requirements, are transferred to the Q outputs on positive going transitions of the Clock (CK) input. When a high logic level is applied to the Output Control (OC) input, all outputs go to a high impedance state, regardless of what signals are present at the other inputs and the state of the storage elements

The MM74HCT devices are intended to interface between TTL and NMOS components and standard CMOS devices. These parts are also plug in replacements for LS-TTL devices and can be used to reduce power consumption in existing designs.

Features


- TTL input characteristic compatible
- Typical propagation delay: 18 ns
- Low input current: 1 µA maximum
- \blacksquare Low quiescent current: 80 μA maximum
- Compatible with bus-oriented systems■ Output drive capability: 15 LS-TTL loads

Ordering Codes:


| Order Number | Package Number | Package Description |
|---------------|----------------|---|
| MM74HCT573WM | M20B | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide |
| MM74HCT573SJ | M20D | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide |
| MM74HCT573MTC | MTC20 | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| MM74HCT573N | N20A | 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide |
| MM74HCT574WM | M20B | 20-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-013, 0.300" Wide |
| MM74HCT574SJ | M20D | 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide |
| MM74HCT574MTC | MTC20 | 20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide |
| MM74HCT574N | N20A | 20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide |

Devices also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering code.

Connection Diagrams



Top View MM74HCT573



Top View MM74HCT574

Truth Tables

MM74HCT573

| Output Control | LE | Data | Output |
|-------------------|----|------|--------|
| L | Н | Н | Н |
| L | Н | L | L |
| L | L | Х | Q_0 |
| Н | Х | Х | Z |

H = HIGH Level

L= LOW Level
Q₀ = Level of output before steady-state input conditions were established.
Z = High Impedance State

MM74HCT574

| Output Control | LE | Data | Output |
|-------------------|----------|------|--------|
| L | ↑ | Н | Н |
| L | ↑ | L | L |
| L | L | Х | Q_0 |
| Н | Х | Х | Z |

H = HIGH Level
L = LOW Level
Q₀ = Level of output before steady-state input conditions were established.

Z = High Impedance State

↑ = Transition from LOW-to-HIGH

Absolute Maximum Ratings(Note 1)

(Note 2)

| Supply Voltage (V _{CC}) | -0.5 to +7.0V |
|--|---------------------------|
| DC Input Voltage (V _{IN}) | -1.5 to V_{CC}^+ 1.5V |
| DC Output Voltage (V _{OUT}) | –0.5 to V_{CC}^+ 0.5V |
| Clamp Diode Current (I _{IK} , I _{OK}) | ± 20 mA |
| DC Output Current, per pin (I _{OUT}) | ± 35 mA |
| DC V_{CC} or GND Current, per pin (I_{CC}) | \pm 70 mA |
| Storage Temperature Range (T _{STG}) | -65°C to +150°C |
| Power Dissipation (P _D) | |
| (Note 3) | 600 mW |

(Note 3) S. O. Package only

Lead Temperature (T_L)

(Soldering 10 seconds) 260°C

Recommended Operating Conditions

| | Min | Max | Units |
|---|----------|-----------|---------|
| Supply Voltage (V _{CC}) | 4.5 | 5.5 | V |
| DC Input or Output Voltage | | | |
| (V_{IN}, V_{OUT}) | 0 | V_{CC} | V |
| Operating Temperature Range (T _A) | -40 | +85 | °C |
| Input Rise or Fall Times | | | |
| t_r , t_f | | 500 | ns |
| Note 1: Absolute Maximum Ratings are those | values b | eyond whi | ch dam- |

Note 1: Absolute Maximum Ratings are those values beyond which damage to the device may occur.

Note 2: Unless otherwise specified all voltages are referenced to ground.

Note 3: Power Dissipation temperature derating — plastic "N" package: –
12 mW/°C from 65°C to 85°C.

DC Electrical Characteristics

 $V_{CC} = 5V \pm 10\%$ (unless otherwise specified)

| Symbol | Parameter | Conditions | T _A = 25°C | | $T_A = -40 \text{ to } 85^{\circ}\text{C}$ | T _A = -55 to 125°C | Units |
|-----------------|--------------------|---|-----------------------|-----------------------|--|-------------------------------|-------|
| Зупьог | | Conditions | Тур | | Guaranteed Limits | | |
| V _{IH} | Minimum HIGH Level | | | 2.0 | 2.0 | 2.0 | V |
| | Input Voltage | | | | | | |
| V _{IL} | Maximum LOW Level | | | 0.8 | 0.8 | 0.8 | V |
| | Input Voltage | | | | | | |
| V _{OH} | Minimum HIGH Level | $V_{IN} = V_{IH}$ or V_{IL} | | | | | |
| | Output Voltage | $ I_{OUT} = 20 \mu A$ | V_{CC} | V _{CC} - 0.1 | V _{CC} - 0.1 | V _{CC} - 0.1 | V |
| | | $ I_{OUT} = 6.0 \text{ mA}, V_{CC} = 4.5 \text{V}$ | 4.2 | 3.98 | 3.84 | 3.7 | V |
| | | $ I_{OUT} = 7.2 \text{ mA}, V_{CC} = 5.5V$ | 5.7 | 4.98 | 4.84 | 4.7 | |
| V _{OL} | Maximum LOW Level | $V_{IN} = V_{IH}$ or V_{IL} | | | | | |
| | Voltage | $ I_{OUT} = 20 \mu A$ | 0 | 0.1 | 0.1 | 0.1 | V |
| | | $ I_{OUT} = 6.0 \text{ mA}, V_{CC} = 4.5V$ | 0.2 | 0.26 | 0.33 | 0.4 | V |
| | | $ I_{OUT} = 7.2 \text{ mA}, V_{CC} = 5.5 \text{V}$ | 0.2 | 0.26 | 0.33 | 0.4 | |
| I _{IN} | Maximum Input | $V_{IN} = V_{CC}$ or GND, | | ±0.1 | ±1.0 | ±1.0 | μА |
| | Current | V _{IH} or V _{IL} | | | | | |
| l _{oz} | Maximum 3-STATE | V _{OUT} = V _{CC} or GND | | ±0.5 | ±5.0 | ±10 | μΑ |
| | Output Leakage | Enable = V _{IH} or V _{IL} | | | | | |
| | Current | | | | | | |
| I _{CC} | Maximum Quiescent | $V_{IN} = V_{CC}$ or GND | | 8.0 | 80 | 160 | μА |
| | Supply Current | $I_{OUT} = 0 \mu A$ | | | | | |
| | | V _{IN} = 2.4V or 0.5V (Note 4) | | 1.5 | 1.8 | 2.0 | mA |

500 mW

Note 4: Measured per pin. All others tied to $V_{\rm CC}$ or ground.

AC Electrical Characteristics MM74HCT573

 $V_{CC} = 5.0 V, \, t_r = t_f = 6 \, \, \text{ns}, \, T_A = 25 ^{\circ} \text{C} \, \, \text{(unless otherwise specified)}$

| Symbol | Parameter | Conditions | Тур | Guaranteed Limit | Units |
|------------------|-----------------------------------|------------------------|-----|------------------|-------|
| t _{PHL} | Maximum Propagation Delay | C _L = 45 pF | 17 | 27 | ns |
| t _{PLH} | Data to Output | | | | |
| t _{PHL} | Maximum Propagation Delay | C _L = 45 pF | 16 | 27 | ns |
| t _{PLH} | Latch Enable to Output | | | | |
| t _{PZH} | Maximum Enable Propagation Delay | C _L = 45 pF | 21 | 30 | ns |
| t _{PZL} | Control to Output | $R_L = 1 k\Omega$ | | | |
| t _{PHZ} | Maximum Disable Propagation Delay | C _L = 5 pF | 14 | 23 | ns |
| t _{PLZ} | Control to Output | $R_L = 1 k\Omega$ | | | |
| t _W | Minimum Clock Pulse Width | | | 15 | ns |
| t _S | Minimum Setup Time Data to Clock | | | 5 | ns |
| t _H | Minimum Hold Time Clock to Data | | | 12 | ns |

AC Electrical Characteristics MM74HCT573

 $V_{CC} \! = 5.0 V \pm 10\%, \, t_{f} \! = t_{f} \! = \! 6 \, \text{ns}$ (unless otherwise specified)

| Symbol | Parameter | Conditions | T _A | = 25 ° | $T_A = -40 \text{ to } 85^{\circ}\text{C}$ | T _A = -55 to 125°C | Units |
|------------------|----------------------------------|------------------------|----------------|---------------|--|-------------------------------|-------|
| Syllibol | | Conditions | Тур | | Units | | |
| t _{PHL} | Maximum Propagation | C _L = 50 pF | 18 | 30 | 38 | 45 | ns |
| t _{PLH} | Delay Data to Output | | | | | | |
| t _{PHL} | Maximum Propagation Delay | C _L = 50 pF | 17 | 30 | 44 | 53 | ns |
| t _{PLH} | Latch Enable to Output | | | | | | |
| t _{PZH} | Maximum Enable Propagation | C _L = 50 pF | 22 | 30 | 38 | 45 | ns |
| t _{PZL} | Delay Control to Output | $R_L=1\ k\Omega$ | | | | | |
| t _{PHZ} | Maximum Disable Propagation | C _L = 50 pF | 15 | 30 | 38 | 45 | ns |
| t _{PLZ} | Delay Control to Output | $R_L=1\ k\Omega$ | | | | | |
| t _{THL} | Maximum Output | C _L = 50 pF | 6 | 12 | 15 | 18 | ns |
| t _{TLH} | Rise and Fall Time | | | | | | |
| t _W | Minimum Clock Pulse Width | | | 15 | 20 | 24 | ns |
| t _S | Minimum Setup Time Data to Clock | | -3 | 5 | 6 | 8 | ns |
| t _H | Minimum Hold Time Clock to Data | | 4 | 12 | 15 | 18 | ns |
| C _{IN} | Maximum Input Capacitance | | | 10 | 10 | 10 | pF |
| C _{OUT} | Maximum Output Capacitance | | | 20 | 20 | 20 | pF |
| C _{PD} | Power Dissipation Capacitance | OC = V _{CC} | | 5 | | | pF |
| | (Note 5) | OC = GND | | 52 | | | |

Note 5: C_{PD} determines the no load dynamic power consumption, P_D = C_{PD} V_{CC}2 f+I_{CC} V_{CC}, and the no load dynamic current consumption, I_S = C_{PD} V_{CC} f+I_{CC}.

AC Electrical Characteristics MM74HCT574

 $V_{CC} = 5.0V, t_r = t_f = 6 \text{ ns}, T_A = 25^{\circ}\text{C}$


| Symbol | Parameter | Conditions | Тур | Guaranteed Limit | Units |
|------------------|-----------------------------------|------------------------|-----|------------------|-------|
| f _{MAX} | Maximum Clock Frequency | | 60 | 33 | MHz |
| t _{PHL} | Maximum Propagation Delay | C _L = 45 pF | 17 | 27 | ns |
| t _{PLH} | to Output | | | | |
| t _{PZH} | Maximum Enable Propagation Delay | C _L = 45 pF | 19 | 28 | ns |
| t _{PZL} | Control to Output | $R_L = 1 k\Omega$ | | | |
| t _{PHZ} | Maximum Disable Propagation Delay | C _L = 45 pF | 14 | 25 | ns |
| t_{PLZ} | Control to Output | $R_L = 1 k\Omega$ | | | |
| t _W | Minimum Clock Pulse Width | | | 15 | ns |
| t _S | Minimum Setup Time Data to Clock | | | 12 | ns |
| t _H | Minimum Hold Time Clock to Data | | | 5 | ns |

AC Electrical Characteristics MM74HCT574

 $V_{CC} = 5.0V \pm 10\%$, $t_r = t_f = 6$ ns (unless otherwise specified)

| Symbol | Parameter | Conditions | T _A = 2 | 5°C | $T_A = -40 \text{ to } 85^{\circ}\text{C}$ $T_A = -55 \text{ to } 125^{\circ}\text{C}$ | | Units |
|------------------|----------------------------------|---------------------------|--------------------|-----|--|----------|-------|
| · , | | | Тур | | Guaranteed | l Limits | 0 |
| f _{MAX} | Maximum Clock Frequency | | | 33 | 28 | 23 | MHz |
| t _{PHL} | Maximum Propagation Delay | C _L = 50 pF | 18 | 30 | 38 | 45 | ns |
| t _{PLH} | Clock to Output | | | | | | |
| t _{PZH} | Maximum Enable Propagation | C _L = 50 pF | 22 | 30 | 38 | 45 | ns |
| t_{PZL} | Delay Control to Output | $R_L = 1 \text{ k}\Omega$ | | | | | |
| t _{PHZ} | Maximum Disable Propagation | C _L = 50 pF | 15 | 30 | 38 | 45 | ns |
| t_{PLZ} | Delay Control to Output | $R_L = 1 k\Omega$ | | | | | |
| t _{THL} | Maximum Output | C _L = 50 pF | 6 | 12 | 15 | 18 | ns |
| t _{TLH} | Rise and Fall Time | | | | | | |
| t _W | Minimum Clock Pulse Width | | | 15 | 20 | 24 | ns |
| t _S | Minimum Setup Time Data to Clock | | 6 | 12 | 15 | 18 | ns |
| t _H | Minimum Hold Time Clock to Data | | -1 | 5 | 6 | 8 | ns |
| C _{IN} | Maximum Input Capacitance | | | 10 | 10 | 10 | pF |
| C _{OUT} | Maximum Output Capacitance | | | 20 | 20 | 20 | pF |
| C _{PD} | Power Dissipation Capacitance | $OC = V_{CC}$ | 5 | | | | pF |
| | (Note 6) | OC = GND | 58 | | | | |

Note 6: C_{PD} determines the no load power consumption, $P_D = C_{PD} \ V_{CC}^2 \ f + I_{CC} \ V_{CC}$, and the no load dynamic current consumption, $I_S = C_{PD} \ V_{CC} \ f + I_{CC}$.




Physical Dimensions inches (millimeters) unless otherwise noted (Continued) 12.6±0.10 0.40 TYP --A-5.01 TYP 5.3±0.10 9.27 TYP 7.8 -B-3.9 0.2 C B A ALL LEAD TIPS 10 PIN #1 IDENT.-0.6 TYP 1.27 TYP LAND PATTERN RECOMMENDATION ALL LEAD TIPS SEE DETAIL A 0.1 C 1.8±0.1 -C-L _{0.15±0.05} 0.15-0.25 1.27 TYP 0.35-0.51 ⊕ 0.12 **(** C A DIMENSIONS ARE IN MILLIMETERS GAGE PLANE 0.25 NOTES: A. CONFORMS TO EIAJ EDR-7320 REGISTRATION, ESTABLISHED IN DECEMBER, 1998. B. DIMENSIONS ARE IN MILLIMETERS. C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH, AND TIE BAR EXTRUSIONS. 0.60±0.15 SEATING PLANE 1.25 -M20DRevB1 DETAIL A 20-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide Package Number M20D

Physical Dimensions inches (millimeters) unless otherwise noted (Continued) -0.20 7.72 64 4.4±0.1 -B-32 0.65 PIN #1 IDENT. LAND PATTERN RECOMMENDATION O.1 C ALL LEAD TIPS SEE DETAIL A 0.90+0.15 0.09-0.20 0.65 0.19-0.30 | \$\int 0.10\(0 A R \) 0 \(0 \) **√**12.00° R0.09min GAGE PLANE DIMENSIONS ARE IN MILLIMETERS NOTES: A. CONFORMS TO JEDEC REGISTRATION MD-153, VARIATION AC, REF NOTE 6, DATE 7/93. -0.6±0.1-R0.09min B. DIMENSIONS ARE IN MILLIMETERS. C. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLDS FLASH, AND THE BAR EXTRUSIONS. DETAIL A D. DIMENSIONS AND TOLERANCES PER ANSI Y14.5M, 1982.

MTC20REVD1

20-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide Package Number MTC20



20-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide Package Number N20A

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

- Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
- A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

www.fairchildsemi.com

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative