



Visual Signals STATIC FILAMENT


BEACONS

Industrial Static Filament Beacons > SF125 DIN Base Series

Product overview

These units are identical to Flashing Filament beacons with the exception that they do not operate through an On and Off cycle. When the unit is energised, the light source stays permanently 'On' - often referred to as steady mode. The

main advantage of this type of beacon is that the light can be controlled by a separate source, i.e. a control panel, giving the unit more flexibility. These units are available with either a filament or tungsten halogen lamp. The Din Base series offers the installer the option of a three point fix using external fixing points.



FEATURES

Continuously rated

Suitable for surface mounting

Optional protective guard available - see accessory page

360° visibility

IP65

MATERIAL

UV Stable Polycarbonate Lens

UV Stable ABS Plastic Base



Code No:	Voltage:	Light Source:	Current:
SF125-90	12v Dc ---	Ba15d x 21w	1.75 A
SF125-91	24v Dc ---	Ba15d x 21w	0.88 A
SF125-92	115v Ac ~	Ba15d x 15w	0.13 A
SF125-93	230v Ac ~	Ba15d x 15w	0.07 A

Kg 0.22

50/60 **Hz**

°C -35+66

IP 65

INDUSTRIAL

APPROVAL AND
CONFORMITIES



ADD THE FOLLOWING LENS CODES TO
THE PRODUCT CODE WHEN ORDERING

01

02

03

04

05