








SUGGESTED MATING TAB



- 1 - MATL: 1/2H BRASS OR NICKEL PL STEEL.
- 2 - NO BURRS PERMISSIBLE AT HOLE.
- 3 - MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4 - HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



- 1 CONTINUOUS STRIP ON REELS
- 2 TIN PL 0.002032 [.000080] MIN THK PER MIL-T-10727A
- 3 63606-1 SOLD TO FORD WITH FORD'S P/N ON REELING LABEL.
- 4 SPECIAL PACKAGING
- 5 WIRE SIZE IS 0.8-2.0MM² [18-14] AWG
- 6 INSULATION RANGE IS 4.09-4.98 [.161-.196] DIA.
- 7 FOR LOOSE PIECE PARTS ONLY
- 8 PRE-TIN PLATED
- 9 PREPRODUCTION- FASR REQUIRED
- 10 OBSOLETE

F	4.57 [.180]	4.78 [.188]	F	2.29 [.090]	1.85 [.073]	2.0mm ² [14]
					1.57 [.062]	1.3mm ² [16]
					1.40 [.055]	0.8mm ² [18]
TYPE	WIDTH	STRIP LENGTH ±0.38 [±.015]	TYPE	WIDTH	±0.051 [±.002] HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

10 7	LOOSE PIECE	8	BRASS	9 1-63606-6
10 7	LOOSE PIECE	---	BRASS	9 1-63606-5
7	LOOSE PIECE	2	BRASS	9 1-63606-4
		8	BRASS	9 63606-6
		---	BRASS	63606-5
		2	BRASS	63606-4
		2	#4 PHOS BRONZE	4 63606-3
				63606-2
				63606-1
F2DU14474AA				
FORD P/N	FINISH		MATERIAL	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 2/25/91	TE Connectivity	
DIMENSIONS: MM[INCHES]		CHK MS FEHER 2/25/91		
		APVD J GILLESPIE 2/25/91		
		PRODUCT SPEC		
		APPLICATION SPEC		
		WEIGHT 0.000000		
MATERIAL SEE TABLE	FINISH SEE TABLE	CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 1
			REV M8	