


PLATING SPECIFICATIONS			
	CONTACT		TERMINAL
A	.000015" GOLD		.0001" TIN/LEAD
D	.00003" GOLD		.00003" GOLD OVERALL
G	.00001" GOLD		.000005" GOLD
M	.00003" GOLD		.00001" GOLD OVERALL
N	.00005" GOLD		.0001" TIN/LEAD
O	.00003" GOLD		.0001" TIN/LEAD
P	GOLD FLASH		GOLD FLASH
R	.00002" GOLD		.0001" TIN/LEAD
S	.00001" GOLD		.00001" GOLD OVERALL
T	.0001" TIN/LEAD		.0001" TIN/LEAD OVERALL
V	.00003" GOLD		.000005" GOLD
W	GOLD FLASH		.0001" TIN/LEAD
X	.00003" GOLD		.0001" TIN/LEAD
Y	.00003" GOLD		.000005" GOLD
Z	.00001" GOLD		.0001" TIN/LEAD

PART NUMBER	CONTACT PIN	HEAD LENGTH	TAIL LENGTH
GTC _DABN-M30	ETC-SAB	0.230 [5.84]	0.420 [10.69]
GZC _DABN-M30	EZC-SAB	0.230 [5.84]	0.420 [10.69]
GTC _DFBN-M30	ETC-SFB	0.318 [8.08]	0.400 [10.16]
GZC _DFBN-M30	EZC-SFB	0.318 [8.08]	0.400 [10.16]

PART NUMBER	BODY NUMBER	A
G_C01D_N-M30	H01D-A360	0.100 [2.54]
G_C02D_N-M30	H02D-A360	0.200 [5.08]
G_C03D_N-M30	H03D-A360	0.300 [7.62]
G_C04D_N-M30	H04D-A360	0.400 [10.16]
G_C05D_N-M30	H05D-A360	0.500 [12.70]
G_C06D_N-M30	H06D-A360	0.600 [15.24]
G_C07D_N-M30	H07D-A360	0.700 [17.78]
G_C08D_N-M30	H08D-A360	0.800 [20.32]
G_C09D_N-M30	H09D-A360	0.900 [22.86]
G_C10D_N-M30	H10D-A360	1.000 [25.40]
G_C11D_N-M30	H11D-A360	1.100 [27.94]
G_C12D_N-M30	H12D-A360	1.200 [30.48]
G_C13D_N-M30	H13D-A360	1.300 [33.02]
G_C14D_N-M30	H14D-A360	1.400 [35.56]
G_C15D_N-M30	H15D-A360	1.500 [38.10]
G_C16D_N-M30	H16D-A360	1.600 [40.64]
G_C17D_N-M30	H17D-A360	1.700 [43.18]
G_C18D_N-M30	H18D-A360	1.800 [45.72]
G_C19D_N-M30	H19D-A360	1.900 [48.26]
G_C20D_N-M30	H20D-A360	2.000 [50.80]
G_C21D_N-M30	H21D-A360	2.100 [53.34]
G_C22D_N-M30	H22D-A360	2.200 [55.88]
G_C23D_N-M30	H23D-A360	2.300 [58.42]
G_C24D_N-M30	H24D-A360	2.400 [60.96]
G_C25D_N-M30	H25D-A360	2.500 [63.50]
G_C26D_N-M30	H26D-A360	2.600 [66.04]
G_C27D_N-M30	H27D-A360	2.700 [68.58]
G_C28D_N-M30	H28D-A360	2.800 [71.12]
G_C29D_N-M30	H29D-A360	2.900 [73.66]
G_C30D_N-M30	H30D-A360	3.000 [76.20]
G_C31D_N-M30	H31D-A360	3.100 [78.74]
G_C32D_N-M30	H32D-A360	3.200 [81.28]
G_C33D_N-M30	H33D-A360	3.300 [83.82]
G_C34D_N-M30	H34D-A360	3.400 [86.36]
G_C35D_N-M30	H35D-A360	3.500 [88.90]
G_C36D_N-M30	H36D-A360	3.600 [91.44]



COMPUTER
GENERATED
DOCUMENT DO
NOT CHANGE
MANUALLY

PROPRIETARY AND CONFIDENTIAL

THIS DRAWING AND DESIGN IS THE
PROPERTY OF SULLINS ELECTRONICS
IT MAY NOT BE USED FOR ANY
PURPOSE OTHER THAN BY THE OWNER
SULLINS ELECTRONICS DOES NOT
AUTHORIZE THE REPRODUCTION OR
CONVEYANCE OF ANY INFORMATION
CONTAINED HEREIN.

B	83	CHANGED DIMENSION FROM .150 TO .160		10/24/03	JFW	AJT
A	62	ORIGINAL RELEASE		9/23/03	JFW	AJT
REV.	ECO NO.	DESCRIPTION		DATE	BY	APPV'D
		UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL ± 1/32 ANGULAR ± .1° TWO PLACE DECIMAL ± .02 THREE PLACE DECIMAL ± .005 FOUR PLACE DECIMAL ± .0005 INTERPRET GEOMETRIC TOLERANCING PER:		DRAWN 9/23/03 JWH/ITE CHECKED 9/23/03 AJT	SULLINS ELECTRONICS	
		MATERIAL NOTED FRESH N/A		PART NO./DESCRIPTION: HEADERS G_C _ D _ N-M30		
NEXT ASSY	USED ON	 		SIZE C DWG. NO. 10059	REV B	
APPLICATION		DO NOT SCALE DRAWING		SCALE: 1:1		SHEET 1 OF 1