







NOTES

- 1 CORROSION RESISTANT STEEL ENCLOSURE
2 SWITCH SEALED PER MIL-S-8805, SYMBOL 4
3 CIRCUIT DIAGRAM, DATE CODE, FED. MFG. CODE
AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
4 HARDWARE MAY BE PACKAGED UNASSEMBLED
PER MIL-S-8805

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		
OPERATING FORCE ----- 6-12 LB		CONTACT ARRANGEMENT		
FULL OVERTRAVEL FORCE ----- 30 LB MAX		S P N O		
RELEASE FORCE ----- 4 LB MIN		LOAD	28 VDC	
PRETRAVEL ----- .040 MAX			SEA LEVEL	50,000 FT.
DIFFERENTIAL TRAVEL ----- .020 MAX			RES	4
OVERTRAVEL ----- .250 MIN			IND	2

ELECTRICAL DATA		
CONTACT ARRANGEMENT		
S P N O		
LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	4	4
IND	2	2
MOTOR	4	
LAMP		

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE $\pm$

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/04		
ONE PLACE	X, X	0.41/018	X, X	0.01/003
TWO PLACES	X, XX	0.15/008	X, XX	0.06/010
THREE PLACES			X, XXX	0.13/015
ANGLES				

DESIGN UNITS ☐ SI METRIC ☐

CONCLUSION

WEIGHT 4.5 OZ MAX

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN8-8](#)