

Tous droits strictement réservés. Reproduction ou communication sans autorisation écrite du propriétaire.
interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
© F C I b.v.


Reproduction or issue to third parties in any form
without written authority from the proprietor.
© F C I b.v.

All rights strictly reserved.
whenever is not permitted
without written authority from the proprietor.
© F C I b.v.

PRODUCT NUMBER:
85706-XYZ1LF


HEAT SHRINK VERSION

PRODUCT NO.
85706-X0Z1LF




TERMINAL BLOCK ASS'Y
72377-X1Z1LF

METAL SHIELD
85988-003LF




TERMINAL BLOCK ASS'Y
72377-X2Z1LF

METAL SHIELD
85988-001LF




CRIMPED VERSION


PRODUCT NO.
85706-XYZ1LF



TERMINAL BLOCK ASS'Y
72377-X1Z1LF




OUTER FERRULE
85678-00VLF




INNER FERRULE
85677-00VLF

METAL SHIELD
85988-0W3LF



TERMINAL BLOCK ASS'Y
72377-X2Z1LF

METAL SHIELD
85988-0W2LF



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		FCI	
litr	ecn no	dr	date				projection		www.fciconnect.com	
A	H80084	VW0	971029	linear					title	
B	H80824	VW0	981119						5x6 Shielded	
C	D605-0071	CLu	050402	angles					CABLE CONNECTOR KIT	
D	D605-0438	CLu	051102	dr	H v Woensel	971016	mm		product family	
E	D606-0198	CLu	060526	eng	H v Woensel	971016	scale		Metral(tm)	
				chr	H Cooijmans	980205	1:1		code	
				app	H v Woensel	980205			213	
sheet index	revision	E	E						sheet	
	sheet	1	2						1 of 2	

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Property of FCI b.v.
© FCI b.v.

Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI b.v.
© FCI b.v.

PRODUCT NUMBER:
85706-XYZ1LF

NOTES:

1. SEE APPLICATION SPECIFICATION GES-20-003 FOR INSTRUCTIONS ON WIRE INSERTION AND ASSEMBLY OF COMPONENTS FOR CONNECTORS
2. PLUGS INTO SHIELDED HEADERS 72031, 72032, SHROUDS 72033 AND 72034.
3. MAXIMUM SHEATH DIAMETER: 8 mm.
MAXIMUM DIAMETER OVER BRAID: 6 mm
4. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008 .
5. THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.

MATERIAL:

TERMINAL BLOCKS: GLASS FILLED 612
POLYAMIDE (UL 94 V-0)
CONTACTS:
PHOSPHOR BRONZE
SOLDER FINISH ON IDC DIMPLES

	PART:	INNER FERRULE:	OUTER FERRULE:
Y=1	85988-002LF 85988-003LF 85677-001LF 85678-001LF	ø5.5 mm	ø7.45 mm
Y=3	85988-002LF 85988-003LF 85677-001LF 85991-002LF	ø5.5 mm	ø7.45 mm
Y=2	85988-012LF 85988-013LF 85677-002LF 85678-002LF	ø8 mm	ø10.0 mm
Y=4	85988-012LF 85988-013LF 85677-002LF	ø8 mm	ø10.0 mm

ORDERING INFORMATION FOR KITS:

ORDER KITS 85706-XYZ1LF WHERE
PLATING IN CONTACT AREA:

X=1 FOR 0.8 æm GOLD
X=2 FOR 2.0 æm GOLD
X=3 FOR 1.3 æm GOLD
X=9 FOR 0.8 æm GXT™

LATCH TYPE:

Y=0 HEAT SHRINK VERSION FOR USE WITH LATCH 85991-001LF OR 85992-001LF

Y=3 OVERMOLDED VERSION FOR USE FOR LATCH 85991-002LF

Y>0 CRIMPED VERSION FOR USE WITH LATCH 85991-002LF OR 85992-002LF, SEE TABLE.

COPPER WIRE SIZE:

Z=1 FOR 0.40 - 0.51 mm DIA (26 TO 24 AWG)
Z=2 FOR 0.25 - 0.32 mm DIA (30 TO 28 AWG)

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		FCI www.fciconnect.com			
ltr	ecn	no	dr	date	linear	projection mm		title 5x6 Shielded CABLE CONNECTOR KIT			
E											
					angles	scale 1:1		product family Metral(tm) size dwg no 85706			
					dr	H v Woensel	971016				
					eng	H v Woensel	971016	code 213 sheet 2 of 2			
					chr	H Coojmans	980205				
					app	H v Woensel	980505				
sheet index	revision	sheet									