




TIN LEAD PART NUMBER							
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S90C4GX00	D09S90C6GX00
15	39.14	33.32	25.18	24.54	19.18	D15S90C4GX00	D15S90C6GX00
25	53.03	47.04	39.12	38.25	33.12	D25S90C4GX00	D25S90C6GX00
37	69.32	63.50	55.68	54.71	49.68	D37S90C4GX00	D37S90C6GX00
gold flash						0.76µ gold	

LEAD FREE PART NUMBER							
SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S90C4GX00LF	D09S90C6GX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S90C4GX00LF	D15S90C6GX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S90C4GX00LF	D25S90C6GX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S90C4GX00LF	D37S90C6GX00LF
gold flash						0.76µ gold	

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0001

rev	ecn no	dr	date
C	-	-	1996/07/24
D	LS05-004	MPE	2005/02/10
E	LS06-0097	LGO	2006/07/29
F	LS06-0186	LGO	2006/09/25
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com

surface
ISO 1302 ✓

tolerance std
ISO 406 ISO 1101

projection
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED

ANGULAR
0.X
0.XX
0.XXX

LINEAR
±0.1
±0.1
±0.1

size
A3

Scale
2

ECN
LS06-0186

Product family
D-SUB

Spec ref
-

Dr
Eng
Chr
Appr

PESSON
PESSON
LEGARE
LEGARE

1995/04/27
1995/04/27
1995/04/27
1995/04/27

FCJ

title
straight press-fit

catalog no

Rev.

F

C01-8646-0348

CUSTOMER

sheet 1 of 1