


1907123
Rev. 01
THIS DRAWING IS A CONTROLLED DOCUMENT

USED ON



Left Side

Connector(s): LC-Duplex Secure
Mode: MM
Housing Color: Slate
Geom. Spec: N/A

Fiber Path


A - _____ - Fiber B
B - _____ - Fiber A

Notes:

- 1 Product and Processing must meet requirements of Tyco Electronics Standard 230-702
- 2 Includes dust caps (not shown on print).

Right Side

Connector(s): MT-RJ (No Pins)
Mode: MM
Housing Color: Black
Geom. Spec: 115-1215



VIEW D-D
NOT TO SCALE

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS, INC. IT IS TO BE USED ONLY FOR THE PURPOSES AND IN THE MANNER SPECIFIED HEREIN. IT MAY NOT BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA 17105-3608.

LOC
CE
DIST
16


CAC Customer Layout Rev: D

	A	Rev Per EC#	RELEASE	7/28/2008	-	JD			
P	LTR	REVISION RECORD		DATE	DN	APVD			

DIMENSIONS:
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 P.L.C. ± .
1 P.L.C. ± .
2 P.L.C. ± .
3 P.L.C. ± .
4 P.L.C. ± .

Restricted To:

DWG Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Joe Davis		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Joe Davis					
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to MT-RJ (No Pins)					
SCALE	SIZE	DRAWING NO	SHEET		REV
NTS	A2	C- 1907123	1 of 4		A

8

7

6

5

4

3

2

1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE PURPOSES AND IN THE MANNER SPECIFIED HEREIN. IT IS NOT TO BE DISCLOSED TO ANY OTHER PERSON OR ENTITY WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Slate		MT-RJ (No Pins), Black	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
0-1907123-1	0.950 - 1.050	3.11 - 3.44	0.5	-	0.5	20
0-1907123-2	1.950 - 2.050	6.39 - 6.72	0.5	-	0.5	20
0-1907123-3	2.950 - 3.050	9.67 - 10.00	0.5	-	0.5	20
0-1907123-4	3.920 - 4.080	12.86 - 13.38	0.51	-	0.51	20
0-1907123-5	4.920 - 5.080	16.14 - 16.66	0.51	-	0.51	20
0-1907123-6	5.920 - 6.080	19.42 - 19.94	0.51	-	0.51	20
0-1907123-7	6.920 - 7.080	22.70 - 23.22	0.51	-	0.51	20
0-1907123-8	7.920 - 8.080	25.98 - 26.50	0.51	-	0.51	20
0-1907123-9	8.850 - 9.150	29.03 - 30.01	0.51	-	0.51	20
1-1907123-0	9.850 - 10.150	32.31 - 33.30	0.52	-	0.52	20
1-1907123-1	10.850 - 11.150	35.59 - 36.58	0.52	-	0.52	20
1-1907123-2	11.850 - 12.150	38.87 - 39.86	0.52	-	0.52	20
1-1907123-3	12.850 - 13.150	42.15 - 43.14	0.52	-	0.52	20
1-1907123-4	13.850 - 14.150	45.43 - 46.42	0.52	-	0.52	20
1-1907123-5	14.850 - 15.150	48.72 - 49.70	0.52	-	0.52	20
1-1907123-6	15.840 - 16.160	51.96 - 53.01	0.52	-	0.52	20
1-1907123-7	16.830 - 17.170	55.21 - 56.33	0.53	-	0.53	20
1-1907123-8	17.820 - 18.180	58.46 - 59.64	0.53	-	0.53	20
1-1907123-9	18.810 - 19.190	61.71 - 62.95	0.53	-	0.53	20
2-1907123-0	19.800 - 20.200	64.96 - 66.27	0.53	-	0.53	20
2-1907123-1	20.790 - 21.210	68.20 - 69.58	0.53	-	0.53	20
2-1907123-2	21.780 - 22.220	71.45 - 72.90	0.53	-	0.53	20
2-1907123-3	22.770 - 23.230	74.70 - 76.21	0.53	-	0.53	20
2-1907123-4	23.760 - 24.240	77.95 - 79.52	0.54	-	0.54	20
2-1907123-5	24.750 - 25.250	81.20 - 82.84	0.54	-	0.54	20
2-1907123-6	25.740 - 26.260	84.44 - 86.15	0.54	-	0.54	20
2-1907123-7	26.730 - 27.270	87.69 - 89.46	0.54	-	0.54	20
2-1907123-8	27.720 - 28.280	90.94 - 92.78	0.54	-	0.54	20
2-1907123-9	28.710 - 29.290	94.19 - 96.09	0.54	-	0.54	20
3-1907123-0	29.700 - 30.300	97.44 - 99.40	0.55	-	0.55	20
3-1907123-1	30.690 - 31.310	100.68 - 102.72	0.55	-	0.55	20
3-1907123-2	31.680 - 32.320	103.93 - 106.03	0.55	-	0.55	20
3-1907123-3	32.670 - 33.330	107.18 - 109.35	0.55	-	0.55	20
3-1907123-4	33.660 - 34.340	110.43 - 112.66	0.55	-	0.55	20
3-1907123-5	34.650 - 35.350	113.68 - 115.97	0.55	-	0.55	20
3-1907123-6	35.640 - 36.360	116.92 - 119.29	0.55	-	0.55	20
3-1907123-7	36.630 - 37.370	120.17 - 122.60	0.56	-	0.56	20
3-1907123-8	37.620 - 38.380	123.42 - 125.91	0.56	-	0.56	20
3-1907123-9	38.610 - 39.390	126.67 - 129.23	0.56	-	0.56	20
4-1907123-0	39.600 - 40.400	129.92 - 132.54	0.56	-	0.56	20
4-1907123-1	40.590 - 41.410	133.16 - 135.85	0.56	-	0.56	20
4-1907123-2	41.580 - 42.420	136.41 - 139.17	0.56	-	0.56	20

Qty	U of M	Description	Item No.
2	piece	LC Connector Assy, 1.6mm-2.0mm, MM	14
1	piece	LC Duplex clip, black	13
1	piece	MT-RJ, SPRING PUSH, UNIVERSAL	12
AR	meter	2 fiber, 50/125, 1.8mm, Twinzip, Orange, OFNP (Plenum)	11
1	piece	PIN KEEPER, 3.8MM	10
2	piece	Trace Label	9
1	piece	CRIMP EYELET, MT-RJ	8
1	piece	HOUSING, CONN, MT-RJ, BLACK	7
1	piece	SPRING, MT-RJ, 3.8 DESIGN	6
2	piece	LC, SC, FC Straight Boot, Beige	5
2	piece	Eyelet/Shrink tube assembly - White	4
1	piece	DUST COVER, MT-RJ	3
1	piece	MT-RJ FERRULE, THERMOPLAST, MM	2
1	piece	MT-RJ TwinZip Bend Limiting Boot, Beige	1

DIMENSIONS: meters	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 P.L.C. ± . 1 P.L.C. ± . 2 P.L.C. ± . 3 P.L.C. ± . 4 P.L.C. ± .

Restricted To:

DIN Cable Assy Configurator		MATERIAL -	HEAT TREAT -	
CHK Joe Davis				
APVD Joe Davis				
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to MT-RJ (No Pins)				
SCALE NTS	SIZE A2	DRAWING NO C- 1907123	SHEET 2 of 4	REV A

8 7 6 5 4 3 2 1

DAG NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

Part #	L (meters)	L (feet)	LC-Duplex Secure, Slate		MT-RJ (No Pins), Black	
			IL (dB)	RL (dB)	IL (dB)	RL (dB)
4-1907123-3	42.570 - 43.430	139.66 - 142.48	0.56	-	0.56	20
4-1907123-4	43.560 - 44.440	142.91 - 145.80	0.57	-	0.57	20
4-1907123-5	44.550 - 45.450	146.16 - 149.11	0.57	-	0.57	20
4-1907123-6	45.540 - 46.460	149.40 - 152.42	0.57	-	0.57	20
4-1907123-7	46.530 - 47.470	152.65 - 155.74	0.57	-	0.57	20
4-1907123-8	47.520 - 48.480	155.90 - 159.05	0.57	-	0.57	20
4-1907123-9	48.510 - 49.490	159.15 - 162.36	0.57	-	0.57	20
5-1907123-0	49.500 - 50.500	162.40 - 165.68	0.58	-	0.58	20
5-1907123-1	50.490 - 51.510	165.64 - 168.99	0.58	-	0.58	20
5-1907123-2	51.480 - 52.520	168.89 - 172.30	0.58	-	0.58	20
5-1907123-3	52.470 - 53.530	172.14 - 175.62	0.58	-	0.58	20
5-1907123-4	53.460 - 54.540	175.39 - 178.93	0.58	-	0.58	20
5-1907123-5	54.450 - 55.550	178.64 - 182.25	0.58	-	0.58	20
5-1907123-6	55.440 - 56.560	181.88 - 185.56	0.58	-	0.58	20
5-1907123-7	56.430 - 57.570	185.13 - 188.87	0.59	-	0.59	20
5-1907123-8	57.420 - 58.580	188.38 - 192.19	0.59	-	0.59	20
5-1907123-9	58.410 - 59.590	191.63 - 195.50	0.59	-	0.59	20
6-1907123-0	59.400 - 60.600	194.88 - 198.81	0.59	-	0.59	20
6-1907123-1	60.390 - 61.610	198.12 - 202.13	0.59	-	0.59	20
6-1907123-2	61.380 - 62.620	201.37 - 205.44	0.59	-	0.59	20
6-1907123-3	62.370 - 63.630	204.62 - 208.75	0.59	-	0.59	20
6-1907123-4	63.360 - 64.640	207.87 - 212.07	0.6	-	0.6	20
6-1907123-5	64.350 - 65.650	211.12 - 215.38	0.6	-	0.6	20
6-1907123-6	65.340 - 66.660	214.37 - 218.70	0.6	-	0.6	20
6-1907123-7	66.330 - 67.670	217.61 - 222.01	0.6	-	0.6	20
6-1907123-8	67.320 - 68.680	220.86 - 225.32	0.6	-	0.6	20
6-1907123-9	68.310 - 69.690	224.11 - 228.64	0.6	-	0.6	20
7-1907123-0	69.300 - 70.700	227.36 - 231.95	0.61	-	0.61	20
7-1907123-1	70.290 - 71.710	230.61 - 235.26	0.61	-	0.61	20
7-1907123-2	71.280 - 72.720	233.85 - 238.58	0.61	-	0.61	20
7-1907123-3	72.270 - 73.730	237.10 - 241.89	0.61	-	0.61	20
7-1907123-4	73.260 - 74.740	240.35 - 245.20	0.61	-	0.61	20
7-1907123-5	74.250 - 75.750	243.60 - 248.52	0.61	-	0.61	20
7-1907123-6	75.240 - 76.760	246.85 - 251.83	0.61	-	0.61	20
7-1907123-7	76.230 - 77.770	250.09 - 255.15	0.62	-	0.62	20
7-1907123-8	77.220 - 78.780	253.34 - 258.46	0.62	-	0.62	20
7-1907123-9	78.210 - 79.790	256.59 - 261.77	0.62	-	0.62	20
8-1907123-0	79.200 - 80.800	259.84 - 265.09	0.62	-	0.62	20

	A	Rev Per EC#	RELEASE	7/28/2008	-	JE	
P	LTR	REVISION RECORD			DATE	DIN	AP

DIMENSIONS;
meters

TOLERANCES UNLESS OTHERWISE SPECIFIED		
0 PLC	±	—
1 PLC	±	—
2 PLC	±	—
3 PLC	±	—
4 PLC	±	—

Restricted To:

Q1 Cable Assy Configurator		MATERIAL -		HEAT TREAT -	
CHK Joe Davis		 Tyco Electronics, Inc. Harrisburg, PA 17105-3608			
APVD Joe Davis					
NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex Secure to MT-RJ (No Pins)					
SCALE NTS	SIZE A2	DRAWING NO C- 1907123	SHEET 3 of 4	REV A	

D

C

3

A

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION. IT MAY NOT BE DISCLOSED TO ANY OTHERS WITHOUT THE WRITTEN AUTHORIZATION OF TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA.

THIS DRAWING IS A CONTROLLED DOCUMENT.

LOC
CE
DIST
16

CAC Customer Layout Rev: D

8

7

6

5

4

3

2

1

Label 1

Per specification 107-1645-1



Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.

Label 2

Per specification 107-1645-1




Trace # - Bar Code

Trace # - Human Readable

Part Number

Country of Origin

This label is used on all lengths on this drawing.



DIMENSIONS:
meters

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 P.L.C.
1 P.L.C.
2 P.L.C.
3 P.L.C.
4 P.L.C.

±
±
±
±
±

DIN Cable Assy Configurator

OK Joe Davis

APVD Joe Davis

NAME FO C/A - 2 fiber, 50/125, OFNP (Plenum) jacket, LC-Duplex
Secure to MT-RJ (No Pins)

SCALE
NTS

SIZE
A2

DRAWING NO
C- 1907123

SHEET
4 of 4

REV
A

MATERIAL HEAT TREAT

AMP Tyco Electronics, Inc.
Harrisburg, PA 17105-3608

Restricted To:

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[250961-3](#)