

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [84732-0005](#)
Status: **Active**
Overview: [Sealed Industrial USB Solutions](#)
Description: Sealed Industrial USB Type A Plug-to-Sealed Industrial USB Type B Plug Double Ended Cord Set, 5.0m Length

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	84732
Assembly Configuration	Dual Ended Connectors
Comments	Fully shielded for EMI/RFI protection
Connector to Connector	USB Type A-to-Pigtail
Overview	Sealed Industrial USB Solutions
Product Name	Industrial USB
UPC	822348749362

Physical

Cable Length	5.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Plug
Lock to Mating Part	None
Material - Resin	PVC
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Single Ended	No
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP67, NEMA 6P
Wire Insulation Diameter	3.5mm (.14")
Wire Size AWG	N/A
Wire/Cable Type	USB

Electrical

Current - Maximum per Contact	1A
Impedance	Non-constant
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC (RMS)

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-84732-001
---------------	--------------



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[84732Series](#)

Mates With

84729 Sealed Industrial USB 2.0 Type A
Panel Mount Receptacle to Sealed Industrial
USB 2.0 Type A Plug Cordset . [84730-0001](#)
Sealed Industrial USB 2.0 Type B Panel
Mount PCB Receptacle

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[84732-0005](#)