





REV.	DATE	DESCRIPTION
A	04/28/97	CHANGE GOLD PLATING SPEC.
B	03/08/08	UPDATE DRAWING FORMAT, ADD CRIMP NOTES



RECOMMENDED CABLE
STRIPPING DIM'S



NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE .255"
2. CRIMPED CONTACT HEX CRIMP SIZE .042" OR SOLDER.

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
7						DRAWN	G.R.S.	03/08/08						
6						CHECKED			PART DESCRIPTION BNC CRIMP PLUG (FOR RG-59/U 20AWG – VPM2000 CABLE-75ohm)					
5						ISSUED								
4	FERRULE	BRASS	NICKEL	1		SHEET	1 OF 1			PART NO. 112956				
3	CONTACT PIN	BRASS	GOLD	1										
2	INSULATOR	TEFLON	NATURAL	1				DWG. NO. 112956.DWG						
1	BODY	BRASS	NICKEL	1										
DESCRIPTION		MATERIAL	FINISH	QTY	CAD FILE C:/112/112956.DWG			REV. B		SIZE A		SCALE NA		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[112956](#)