

0338	0378	6002	7009
0338-0-15-XX-15-XX-10-0 Solder mount in .057 min. mounting hole Also available on 12mm wide carrier tape: 3,600 parts per 13" reel. Order as: 0338-0-58-XX-15-XX-10-0	0378-0-15-XX-15-XX-10-0 Solder mount in .082 min. mounting hole	6002-0-19-XX-15-XX-10-0 Solder mount in .059 min. mounting hole	7009-0-19-XX-15-XX-10-0 Press-fit in .063 mounting hole

0339			
0339-0-15-XX-15-XX-10-0 Solder mount in .057 min. mounting hole			

--	--	--	--

SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2°	ORDER CODE: XXXX - X - 1X - XX - 15 - XX - 10 - 0 BASIC PART # → SPECIFY SHELL FINISH: → 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL 15 10μ" GOLD OVER NICKEL SPECIFY CONTACT FINISH: → 01 200μ" TIN/LEAD OVER NICKEL 80 200μ" TIN OVER NICKEL 27 30μ" GOLD OVER NICKEL CONTACT → #15 CONTACT (DATA ON PAGE 220)
--	---