

Peli Products Table of Cases

CASE	Weight w/ foam	Weight w/o foam	Temp. min. °C	Temp. max °C	Bouyancy Kg. Max	INTERNAL DIMEN.			EXTERNAL DIMEN.			Depth in Cm.		Colours				Units Master.	PanelFra.	Extras
						Length	Width	Height	Length	Width	Height	Lid	Case	Black	Silver	Orange	Yellow			
1120	0,56	0,53	-23	99	3,2	18,7	12,4	7,7	20,9	16,6	9	1,3	6,5	B		O	Y	6	N	-
1150	0,9	0,8	-23	99	2,7	21,2	14,9	9,3	23,5	19,2	11,1	1,9	7,4	B	S		Y	6	Y	-
1200	1,3	1,2	-23	99	3,6	23,8	18,4	10,3	27	24,6	12,3	3	7,4	B	S	O		6	Y	-
1300	1,6	1,4	-23	99	5,4	23,8	18,4	15,5	27	24,6	17,4	3	12,5	B	S	O		4	Y	-
1400	2	1,8	-23	99	9,1	30,5	23	13,1	34	29,5	15,2	3	10,2	B	S	O		4	Y	-
1420	-	1,72	-23	99	9,07	33	12,7	25,4	38,1	21,6	26,6	2,7	22,5	B	-	-	-	-	-	-
1450	2,9	2,5	-23	99	11,3	37,6	26,3	15,2	40,6	33	17,4	4,4	10,8	B	S	O		4	Y	Dividers
1470WF	1,95	1,72	-23	99	9,07	40	26,8	9,5	42,4	33,2	11,1	3,5	6	B				4	N	-
1470NF	-	1,72	-23	99	9,07	40	26,8	9,5	42,4	33,2	11,1	3,5	6	B				4	N	-
1470CC1	3	-	-23	99	9,07	40	26,8	9,5	42,4	33,2	11,1	3,5	6	B				4	N	Lid&Tray
1470AC	2,95	-	-23	99	9,07	40	26,8	9,5	42,4	33,2	11,1	3,5	6	B				4	N	Lid
1470CC2	3,04	-	-23	99	9,07	40	26,8	9,5	42,4	33,2	11,1	3,5	6	B				4	N	Lid&Foam
1490WF	2,72	2,27	-23	99	9,07	45,4	29,2	10,5	49,4	35,4	11,9	3,8	6,6	B				4	N	-
1490NF	-	2,27	-23	99	9,07	45,4	29,2	10,5	49,4	35,4	11,9	3,8	6,6	B				4	N	-
1490CC1	3,63	-	-23	99	9,07	45,4	29,2	10,5	49,4	35,4	11,9	3,8	6,6	B				4	N	Lid & Tray
1490AC	3,63	-	-23	99	9,07	45,4	29,2	10,5	49,4	35,4	11,9	3,8	6,6	B				4	N	Lid
1490CC2	3,63	-	-23	99	9,07	45,4	29,2	10,5	49,4	35,4	11,9	3,8	6,6	B			4	N	Lid & Foam	
1500	3,2	2,9	-23	99	18,1	43,2	29	15,5	47	35,7	17,6	4,6	11	B	S	O		4	Y	Div.Lid/Pho/Att.
1520	3,9	3,6	-23	99	18,1	45,4	32,4	17,1	48,6	39,2	19,2	4,6	12,5	B	S	O		2	Y	Dividers
1550	5,4	4,8	-23	99	20,4	48,1	36,7	19,7	52,5	43,6	21,7	4,6	15	B	S	O		2	Y	Dividers
1600	6,4	-	-23	99	25	55,2	42,7	20	61,6	49,4	22	4,6	15,5	B	S	O		2	N	Dividers
1610 **	10,2	9,07	-23	99	45	56,3	43,5	26,9	62,4	49	30,3	5,2	21,6	B				2	N	Dividers
1620 **	11,8	11,1	-23	99	45	56	43,2	32	63	49,2	35,2	5,2	26,6	B	S			2	N	Dividers
1650 **	10,4	8,2	-23	99	45,4	73,6	45,4	26,7	82,5	52	28,7	4,7	21,9	B				1	N	Div.Lid Organ.
1700 **	7,7	-	-23	99	20,4	91	35,1	13,3	96,8	45,2	15,5	4,4	8,9	B				1	N	-
1750 **	11,6	-	-23	99	25	128,3	34,1	13,3	134,6	44,3	15,4	4,4	8,9	B				1	N	-

Peli Products Table of Cases

** With Whells		
	Materials	Test Specifications
Case	Copolymer Polypropylene Structural Resin	MIL STANDARD MIL-C-4150-J
Latches	ABS	
O' Ring	Neoprene Sponge	Air Transportation Association Spec. 300
Pins	Stainless Steel	
Foam	Polyester	IP 67 in accordance EN60529/91 & IEC60529/89
Purge Valve	ABS - Stainless Steel - Neoprene	

Peli Products, S.A. C/ Passeig de Gràcia, 54 7º C -08007 Barcelona - SPAIN
Phone: +34 93 467 49 99/ Fax: +34 93 487 73 93 / e-mail: info@peli.com / www.peli.com