




PRODUCT NUMBER
SEE TABLE





mat'l. code		surface	tolerance	projection	product family
ISO 1302		ISO 1302	ISO 406	ISO 1101	QUICKIE
ltr	ecr	n	dr	date	tolerances unless otherwise specified
H	N05-0123	ZC	5/9/05		angles
J	N07-0151	WG	8/02/07		linear
K	SLX-N-012098	J.Z	2012-07-04	$\pm 2^\circ$	
dr	M. CLOUSER	7/11/90			
enr	M. SMYK	7/11/90			
chr	M. SMYK	8/21/91			
app	M. SMYK	8/21/91			
sheet	revision	K	K	K	K
index	sheet	1	2	3	4
		5	6	7	8
		9	10		

title	product family
HEADER, QUICKIE, SLIM LINE	QUICKIE
VERTICAL, 4-WALL	
dwg no	sheet of 10 size
88880	A3
type	Product Customer Drawing

PRODUCT NUMBER
SEE TABLE

HEADER STYLE



RECOMMENDED BOARD LAYOUT

NOTES:

1. SAME POSITION TOLERANCE APPLIES TO BOTH ENDS OF PINS.
2. MOLDING MATERIAL: GLASS-FILLED POLYESTER, FLAME RETARDANT PER UL 94 V-0, COLOR: BLACK.
3. 1° MAX. DRAFT PERMISSIBLE ON ALL SURFACES.
4. 3 LBS./1.36 KG MIN. TERMINAL PULL-OUT FORCE.
5. TERMINAL MATERIAL: PHOSPHORUS BRONZE.
6. TO DETERMINE DIMENSIONS:
N = NUMBER OF POSITIONS PER ROW
7. SEE 68751 FOR LATCHES.
8. PART NUMBERS WITH "R" FOLLOWING THE PART NUMBER (EXAMPLE 66506-326 R) HAS RETENTION. (ONLY PARTS WITH .105, .120, AND .150 ROUND OR SQUARE TAILS CAN HAVE RETENTION.) LOCATION IS MANUFACTURERS OPTION.
FOR CONNECTORS:
RETENTIVE LEG APPLICABLE TO TAIL LENGTHS .125/3.18 MAX.
5LB/2.3KG MAX INSERTION FORCE AND .25LB/1KG MIN RETENTION FORCE
PER RETENTIVE PIN USING .062/1.57 THICK CIRCUIT BOARD AND RECOMMENDED HOLE PATTERN. RETENTIVE LOCATION AT THE DISCRETION OF THE MANUFACTURER. RETENTION PIN MAY BE SHIFTED TO NEXT POSITION.
9. PART NUMBERS WITH "T" FOLLOWING PART NUMBER (EXAMPLE 66506-068 T IS PACKED IN TUBES.) (CALL PRODUCT MANAGER FOR AVAILABILITY.)
10. MAY BE ORDERED WITH "G" PACK PACKAGING BY ADDING "G" TO DASH NUMBER.
11. UNDER PLATING: 50μ"/1.27μm Ni.
12. ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION & PART NUMBERS WITH "LF" SUFFIX ADDED IN THE TABLE ARE LEAD FREE.
13. IF "LF" P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
14. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES IF THEY ARE AVAILABLE.
15. "THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKER GROWTH IN ALL INTERCONNECT ENVIRONMENTS."
16. PLATING OPTIONS:
PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT ON CONTACT OR TAIL, OPTIONALLY TIN ON TAIL.

mat'l. code		surface	tolerance	projection	product family
		ISO 1302	ISO 406 ISO 1101		QUICKIE
l	tr	ec	n	o	d
K		date	tolerances unless otherwise specified		title
			angles	INCH/MM	HEADER, QUICKIE, SLIM LINE
			linear	scale 1:1	VERTICAL, 4-WALL
			±2°		
		dr	M. CLOUSER	7/11/90	dwg no
		engr	M. SMYK	7/11/90	shee 2 of 10
		chr	M. SMYK	8/21/91	size
		appd	M. SMYK	8/21/91	A3
sheet		revision			type Product Customer Drawing
index	sheet				



Copyright FCI

1		2		3		4		5		6	
PRODUCT NO.		SIZE	STYLE	DIM C	DIM J	PIN PLATING		PLASTIC MATERIAL			
NOTE 8 & 9											
88880-001		2 X 5	B	. 400/10. 16	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni		NOTE 2			
-002					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-003					. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-004					. 105/2. 67	150u"/3. 81u TIN					
-005					. 150/3. 81	150u"/3. 81u TIN					
-006		2 X 5	B	. 400/10. 16	. 675/17. 15	150u"/3. 81u TIN					
-007		2 X 10	D	. 900/22. 86	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-008					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-009					. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-010					. 105/2. 67	150u"/3. 81u TIN					
-011					. 150/3. 81	150u"/3. 81u TIN					
-012		2 X 10		. 900/22. 86	. 675/17. 15	150u"/3. 81u TIN					
-013		2 X 13		1. 200/30. 48	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-014					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-015					. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-016					. 105/2. 67	150u"/3. 81u TIN					
-017					. 150/3. 81	150u"/3. 81u TIN					
-018		2 X 13		1. 200/30. 48	. 675/17. 15	150u"/3. 81u TIN					
-019		2 X 17		1. 600/40. 64	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-020					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-021					. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-022					. 105/2. 67	150u"/3. 81u TIN					
-023					. 150/3. 81	150u"/3. 81u TIN					
-024		2 X 17		1. 600/40. 64	. 675/17. 15	150u"/3. 81u TIN					
-025		2 X 20		1. 900/48. 26	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-026					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-027					. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-028					. 105/2. 67	150u"/3. 81u TIN					
-029					. 150/3. 81	150u"/3. 81u TIN					
-030		2 X 20		1. 900/48. 26	. 675/17. 15	150u"/3. 81u TIN					
-031		2 X 25		2. 400/60. 96	. 105/2. 67	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-032					. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-033					. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni					
-034					. 105/2. 67	150u"/3. 81u TIN					
88880-035		2 X 25	D	2. 400/60. 96	. 150/3. 81	150u"/3. 81u TIN		NOTE 2			

FCIconnect.com

FCI

mat'l. code		surface		tolerance		projection		product family	
ISO 1302		ISO 406		ISO 1101				QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		angles		INCH/MM		title	
K		linear		±2°		scale 1:1		HEADER, QUICKIE, SLIM LINE	
		dr		M. CLOUSER		7/11/90		dwg no	
		engr		M. SMYK		7/11/90		88880	
		chr		M. SMYK		8/21/91		A3	
		appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet index		revision sheet							

Form A3

1

2

3

4

5

6

PDS: Rev :K

STATUS: Released

Printed: Jul 10, 2012



FCIconnect.com

Copyright FCI

D

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
NOTE 8 & 9						
88880-036	2 X 25	D	2. 400/60. 96	. 675/17. 15	150u" /3. 81u TIN	NOTE 2
-037	2 X 7	C	. 600/15. 24	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-038				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-039				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-040				. 105/2. 67	150u" /3. 81u TIN	
-041				. 150/3. 81	150u" /3. 81u TIN	
-042	2 X 7	C	. 600/15. 24	. 675/17. 15	150u" /3. 81u TIN	
-043	2 X 8	D	. 700/17. 78	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-044				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-045				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-046				. 105/2. 67	150u" /3. 81u TIN	
-047				. 150/3. 81	150u" /3. 81u TIN	
-048	2 X 8	D	. 700/17. 78	. 675/17. 15	150u" /3. 81u TIN	
-049	2 X 5	B	. 400/10. 16	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-050	2 X 10	D	. 900/22. 86			
-051	2 X 13		1. 200/30. 48			
-052	2 X 17		1. 600/40. 64			
-053	2 X 20		1. 900/48. 26			
-054	2 X 25	D	2. 400/60. 96			
-055	2 X 7	C	. 600/15. 24			
-056	2 X 8	D	. 700/17. 78	. 150/3. 81		
-057	2 X 30		2. 900/73. 66	. 105/2. 67		
-058				. 150/3. 81		
-059				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-060				. 105/2. 67	150u" /3. 81u TIN	
-061				. 150/3. 81	150u" /3. 81u TIN	
-062				. 675/17. 15	150u" /3. 81u TIN	
-063				. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-064				. 150/3. 81		
-065	2 X 30	D	2. 900/73. 66	. 675/17. 15		
-066	2 X 5	B	. 400/10. 16	. 105/2. 67		
-067	2 X 5	B	. 400/10. 16	. 675/17. 15		
-068	2 X 7	C	. 600/15. 24	. 105/2. 67		
-069	2 X 7	C	. 600/15. 24	. 675/17. 15		
88880-070	2 X 8	D	. 700/17. 78	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 1st angle		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2"		scale 1:1		dwg no 88880	
		dir		M. CLOUSER		7/11/90		shee# of 10 size A3	
		engr		M. SMYK		7/11/90			
		chr		M. SMYK		8/21/91			
		appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet index		revision sheet							

1

2 3

4

5

6

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING		PLASTIC MATERIAL
88880-071	2 X 8	D	. 700/17. 78	. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni		NOTE 2
-072	2 X 10		. 900/22. 86	. 105/2. 67			
-073	2 X 10		. 900/22. 86	. 675/17. 15			
-074	2 X 13		1. 200/30. 48	. 105/2. 67			
-075	2 X 13		1. 200/30. 48	. 675/17. 15			
-076	2 X 17		1. 600/40. 64	. 105/2. 67			
-077	2 X 17		1. 600/40. 64	. 675/17. 15			
-078	2 X 20		1. 900/48. 26	. 105/2. 67			
-079	2 X 20		1. 900/48. 26	. 675/17. 15			
-080	2 X 25		2. 400/60. 96	. 105/2. 67			
-081	2 X 25	D	2. 400/60. 96	. 675/17. 15	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni		
-082	2 X 5	B	. 400/10. 16	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni		
-083	2 X 5	B	. 400/10. 16	. 150/3. 81			
-084	2 X 5	B	. 400/10. 16	. 675/17. 15			
-085	2 X 7	C	. 600/15. 24	. 105/2. 67			
-086	2 X 7	C	. 600/15. 24	. 150/3. 81			
-087	2 X 7	C	. 600/15. 24	. 675/17. 15			
-088	2 X 8	D	. 700/17. 78	. 105/2. 67			
-089	2 X 8		. 700/17. 78	. 150/3. 81			
-090	2 X 8		. 700/17. 78	. 675/17. 15			
-091	2 X 10		. 900/22. 86	. 105/2. 67			
-092	2 X 10		. 900/22. 86	. 150/3. 81			
-093	2 X 10		. 900/22. 86	. 675/17. 15			
-094	2 X 13		1. 200/30. 48	. 105/2. 67			
-095	2 X 13		1. 200/30. 48	. 150/3. 81			
-096	2 X 13		1. 200/30. 48	. 675/17. 15			
-097	2 X 17		1. 600/40. 64	. 105/2. 67			
-098	2 X 17		1. 600/40. 64	. 150/3. 81			
-099	2 X 17		1. 600/40. 64	. 675/17. 15			
-100	2 X 20		1. 900/48. 26	. 105/2. 67			
-101	2 X 20		1. 900/48. 26	. 150/3. 81			
-102	2 X 20		1. 900/48. 26	. 675/17. 15			
-103	2 X 25		2. 400/60. 96	. 105/2. 67			
-104	2 X 25		2. 400/60. 96	. 150/3. 81			
88880-105	2 X 25	D	2. 400/60. 96	. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni		NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection ⊕ ↖		product family QUICKIE	
ltr ecn nodr		date		tolerances unless otherwise specified		INCH/MM		title	
K				angles	linear			HEADER, QUICKIE, SLIM LINE	
				±2°				VERTICAL, 4-WALL	
				dr	M. CLOUSER	7/11/90			dwg no
				engr	M. SMYK	7/11/90			shee 5 of 10
				chr	M. SMYK	8/21/91			size
				appd	M. SMYK	8/21/91			A3
sheet index		revision sheet						type Product Customer Drawing	

1

2 3

4

5

6

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-106	2 X 30	D	2. 900/73. 66	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
-107	2 X 30	D	2. 900/73. 66	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-108	2 X 30	D	2. 900/73. 66	. 675/17. 15	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-109	2 X 5	B	. 400/10. 16	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-110				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-111				. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-112				. 105/2. 67	150u" /3. 81u TIN	
-113				. 150/3. 81	150u" /3. 81u TIN	
-114				. 675/17. 15	150u" /3. 81u TIN	
-115				. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-116				. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-117				. 675/17. 15	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-118				. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-119				. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
88880-120	2 X 5	B	. 400/10. 16	. 675/17. 15	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
88880-121	DISCONTINUED					
THRU						
88880-216						
88880-217	2 X 12	D	1. 100/27. 94	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
-218					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-219					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-220				. 105/2. 67	150u" /3. 81u TIN	
-221				. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-222					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-223					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-224				. 150/3. 81	150u" /3. 81u TIN	
-225				. 675/17. 15	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-226					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-227					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-228	2 X 12		1. 100/27. 94	. 675/17. 15	150u" /3. 81u TIN	
-229	2 X 15		1. 400/35. 56	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-230					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-231					30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-232				. 105/2. 67	150u" /3. 81u TIN	
88880-233	2 X 15	D	1. 400/35. 56	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nldr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2°		scale 1:1		dwg no 88880	
		dir M. CLOUSER		7/11/90				shee 6 of 10 size A3	
		engr M. SMYK		7/11/90					
		chr M. SMYK		8/21/91					
		appd M. SMYK		8/21/91				type Product Customer Drawing	
sheet index		revision sheet							



FCIconnect.com

Copyright FCI

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-234	2 X 15	D	1. 400/35. 56	. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
-235				. 150/3. 81	30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-236				. 150/3. 81	150u"/3. 81u TIN	
-237				. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-238					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-239					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-240	2 X 15		1. 400/35. 56	. 675/17. 15	150u"/3. 81u TIN	
-241	2 X 22		2. 100/53. 34	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-242					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-243					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-244				. 105/2. 67	150u"/3. 81u TIN	
-245				. 150/3. 81	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-246					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-247					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-248				. 150/3. 81	150u"/3. 81u TIN	
-249				. 675/17. 15	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-250					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-251					30u"/0. 76u MIN (NOTE 16) OVER 50u"/1. 27u Ni	
-252	2 X 22					
88880-253	2 X 17	D	1. 600/40. 64	. 105/2. 67	15u"/0. 38u MIN (NOTE 16) OVER 50u"/1. 27u Ni	NOTE 2
88880-254	UNAVAILABLE					
THRU						
88880-279	UNAVAILABLE					
88880-280	2 X 10	D	. 900/22. 86	. 105/2. 67	150u"/3. 81u TIN	NOTE 2
88880-281	UNAVAILABLE					
THRU						
88880-306						

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2"		scale 1:1		dwg no 88880	
		dr		M. CLOUSER		7/11/90		shee 7 of 10 size A3	
		engr		M. SMYK		7/11/90			
		chr		M. SMYK		8/21/91			
		appd		M. SMYK		8/21/91		type Product Customer Drawing	
sheet index		revision sheet							

PRODUCT NO. NOTE 8 & 9	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-307	2 X 5	B	. 400/10. 16	. 097/2. 46	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2
-308	2 X 5	B	. 400/10. 16			
-309	2 X 7	C	. 600/15. 24			
-310	2 X 8	D	. 700/17. 78			
-311	2 X 10		. 900/22. 86			
-312	2 X 12		1. 100/27. 94			
-313	2 X 13		1. 200/30. 48			
-314	2 X 15		1. 400/35. 56			
-315	2 X 17		1. 600/40. 64			
-316	2 X 20		1. 900/48. 26			
-317	2 X 22		2. 100/53. 34			
-318	2 X 25		2. 400/60. 96			
-319	2 X 30		2. 900/73. 66	. 097/2. 46		
-320	2 X 8		. 700/17. 78	. 105/2. 67		
-321	2 X 25		2. 400/60. 96		30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-322	2 X 8		. 700/17. 78		50u" /1. 27u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-323	2 X 17		1. 600/40. 64	. 105/2. 67	50u" /1. 27u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-324	2 X 25		2. 400/60. 96	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-325	2 X 25		2. 400/60. 96	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-326	2 X 10		. 900/22. 86	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-327	2 X 17		1. 600/40. 64	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-328	2 X 25		2. 400/60. 96	. 120/3. 05	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-329	2 X 13		1. 200/30. 48	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-330	2 X 25		2. 400/60. 96		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-331	2 X 30		2. 900/73. 66		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-332	2 X 17		1. 600/40. 64		15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-333	2 X 20		1. 900/48. 26	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-334	2 X 10		. 900/22. 86	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-335	2 X 20		1. 900/48. 26	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-336	2 X 22	D	2. 100/53. 34	. 105/2. 67	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-337	2 X 12	D	1. 100/27. 94	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-338	2 X 5	B	. 400/10. 16	. 150/3. 81	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
-339	2 X 4	B	. 300/7. 62	. 105/2. 67	15u" /0. 38u MIN (NOTE 16) OVER 50u" /1. 27u Ni	
88880-340	2 X 10	D	. 900/22. 86	. 150/3. 81	30u" /0. 76u MIN (NOTE 16) OVER 50u" /1. 27u Ni	NOTE 2

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family QUICKIE	
ltr ecn nodr date		tolerances unless otherwise specified		linear		INCH/MM		title HEADER, QUICKIE, SLIM LINE VERTICAL, 4-WALL	
K		angles		±2°		scale 1:1		dwg no 88880	
		dr M. CLOUSER		7/11/90				shee 8 of 10 size A3	
		engr M. SMYK		7/11/90					
		chr M. SMYK		8/21/91					
		appd M. SMYK		8/21/91				type Product Customer Drawing	
sheet index		revision sheet							



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL
88880-341	2 X 17	D	1.600/40.64	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-342	2 X 10	D	.900/22.86	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-343	2 X 17	D	1.600/40.64	.150/3.81	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-344	U N A S S I G N E D					
-345	2 X 20	D	1.900/48.26	.120/3.05	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-346	U N A S S I G N E D					
-347	U N A S S I G N E D					
-348	2 X 5	B	.400/10.16	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-349	2 X 7	C	.600/15.24			
-350	2 X 8	D	.700/17.78			
-351	2 X 10		.900/22.86			
-352	2 X 13		1.200/30.48			
-353	2 X 17		1.600/40.64			
-354	2 X 20		1.900/48.26			
-355	2 X 22		2.100/53.34			
-356	2 X 25		2.400/60.96			
-357	2 X 30		2.900/73.66	.105/2.67	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-358	2 X 10		.900/22.86	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-359	2 X 17		1.600/40.64	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	
-360	2 X 12	D	1.100/27.94	.295/7.49	15u"/0.38u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-361	U N A S S I G N E D					
-362	2 X 5	B	.400/10.16	.105/2.67	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2
-363	2 X 8	D	.700/17.78			
-364	2 X 10	D	.900/22.86			
-365	2 X 15	D	1.400/35.56			
-366	2 X 17	D	1.600/40.64	.105/2.67		
-367	2 X 5	B	.400/10.16	.150/3.81		
-368	2 X 17	D	1.600/40.64	.150/3.81		
88880-369	2 X 25	D	2.400/60.96	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2

mat'l. code				surface ☒ tolerance ☐		projection		product family			
				ISO 1302 ☒ ISO 406 ☐ ISO 1101 ☐				QUICKIE			
l		tr		ec		n		d		r	
K											
date				tolerances unless otherwise specified							
				angles		linear		INCH/MM		title	
						XXX±.01/XXX.03				HEADER, QUICKIE, SLIM LINE	
						XXX±.005/XXX.013				VERTICAL, 4-WALL	
				±2"		XXX±.0020/XXX±0.051		scale 1:1			
dr		M. CLOUSER		7/11/90				dwg no		sheet 9 of 10	
engr		M. SMYK		7/11/90				88880		A3	
chr		M. SMYK		8/21/91							
appd		M. SMYK		8/21/91				type		Product Customer Drawing	
sheet		revision									
index		sheet									



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	STYLE	DIM C	DIM J	PIN PLATING	PLASTIC MATERIAL	POLARIZED PIN
88880-404	2 X 20	D	1.900/48.26	.120/3.05	15μ/0.38μ MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2	20
↑ -410	2 X 25	↑	2.400/60.96	↑	↑	↑	—
↑ -418	2 X 10	↑	.900/22.86	↑	↑	↑	14
↑ -423	2 X 25	↓	2.400/60.96	↑	↑	↑	25
↑ -426	2 X 17	D	1.600/40.64	↓	↓	↓	3
88880-427	2 X 5	B	.400/10.16	.120/3.05	15μ/0.38μ MIN (NOTE 16) OVER 50u"/1.27u Ni	↓	1
88880-428	2 X 5	B	.400/10.16	.150/3.81	30u"/0.76u MIN (NOTE 16) OVER 50u"/1.27u Ni	NOTE 2	10

mat'l. code				surface ☒ tolerance ☐		projection ☐		product family			
				ISO 1302 ☒ ISO 406 ☐ ISO 1101 ☐				QUICKIE			
l		tr		ec		n		d		title	
K										HEADER, QUICKIE, SLIM LINE	
										VERTICAL, 4-WALL	
										scale 1:1	
										dwg no	
										sheet 10 of 10	
										88880	
										A3	
										type Product Customer Drawing	
sheet		revision									
index		sheet									