


ISDN S Interface Hybrid APC8866D

ELECTRICAL SPECIFICATIONS @25° C OPERATING TEMPERATURE 0° TO +70° C


Turns Ratio ±5%	Primary Inductance mH min	Leakage Inductance	Primary Xfmr DCR $\Omega \pm 20\%$		Secondary Xfmr DCR $\Omega \pm 20\%$		Secondary Total DCR $\Omega \pm 20\%$		Choke	
			TX	RX	TX	RX	Pins 1 - 3	Pins 4 - 6	Inductance per line mH nom	DCR per line $\Omega \pm 20\%$
1CT : 2.5	20	12.5	1.2	1.8	2.62	3.33	127	10.2K	0.05	0.6

NOTE: ISOLATION PRI:SEC
4200 Vrms IEC60950/EN60950 QUALIFIED (REINFORCED)

SCHEMATIC



MECHANICAL



ALL DIMENSIONS IN INCHES [MM].
TOLERANCE ± 0.2 MM UNLESS OTHERWISE STATED.
PIN DIAMETER 0.75MM MAX

©2003 Bel Fuse Inc. Specifications subject to change without notice. 11.06.03

CORPORATE

Bel Fuse Inc.
206 Van Vorst Street
Jersey City, NJ 07302
Tel 201-432-0463
Fax 201-432-9542
www.belfuse.com

FAR EAST

Bel Fuse Ltd.
8F / 8 Luk Hop Street
San Po Kong
Kowloon, Hong Kong
Tel 852-2328-5515
Fax 852-2352-3706
www.belfuse.com

EUROPE

Bel Stewart Connector
45/46 Riverside
Medway City Estate
Rochester, Kent ME2 4DP U.K.
Tel 44-1634-722890
Fax 44-1634-716677
www.belfuse.com