

OBSOLETE
Contact us for replacement model




FEATURES

- HIGH ISOLATION - 3000V RATING
- 8000V ISOLATION TEST VOLTAGE
- BARRIER 100% PRODUCTION TESTED
- LOW BARRIER CAPACITANCE - 10PF
- LOW LEAKAGE CURRENT - 2µA MAX
- INTERNAL FILTERING

APPLICATIONS

- BIOMEDICAL DATA ACQUISITION
- INDUSTRIAL PROCESS CONTROL
- ANALYTICAL MEASUREMENTS
- GROUND LOOP ELIMINATION
- INTRINSIC SAFETY SYSTEMS

MECHANICAL



ELECTRICAL SPECIFICATIONS

Specifications typical at $T_A = +25^{\circ}\text{C}$, nominal input voltage, rated output current unless otherwise noted.

MODEL	NOMINAL INPUT VOLTAGE (V _{DC})	RATED OUTPUT VOLTAGE (V _{DC})	RATED OUTPUT CURRENT (mA)	INPUT CURRENT		EFFICIENCY (%)
				NO LOAD (mA)	RATED LOAD (mA)	
HB04U05S05Q	5	5	800	60	1000	80
HB04U05S12Q	5	12	333	60	1000	80
HB04U05S15Q	5	15	267	60	1000	80
HB04U12S05Q	12	5	800	25	380	87
HB04U12S12Q	12	12	333	25	380	87
HB04U12S15Q	12	15	267	25	380	87
HB04U15S05Q	15	5	800	20	310	87
HB04U15S12Q	15	12	333	20	310	87
HB04U15S15Q	15	15	267	20	310	87
HB04U05D05Q	5	±5	±400	60	944	85
HB04U05D12Q	5	±12	±167	60	944	85
HB04U05D15Q	5	±15	±134	60	944	85
HB04U12D05Q	12	±5	±400	25	375	88
HB04U12D12Q	12	±12	±167	25	375	88
HB04U12D15Q	12	±15	±134	25	375	88
HB04U15D05Q	15	±5	±400	20	300	88
HB04U15D12Q	15	±12	±167	20	300	88
HB04U15D15Q	15	±15	±134	20	300	88

Note: Other input to output voltage options may be available. Please consult factory.

Models with strikethrough have been discontinued.

COMMON SPECIFICATIONS

Specifications typical at $T_A = +25^{\circ}\text{C}$, nominal input voltage, rated output current unless otherwise noted.

PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
INPUT					
Voltage Range		4.5 10.8 13.5	5 12 15	5.5 13.2 16.5	V _{DC}
Reflected Ripple Current			35 ¹		mAp-p
ISOLATION					
Rated Voltage		3000			V _{DC}
Test Voltage	60 Hz, 10 Seconds	8000			V _{pk}
Resistance			10		GΩ
Capacitance			10		pF
Leakage Current	V _{ISO} = 240V _{AC} , 60Hz		1.2	2	μArms
OUTPUT					
Rated Power			4		W
Voltage Setpoint Accuracy			±3	±5	%
Temperature Coefficient			±0.02		%/°C
Ripple & Noise	BW = DC to 10MHz		100		mVp-p
BW = 10Hz to 2MHz			20		mVrms
Line Regulation	High Line to Low Line		±1.5		%/% V _{in}
Load Regulation	See performance curves				
GENERAL					
Switching Frequency			100		kHz
Package Weight			22		g
MTTF per MIL-HDBK-217, Rev. E	Circuit Stress Method		200,000		Hr
Ground Benign	T _A = +25°C				
TEMPERATURE					
Specification		-25		+70	°C
Operation		-40		+85	°C
Storage		-40		+110	°C

1. Reflected ripple current is measured at 50% load with a 33μF capacitor across the input of the UUT.

THROUGH-HOLE SOLDERING INFORMATION

These devices are intended for wave soldering or manual soldering.

They are not intended to be subject to surface mount processes under any circumstances.

The normal wave soldering process can be used with these devices where the device is subjected to a maximum wave temperature of 260°C for a period of no more than 10 seconds. Within this time and temperature range, the integrity of the device's plastic body will not be compromised and internal temperatures within the converter will not exceed 175°C. Care should be taken to control manual soldering limits identical to that of wave soldering.








ABSOLUTE MAXIMUM RATINGS

Internal Power Dissipation.....1W
Short Circuit Duration.....Momentary
Lead Temperature (soldering, 10 seconds max).....+300°C

ORDERING INFORMATION

Device Family HB04U xyzz Q
HB04U Indicates DC/DC Converter
Model Number _____
Where:
xx = Input Voltage
y = Number of Outputs (Single "S", Dual "D")
zz = Output Voltage
Package Option _____

TYPICAL PERFORMANCE CURVES



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Murata:

[HB04U12S12Q](#) [HB04U05D12Q](#) [HB04U05D15Q](#) [HB04U15D12Q](#) [HB04U12D12Q](#) [HB04U15S12Q](#) [HB04U15S05Q](#)
[HB04U12D05Q](#) [HB04U05S12Q](#) [HB04U05S15Q](#) [HB04U15D05Q](#) [HB04U15D15Q](#) [HB04U12D15Q](#) [HB04U15S15Q](#)
[HB04U05D05Q](#) [HB04U05S05Q](#) [HB04U12S15Q](#) [HB04U12S05Q](#)