



CURRENT REGULATOR DIODES

Qualified per MIL-PRF-19500/463

<u>Qualified Levels:</u> JAN, JANTX, JANTXV and JANS

DESCRIPTION

The popular 1N5283-1 thru 1N5314-1 series of 0.5 watt current regulators provides a selection from 0.22 mA to 4.7 mA in standard 10% tolerances. These devices regulate current over a broad voltage range as a counter part offering to Zeners (that regulate voltage over a broad current range) in similar size axial-leaded packages. The somewhat larger DO-7 packaging option offers a double-plug internal bond connection with a larger active die element for its unique function as a current limiter. Microsemi also offers numerous other Zener products to meet higher and lower power voltage regulation applications.

Important: For the latest information, visit our website http://www.microsemi.com.

FEATURES

- JEDEC registered 1N5283 thru 1N5314.
- High source impedance.
- Internal metallurgical bond.
- JAN, JANTX, JANTXV, and JANS qualifications are available per MIL-PRF-19500/463.
- Chips also available as JANHC and JANKC.
- RoHS compliant versions available (commercial grade only).

APPLICATIONS / BENEFITS

- Double-plug construction.
- Regulates current over a broad operating voltage and temperature range.
- Extensive selection from 0.22 mA to 4.7 mA.
- Standard current tolerances are plus/minus 10%.
- Flexible axial-lead mounting terminals.
- Non-sensitive to ESD.
- Inherently radiation hard as described in Microsemi "MicroNote 050".

MAXIMUM RATINGS

Parameters/Test Conditions	Symbol	Value	Unit
Junction and Storage Temperature	T _J and T _{STG}	-65 to +175	°C
Thermal Resistance Junction-to-Lead @ L = .375 in	R _{OJL}	250	°C/W
Thermal Impedance	$Z_{\Theta JX}$	25	°C/W
Steady-State Power Dissipation @ T _L = +50 °C, L = 3/8" (1)	P_D	500	mW
Working Peak Voltage	V_{WM}	100	V
Solder Pad Temperature @ 10 s max.	T _{SP}	260	°C

Notes: 1. Derate at 4mW/°C above +50°C.

DO-7 Package

Also available in:

DO-213AB Package (surface mount)

1N5283UR-1 to 1N5314UR-1

MSC – Lawrence 6 Lake Street,

Lawrence, MA 01841 Tel: 1-800-446-1158 or (978) 620-2600 Fax: (978) 689-0803

MSC - Ireland

Gort Road Business Park, Ennis, Co. Clare, Ireland Tel: +353 (0) 65 6840044 Fax: +353 (0) 65 6822298

Website:


www.microsemi.com



MECHANICAL and PACKAGING

- CASE: Hermetically sealed glass case.
- TERMINALS: Tin/lead finished copper clad steel or RoHS compliant matte-tin finish available (commercial grade only).
- MARKING: Part number and cathode band.
- POLARITY: Diode to be operated with the banded (cathode) end negative.
- TAPE & REEL option: Standard per EIA-296 (add "TR" suffix to part number). Consult factory for quantities.
- WEIGHT: 0.2 grams.
- See Package Dimensions on last page.

PART NOMENCLATURE



SYMBOLS & DEFINITIONS					
Symbol	Definition				
IL	Limiting Current: A specified current below the lower knee of the current-regulating characteristic.				
Is	Regulator current: A current within the regulating range of a current-regulator diode.				
P_D	Power Dissipation: The power dissipation, dc.				
R _{OJL}	Thermal Resistance Junction-to-Lead: The thermal resistance from the virtual junction(s) of a semiconducter device to the lead.				
TL	Lead Temperature: The temperature of a lead terminal.				
T _{SP}	Temperature Solder Pad: The maximum solder temperature that can be safely applied to the terminal.				
V _K	Knee Voltage: A specified regulator voltage near the lower knee of the current-regulating characteristic.				
V _L	Limiting Voltage: The voltage at point I _L on the current-voltage characteristic.				
Vs	Regulator Voltage: A voltage within the regulating range of a current-regulating diode.				
Z _k	Knee Impedance: The small-signal impedance at operating point VK on the current-voltage characteristic.				
Zs	Regulator Impedance: The small-signal impedance within the regulating range of a current-regulator diode.				
$Z_{\Theta JX}$	Thermal Impedance: The thermal impedance junction to reference point.				



ELECTRICAL CHARACTERISTICS (T_A = 25°C, unless otherwise specified)

TYPE NUMBER	REGULATOR CURRENT IS (mA) @ VS = 25 V			MINIMUM DYNAMIC IMPEDANCE @VS = 25 V $z_S (M\Omega)$	MINIMUM KNEE IMPEDANCE @VK = 6.0 V zk (MΩ)	MAXIMUM LIMITING VOLTAGE @ IL = 0.8 IS (min) VL (Volts)
	NOM	MIN	MAX	(Note 1)	(Note 2)	VE (VORS)
1N5283	0.22	0.198	0.242	25.00	2.750	1.00
1N5284	0.24	0.216	0.264	19.00	2.350	1.00
1N5285	0.27	0.243	0.297	14.00	1.950	1.00
1N5286	0.30	0.270	0.330	9.000	1.600	1.00
1N5287	0.33	0.297	0.363	6.600	1.350	1.00
1N5288	0.39	0.351	0.429	4.100	1.000	1.05
1N5289	0.43	0.387	0.473	3.300	0.870	1.05
1N5290	0.47	0.423	0.517	2.700	0.750	1.05
1N5291	0.56	0.504	0.616	1.900	0.560	1.10
1N5292	0.62	0.558	0.682	1.550	0.470	1.13
1N5293	0.68	0.612	0.748	1.350	0.400	1.15
1N5294	0.75	0.675	0.825	1.150	0.335	1.20
1N5295	0.82	0.738	0.902	1.000	0.290	1.25
1N5296	0.91	0.819	1.001	0.880	0.240	1.29
1N5297	1.00	0.900	1.100	0.800	0.205	1.35
1N5298	1.10	0.990	1.210	0.700	0.180	1.40
1N5299	1.20	1.080	1.320	0.640	0.155	1.45
1N5300	1.30	1.170	1.430	0.580	0.135	1.50
1N5301	1.40	1.260	1.540	0.540	0.115	1.55
1N5302	1.50	1.350	1.650	0.510	0.105	1.60
1N5303	1.60	1.440	1.760	0.475	0.092	1.65
1N5304	1.80	1.620	1.980	0.420	0.074	1.75
1N5305	2.00	1.800	2.200	0.395	0.061	1.85
1N5306	2.20	1.980	2.420	0.370	0.052	1.95
1N5307	2.40	2.160	2.640	0.345	0.044	2.00
1N5308	2.70	2.430	2.970	0.320	0.035	2.15
1N5309	3.00	2.700	3.300	0.300	0.029	2.25
1N5310	3.30	2.970	3.630	0.280	0.024	2.35
1N5311	3.60	3.240	3.960	0.265	0.020	2.50
1N5312	3.90	3.510	4.290	0.255	0.017	2.60
1N5313 1N5314	4.30 4.70	3.870 4.230	4.730 5.170	0.245 0.235	0.014 0.012	2.75 2.90

NOTE 1: z_s is derived by superimposing a 90 Hz RMS signal equal to 10% of V_S on V_S . **NOTE 2:** z_k is derived by superimposing a 90 Hz RMS signal equal to 10% of V_K on V_K .



GRAPHS




FIGURE 1 – CURRENT-REGULATOR CHARACTERISTICS




FIGURE 2 – TEMPERATURE COEFFICIENT



GRAPHS (continued)




FIGURE 3 – TEMPERATURE COEFFICIENT





FIGURE 4 – CURRENT REGULATION FACTOR



PACKAGE DIMENSIONS



	Dimensions				
Symbol	Inch		Millimeters		
	Min	Max	Min	Max	
BD	.060	.107	1.52	2.72	
BL	.120	.300	3.05	7.62	
LD	.018	.023	0.46	0.58	
LL	1.000	1.500	25.40	38.10	
LL ₁		0.050		1.27	

NOTES:

- 1. Dimensions are in inches.
- 2. Millimeters are given for general information only.
- 3. The minimum body diameter shall be maintained over .15 inch (3.81 mm) inch of body length.
- 4. The specified lead diameter applies in the zone between .050 inch (1.27 mm) and the end of the lead. Outside of this zone the lead diameter shall not exceed LD.
- 5. Both leads shall be within the specified dimension.
- 6. See 3.3 for L and T_L definitions.
- 7. In accordance with ASME Y14.5M, diameters are equivalent to Φx symbology.