

REVISION R

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:	TITLE:	DWG NO:
ONE PLACE DECIMALS $\pm .1$	THREE PLACE DECIMALS $\pm .005$		ANGLES $\pm 2^\circ$	.100 x .100 C.L. DOUBLE ROW SURFACE MOUNT SOCKET ASSEMBLY	SSF-1XX-XX-XX-D-XX
TWO PLACE DECIMALS $\pm .01$	FOUR PLACE DECIMALS $\pm .0020$				SHEET 1 OF 1






FIGURE 1
-02



SECT. "A"-"A"
(IN-PROCESS VIEW)

SSF-1XX-XX-XX-D-XX

No. OF POSITIONS PER ROW

LEAD STYLE

-02 THRU 36

-01: THROUGH HOLE (SEE FIG.2)
(USE C-44-01-XX)

-02 SURFACE MOUNT (SEE FIG.1)
(USE C-44-02-XX)

-L1: THROUGH HOLE (SEE FIG.2)
(USE C-61-01-XX)

-L2 SURFACE MOUNT (SEE FIG.1)
(USE C-61-02-XX)

OPTION

LEAVE BLANK FOR NO OPTION

-LC: LOCKING CLIP (USE 2 LC-05-TM SEE NOTE 4)
(N/A ON LEAD STYLES -01 OR -L1)

ROW SPECIFICATION

-D: DOUBLE

PLATING SPECIFICATION

-L: 10μ" SELECTIVE GOLD IN CONTACT AREA,
MATTE TIN ON TAIL (USE C-XX-XX-L)

-S: 30μ" SELECTIVE GOLD IN CONTACT AREA,
MATTE TIN ON TAIL (USE C-XX-XX-S)


-F: 3μ" SELECTIVE GOLD IN CONTACT AREA,
MATTE TIN ON TAIL (USE C-XX-XX-F)

-LM: 10μ" SELECTIVE GOLD IN CONTACT AREA,
MATTE TIN ON TAIL (USE C-XX-XX-L)


-SM: 30μ" SELECTIVE GOLD IN CONTACT AREA,
MATTE TIN ON TAIL (USE C-XX-XX-S)

-FM: 3μ" SELECTIVE GOLD IN CONTACT AREA,
MATTE TIN ON TAIL (USE C-XX-XX-F)

PACKAGING



PT-01-24-01-09



PT-1-24-03-09

OPTIONS	PACKAGING TUBE	PLUG
-X1	PT-1-24-03-09	TP-03
-X2, -X2-LC	PT-1-24-01-09	TP-24







FIGURE 2
-01

DIFFERENT AS SHOWN,
OTHERWISE SAME AS FIG. 1



SECT. "B"-"B"
(IN-PROCESS VIEW)

DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG. 1.



LOCKING CLIP OPTION

CLIPS AVAILABLE IN -2
THRU -36 POSITIONS.
(SEE NOTE 4)

[N/A ON LEAD STYLES -01 OR -L1]

MISC MKTG
SSF-1XX-XX-X-D-X-XX-MKT

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

- NOTES:
- 1.) MINIMUM PUSH OUT FORCE: .5 lbs.
 - 2.) COPLANARITY TO BE .006 MAX.
 - 3.) @ REPRESENTS A CRITICAL DIMENSION
 - 4.) ONLY ONE LOCKING CLIP ON -2 POS.
 - 5.) BODY MATERIAL: BLACK PBT
 - 6.) CONTACT: BERYLLIUM COPPER

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: REIDINGER 7-10-91
CHECKED BY: ECKERT

APPROVAL
PAE

SSF-1XX-XX-XX-D-XX
SHEET 1 OF 1