





PART NO.	ENG. NO.	INTERLEAF PAPER OPTION
02-09-1104	1189-A(P901)L	
02-09-1102	1189-A(P901)	
02-09-5111	1189-A(P591)L	
02-09-5102	1189-A(P591)	
02-09-5106	1189-A(P550)L	
02-09-5100	1189-A(P550)	
02-09-6102	1189-A(P901)-I	YES



SECT. "A-A"



SECT. "B-B"



LEGEND

1189-A(****)*-*

INTERLEAF PAPER OPTION

FORM
BLANK=CHAIN
L=LOOSE

BLANK: INTERLEAF PAPER ON FIRST
FEW WRAPS ONLY.
I: INTERLEAF PAPER THROUGH
OUT REEL.


P=PREPLATE
BLANK=POSTPLATE

FINISH CODE

NOTES:


- MATERIAL: CARTRIDGE BRASS, ALLOY #C26000, .010/(0.25) THICK
- FINISH CODES:
 - 901 HOT TIN DIP .000020/(0.00051) MIN.
 - 591 SELECT GOLD PLATE .000050/(0.00127) MIN. IN CONTACT AREA, OVER .000050/(0.00127) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH OVERALL.
 - 550 SELECT GOLD PLATE .000015/(0.00038) MIN. IN CONTACT AREA, OVER .000030/(0.00076) MIN. NICKEL OVERALL WITH .000010/(0.00025) MAX. GOLD FLASH OVERALL.
- *THE PRIMARY SHIPPING CARTON WILL BE LABELED, "COMPLIANT TO RoHS DIRECTIVE 2002/95/EC AND ELV ANNEX OF DIRECTIVE 2000/53/EC", AND CARTONS WITHOUT THIS LABEL MAY CONTAIN PRODUCT WITH TIN-LEAD.

- THIS PART CONFORMS TO PROD. SPEC. 02-09.
- PACKAGING INFORMATION: NOT AVAILABLE
- TERMINAL FOR USE WITH .093/(2.36) SERIES HOUSINGS AND WILL ACCEPT 14 THRU 20 AWG WIRE.
- INSERTION FORCE: 3.5 LBS. MAX. WHEN TERMINAL IS INSERTED INTO AN .093 SERIES HOUSING.
- RETENTION: 20 LBS. MIN. FROM HOUSING.



SECT. "C-C"

CHAIN FORM
FULL SCALE



ADD P/N 02-09-6102 EC NO: UCP2012-2714 DRWN:ALHAG CHKD:JBELL APPR:FSMITH 2012/02/20 2012/02/22 2012/04/25	REV C2	DESCRIPTION	QUALITY SYMBOLS ▽=0 ◊=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 6:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION
					mm	INCH	DRAWN BY GEP	DATE 1987/10/26	TITLE CRIMP TERMINAL, FEMALE, .093/(2.36) DIA. 14-20 AWG		
				4 PLACES	± ---	± ---	CHECKED BY RW	DATE 1987/10/26			
				3 PLACES	± ---	± .010	APPROVED BY RAS	DATE 1987/10/26			
				2 PLACES	± 0.25	± .014	MATERIAL NO. SEE CHART	DOCUMENT NO. SD-1189-*			
				1 PLACE	± 0.35	± ---					
				ANGULAR ± 1/2°							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 1						