



Cable Assemblies > Copper Cable Assemblies > Power Cable Assemblies



Power Cable Assembly Configuration: **Double-Ended**

Wire Size: **.08 mm²**

Power Cable Assembly Overall Outside Cable Diameter: **.93 mm [.036 in]**

Power Cable Assembly Shielded: **No**

Cable Assembly Length: **.11 m [.36 ft]**

Features

Product Type Features

Product Type	Cable Assembly
Product Designation	Patch Cord
Cable Assembly Category	Industry Standard
Power Cable Assembly Shielded	No
Power Cable Assembly Type	Micro-Match Lead
Power Cable Assembly Connector Type (End A)	Power Connector
Power Cable Assembly Connector Type (End B)	Power Connector

Configuration Features

Keyed	Yes
Number of Positions	20
Number of Power Positions	0
Power Cable Assembly Configuration	Double-Ended

Body Features

Equalized	No
Power Cable Assembly Color	None

Housing Features

Power Cable Assembly Housing Material	Nylon - GF
Power Cable Assembly Housing Color	Red

Dimensions

--	--



Wire Size	28 AWG
Power Cable Assembly Overall Outside Cable Diameter	.93 mm[.036 in]

Industry Standards

IEEE 1394	No
-----------	----

Other

CLOUDSPLITTER	No
Cable Assembly Length	.11 m[.36 ft]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUN 2020 (209) Candidate List Declared Against: JUL 2019 (201) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1-161347-2_O_c-1-161347-2-o.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-161347-2_O_c-1-161347-2-o.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-161347-2_O_c-1-161347-2-o.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.