



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	16		1	PPR 08-0502	23OCT2008	JS	JS

1. MAXIMUM CONNECTOR INSERTION LOSS: 1.5 dB PRO BEAM JR. END (1550nm)
0.5 dB ST END (1550nm)
2. MINIMUM CONNECTOR RETURN LOSS: 34 dB PRO BEAM JR. END (1550nm)
55 dB ST END (1550nm)
3. PANEL THICKNESS: 6mm MAX.
4. THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
5. CONNECTOR CAN BE INSTALLED AS A FRONT-PANEL-MOUNT OR REAR-PANEL-MOUNT. POSITION 30x2 O-RING IN APPROPRIATE SIDE OF FLANGE.
6. SEE TRACE LABEL DETAIL.



VIEW A-A

3 RECOMMENDED PANEL CUT-OUT

PRO BEAM JR POSITION	ST LABEL
A1	A1
B1	B1
A2	A2
B2	B2

TE BAR CODE {  } TE TRACE NO.
MADE IN XXXX 2064675-X } TE PART NO.

TRACE LABEL DETAIL 6

50.00±0.33	2064675-1
L	PART NUMBER

DESIGN APPROVED THIS PRINT IS
PRELIMINARY
TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. SHIPE	23OCT2008	Tyco Electronics Corporation Harrisburg, Pa 17105-3608		
DIMENSIONS: FEET		CHK J. SHIPE	23OCT2008	CABLE ASSEMBLY, FIBER OPTIC, SINGLEMODE PRO BEAM JR. SQUARE FLANGE BULKHEAD (NIAIBrz) TO (4) ST, 4x1550nm		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. KADAR-KALLEN	23OCT2008			
MATERIAL		PRODUCT SPEC		SIZE	CAGE CODE	DRAWING NO.
		APPLICATION SPEC		SCALE	NTS	SHEET 1 OF 1
		WEIGHT		REV 1		
		CUSTOMER DRAWING				