


## RF & MICROWAVE TRANSISTORS GENERAL PURPOSE AMPLIFIER APPLICATIONS

- REFRACTORY/GOLD METALLIZATION
- EMITTER SITE BALLASTED
- VSWR CAPABILITY  $\infty:1$  @ RATED CONDITIONS
- HERMETIC STRIPAC<sup>®</sup> PACKAGE
- $P_{OUT} = 1.0$  W MIN. WITH 7.0 dB GAIN @ 3.0 GHz



**.250 2LFL (S010)**  
hermetically sealed


**ORDER CODE**  
MSC83301

**BRANDING**  
83301

### DESCRIPTION

The MSC83301 is a common base hermetically sealed silicon NPN microwave power transistor utilizing an overlay, emitter site ballasted geometry with a refractory gold metallization system. This device is capable of withstanding an infinite load VSWR at any phase angle under rated conditions. The MSC83301 is designed for Class C amplifier/oscillator applications in the 1.0 - 3.0 GHz frequency range.

### PIN CONNECTION



1. Collector      3. Emitter  
2. Base          4. Base

### ABSOLUTE MAXIMUM RATINGS ( $T_{case} = 25^{\circ}C$ )

Symbol	Parameter	Value	Unit
$P_{DISS}$	Power Dissipation* ( $T_C \leq 50^{\circ}C$ )	6.0	W
$I_C$	Device Current*	200	mA
$V_{CC}$	Collector-Supply Voltage*	30	V
$T_J$	Junction Temperature	200	$^{\circ}C$
$T_{STG}$	Storage Temperature	- 65 to +200	$^{\circ}C$

### THERMAL DATA

$R_{TH(j-c)}$	Junction-Case Thermal Resistance*	25	$^{\circ}C/W$
---------------	-----------------------------------	----	---------------

\*Applies only to rated RF amplifier operation




**ELECTRICAL SPECIFICATIONS** ( $T_{\text{case}} = 25^{\circ}\text{C}$ )

**STATIC**



Symbol	Test Conditions		Value			Unit
			Min.	Typ.	Max.	
$BV_{\text{CBO}}$	$I_{\text{C}} = 1 \text{ mA}$	$I_{\text{E}} = 0 \text{ mA}$	45	—	—	V
$BV_{\text{EBO}}$	$I_{\text{E}} = 1 \text{ mA}$	$I_{\text{C}} = 0 \text{ mA}$	3.5	—	—	V
$BV_{\text{CER}}$	$I_{\text{C}} = 5 \text{ mA}$	$R_{\text{BE}} = 10 \Omega$	45	—	—	V
$I_{\text{CBO}}$	$V_{\text{CB}} = 28 \text{ V}$		—	—	0.5	mA
$h_{\text{FE}}$	$V_{\text{CE}} = 5 \text{ V}$	$I_{\text{C}} = 100 \text{ mA}$	30	—	300	—

**DYNAMIC**

Symbol	Test Conditions			Value			Unit
				Min.	Typ.	Max.	
$P_{\text{OUT}}$	$f = 3.0 \text{ GHz}$	$P_{\text{IN}} = 0.20 \text{ W}$	$V_{\text{CC}} = 28 \text{ V}$	1.0	1.3	—	W
$\eta_{\text{C}}$	$f = 3.0 \text{ GHz}$	$P_{\text{IN}} = 0.20 \text{ W}$	$V_{\text{CC}} = 28 \text{ V}$	33	36	—	%
$P_{\text{G}}$	$f = 3.0 \text{ GHz}$	$P_{\text{IN}} = 0.20 \text{ W}$	$V_{\text{CC}} = 28 \text{ V}$	7.0	8.1	—	dB
$C_{\text{OB}}$	$f = 1 \text{ MHz}$	$V_{\text{CB}} = 28 \text{ V}$		—	—	3.5	pF



**TYPICAL PERFORMANCE**


## IMPEDANCE DATA


TYPICAL INPUT  
IMPEDANCE

FREQ.	$Z_{IN} (\Omega)$	$Z_{CL} (\Omega)$
1.0 GHz	$9.0 + j 9.0$	$21.0 + j 48.0$
1.7 GHz	$9.5 + j 23.0$	$12.0 + j 32.0$
2.0 GHz	$18.0 + j 34.5$	$7.5 + j 22.0$
2.3 GHz	$28.0 + j 41.0$	$5.0 + j 13.0$
2.7 GHz	$49.0 + j 39.0$	$4.0 + j 7.0$
3.0 GHz	$65.0 + j 22.0$	$3.8 + j 3.0$

$P_{OUT}$  = Saturated  
 $V_{CC} = 28 \text{ V}$   
 Normalized to 50 ohms


TYPICAL COLLECTOR  
LOAD IMPEDANCE

## TEST CIRCUIT



## PACKAGE MECHANICAL DATA

Ref.: Dwg. No. 12-0216 rev. A



SGS-THOMSON MICROELECTRONICS			CONT'D		
	MINIMUM Inches/mm	MAXIMUM Inches/mm		MINIMUM Inches/mm	MAXIMUM Inches/mm
A	.028/0,71	.032/0,81	K	.165/4,19	.185/4,70
B	.740/18,80		L	.003/0,08	.007/0,18
C	.245/6,22	.255/6,48	M	.058/1,47	.068/1,73
D	.128/3,25	.132/3,35	N	.119/3,02	.135/3,43
E	.125/3,18		P	.149/3,78	.187/4,75
F	.110/2,79	.117/2,97			
G	.117/2,97				
H	.560/14,22	.570/14,48			
I	.795/20,19	.805/20,45			
J	.225/5,72	.235/5,97			

Information furnished is believed to be accurate and reliable. However, SGS-THOMSON Microelectronics assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of SGS-THOMSON Microelectronics. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied. SGS-THOMSON Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of SGS-THOMSON Microelectronics.

©1994 SGS-THOMSON Microelectronics - All Rights Reserved

SGS-THOMSON Microelectronics GROUP OF COMPANIES

Australia - Brazil - France - Germany - Hong Kong - Italy - Japan - Korea - Malaysia - Malta - Morocco - The Netherlands - Singapore - Spain - Sweden - Switzerland - Taiwan - Thailand - United Kingdom - U.S.A.