



PCB Layout
(Top View)



Dimension			
Pos.	A	B	C
06	15.24	12.94	5.08
08	17.78	15.48	7.62
10	20.32	18.02	10.16
12	22.86	20.56	12.70
14	25.40	23.10	15.24
16	27.94	25.64	17.78
20	33.02	30.72	22.86
24	38.10	35.80	27.94
26	40.64	38.34	30.48
30	45.72	43.42	35.56
34	50.80	48.50	40.64
40	58.42	56.12	48.26
44	63.50	61.20	53.34
50	71.12	68.82	60.96
60	83.82	82.51	73.66
64	88.90	86.60	78.74

Material and Finish	Electrical Characteristics	Mechanical Characteristics
1. Housing: Thermoplastic (UL94V-0). 2. Terminal: Sq. 0.64mm Copper Alloy, Gold Plating	1. Current Rating: 3.0 Amp. Max.. 2. Dielectric Withstand Voltage: 1000V AC RMS for 60Seconds. 3. Insulation Resistance: 1000M Ohms Min. at 1000V DC.	1. Operating Temperature: -55°C ~ +105°C 2. Insulator Color , Black Blue ,White

玄茂科技股份有限公司
HSUAN MAO TECHNOLOGY CO., LTD.

制表日:2005/10/05

DRAWING.

kevin

APPROVED

UNIT

MM

APPD.

CKD.

SCALE

TOLERANCE

PART NAME

2.54mm BOX HEADER 180° GOLD
FLASH PLATING LOW-LEAD

PART NO.

C3510-XXSPGX00R

REV.

A