
SECTION
B-B



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire.
Propriete de c FCI. Droits de reproduction FCI.

PRODUCT NO.	PCB THICKNESS	DIMENSION 'A'	DIMENSION 'B'	DIMENSION 'C'	COLOR
10035104-001LF	1.57±0.10	2.54±0.20	2.75±0.20	3.20±0.10	BLACK
10035104-002LF	3.18±0.10	4.06±0.20	4.35±0.20	4.80±0.10	BLACK
10035104-003LF	1.57±0.10	2.54±0.20	2.75±0.20	1.55±0.10	BLACK
10035104-004LF	3.18±0.10	4.06±0.20	4.35±0.20	1.55±0.10	BLACK
10035104-101LF	1.57±0.10	2.54±0.20	2.75±0.20	3.20±0.10	NATURAL



NOTES

1. MATERIAL:
HOUSING: HIGH TEMPERATURE PLASTIC, UL94V-0
CONTACT: COPPER ALLOY
HOLD DOWN: COPPER ALLOY
2. FINISH:
CONTACT: 1.27µm MIN NICKEL UNDERPLATE OVERALL,
2.54µm MIN TIN (LEAD-FREE) ON SOLDER TAIL,
0.76µm MIN GOLD IN CONTACT AREA
3. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
4. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN
5. CONTACT WIRE: 207 MIN FOR SIGNAL AND 252 MIN FOR GROUND

RECOMMENDED PCB LAYOUT
(ALL TOLERANCES ARE ±0.05)

SCALE 3:1

title	dwg	Rev.
4 LANE R/A TH HEADER	10035104	B
catalog no	CUSTOMER	sheet 2 of 2