


Electrical Specs.

Ind. $100\mu\text{H} \pm 10\%$ @ 2.5MHz.
 Q 90 to 100 @ 2.5MHz.
 SRF 12.0 MHz. Min.
 DCR 1.60Ω Max.



Notes:

- Laser mark inductance value.
- Maximum Operating Temperature 105°C
- RoHS Compliant

NEXT ASSEM	USED ON	LTR.	REVISION		BY	DATE
Part #:		17S103K-2LF				
DRAWN BY	KB	APPROVED BY	KB	ENG	QA	MFG

Unless otherwise specified
dimensions are in inches.
in. (mm)

This drawing or
specification is the
property of Gowanda
Electronics. Copies shall
not be reproduced or
copied or used as the
basis for the manufacture
or sale of apparatus
without permission.

