

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G2	REVISED PER ECO-13-005696	24JUL13	KH	MM

D

C

B

A




D

C

B

A


583259



LOOSE PIECE

1. WIRE SIZE: #24-#20 AWG.
INS. RANGE : .050-.090 DIA
- 2 MATTE TIN PLATE IN CRIMP AREA.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

	NICKEL PLATE ALL OVER, TIP PLATE .000015 THICK GOLD.REELING L-R FEED FOR MINI-APPLICATOR.	5-583261-3	5-583259-4
	NICKEL PLATE ALL OVER, TIP PLATE .000015 THICK GOLD.REELING L-R FEED FOR MINI-APPLICATOR.	5-583261-2	5-583259-3
	TIN REELING L-R FEED FOR MINI APPLICATOR.	5-583261-1	5-583259-2
OBSOLETE	TIN REELING L-R FEED FOR STRIPPER CRIMPER.	583261-2	583259-5
OBSOLETE	NICKEL PLATE ALL OVER, TIP PLATE .000015 THICK GOLD.REELING L-R FEED FOR MINI-APPLICATOR.	583261-3	583259-4
	NICKEL PLATE ALL OVER, TIP PLATE .000015 THICK GOLD.REELING L-R FEED FOR MINI-APPLICATOR.	583261-2	583259-3
	TIN REELING L-R FEED FOR MINI APPLICATOR.	583261-1	583259-2
FINISH		LOOSE PIECE PART NO.	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN —	—	 TE Connectivity							
		CHK —	—								
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME							
		APVD —	—								
		PRODUCT SPEC —		MODIFIED FORK CONTACT							
		APPLICATION SPEC —									
		—									
		—									
		—									
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
PHOS. BRONZE		SEE TABLE		A2	00779	C=583259	—				
CUSTOMER DRAWING						SCALE	4:1	SHEET	1 of 1	REV	G2