


DRAWING NUMBER:	15-512-X-XX
PRODUCT GROUP:	TERMINALS
SUB-GROUP:	MILITARY NON-INSULATED TERMINALS
DESCRIPTION:	NON-INSULATED FEED THRU (DOUBLE TURRET/DOUBLE TURRET) TERMINAL



BOARD / PANEL MOUNTING METHOD	MOUNTING HOLE SIZE	DRILL SIZE	FEED THRU COMBINATION
SWAGE MOUNT	0.129" ± 0.001	#30	DOUBLE TURRET/DOUBLE TURRET

PART NO. STRUCTURE:

15-512	-	X	-	XX
PART SERIES		DIMENSION		FINISH

MATERIAL OPTIONS:

15-512-X-XX

COMPONENT	MATERIAL	MATERIAL AND SPECIFICATION
TERMINAL	BRASS	BRASS PER ASTM B16, ALLOY C36000, 1/2 HARD

DIMENSION OPTIONS:

15-512-X-XX

DIMENSION	K	OVERALL LENGTH	SHANK LENGTH (L)	BOARD/PANEL THICKNESS
2	N/A	0.476"	0.105"	1/16"
3	N/A	0.506"	0.135"	3/32"
4	N/A	0.536"	0.165"	1/8"

FINISH - PLATING OPTIONS:

15-512-X-XX

FINISH CODE	COMPONENT	FINISH	FINISH AND SPECIFICATION
05	TERMINAL	ELECTRO-SOLDER	0.000300"MIN. ELECTRO-SOLDER PER SAE-AMS-P-81728 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418
088	TERMINAL	BRIGHT TIN-LEAD	0.000300"MIN. BRIGHT TIN-LEAD (Sn93%-Pb7%) PER ASTM B545 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418
095	TERMINAL	HOT SOLDER DIP	0.000100"MIN. HOT SOLDER DIP USING Sn60 PER IPC-J-STD-006 OVER 0.000100"MIN. COPPER PER SAE-AMS-2418

TOLERANCES:*

DECIMAL	FRACTIONAL	ANGULAR	DRAWING ORIGATION DATE	LAST MODIFICATION DATE
± 0.005	N/A	± 3°	11/4/2002	3/1/2017

*All dimensions are in inches.

RoHS COMPLIANCE:

15-512-2-XX

PART NUMBER	RoHS COMPLIANT
15-512-2-05	NO
15-512-2-088	NO
15-512-2-095	NO

15-512-3-XX

PART NUMBER	RoHS COMPLIANT
15-512-3-05	NO
15-512-3-088	NO
15-512-3-095	NO

15-512-4-XX

PART NUMBER	RoHS COMPLIANT
15-512-4-05	NO
15-512-4-088	NO
15-512-4-095	NO

MILITARY REFERENCE SPECIFICATIONS:

15-512-2-XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER	COMMERCIAL ITEM DESCRIPTION (CID) SPECIFICATION	CID PART NUMBER
15-512-2-05	MIL-T-55155/15	M55155/15XH04	A-A-59126/15	AA59126/15XH04
15-512-2-088	MIL-T-55155/15	M55155/15XJ04	A-A-59126/15	AA59126/15XJ04
15-512-2-095	MIL-T-55155/15	M55155/15XI04	A-A-59126/15	AA59126/15XI04

15-512-3-XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER	COMMERCIAL ITEM DESCRIPTION (CID) SPECIFICATION	CID PART NUMBER
15-512-3-05	MIL-T-55155/15	M55155/15XH05	A-A-59126/15	AA59126/15XH05
15-512-3-088	MIL-T-55155/15	M55155/15XJ05	A-A-59126/15	AA59126/15XJ05
15-512-3-095	MIL-T-55155/15	M55155/15XI05	A-A-59126/15	AA59126/15XI05

Continued on next page...

MILITARY REFERENCE SPECIFICATIONS CONTINUED:

15-512-4-XX

PART NUMBER	MIL SPECIFICATION	MIL PART NUMBER	COMMERCIAL ITEM DESCRIPTION (CID) SPECIFICATION	CID PART NUMBER
15-512-4-05	MIL-T-55155/15	M55155/15XH06	A-A-59126/15	AA59126/15XH06
15-512-4-088	MIL-T-55155/15	M55155/15XJ06	A-A-59126/15	AA59126/15XJ06
15-512-4-095	MIL-T-55155/15	M55155/15XI06	A-A-59126/15	AA59126/15XI06

TOOLING:

INSTALLATION TOOL: ARBOR PRESS	INSTALLATION TOOL: ANVIL (ARBOR PRESS OPERATED)	INSTALLATION TOOL: PRESS-FIT / ROLL SWAGE / RIVET PUNCH (ARBOR PRESS OPERATED)	INSTALLATION TOOL: FLARE SWAGE PUNCH (ARBOR PRESS OPERATED)
TM1	TA156-96-35	TP125-T62	N/A

NOTES:

DATASHEET NOTES

N/A

INSTRUCTION NOTES

SEE GENERAL SWAGING INSTALLATION INSTRUCTION ON CONCORD ELECTRONICS' WEBSITE WWW.CONCORD-ELECTRONICS.COM