

DO NOT  
SCALE FROM  
THIS PRINT

| TABLE 1                                     |              |              |                   |       |
|---------------------------------------------|--------------|--------------|-------------------|-------|
| LEAD STYLE                                  | TERMINAL     | "B"          | TUBE (SEE NOTE 9) | PLUG  |
| -01                                         | T-1M6-13-X-2 | .230 [5.84]  | PT-1-24-01-46     | TP-24 |
| -01 (W / PAD OPTION)                        | T-1M6-13-X-2 | .230 [5.84]  | PT-1-24-05-29     | TP-03 |
| -02                                         | T-1M6-30-X-2 | .100 [2.54]  | PT-1-24-02-29     | TP-24 |
| -02 (W / PAD OPTION)                        | T-1M6-30-X-2 | .100 [2.54]  | PT-1-24-05-29     | TP-03 |
| -03 (W / PAD OPTION)                        | T-1M6-04-X-2 | .125 [3.18]  | PT-1-24-04-15     | TP-09 |
| -03 (NO OPTIONS)                            | T-1M6-04-X-2 | .125 [3.18]  | PT-1-24-02-29     | TP-24 |
| -21                                         | N/A          | .230 [5.84]  | N/A               | N/A   |
| -51                                         | T-1M6-13-X-2 | .190 [4.83]  | PT-1-24-02-29     | TP-24 |
| -52                                         | T-1M6-13-X-2 | .205 [5.21]  | PT-1-24-10-29     | TP-24 |
| -52 (W / PAD OPTION)                        | T-1M6-13-X-2 | .205 [5.21]  | PT-1-24-05-29     | TP-03 |
| -53                                         | T-1M6-05-X-2 | .285 [7.24]  | PT-1-24-02-29     | TP-24 |
| -54 (6-50 POSITION)                         | T-1M6-15-X-2 | .335 [8.51]  | PT-1-24-13-29     | TP-24 |
| -54 (5 POSITION)                            | T-1M6-15-X-2 | .335 [8.51]  | PT-1-24-10-29     | TP-24 |
| -55                                         | T-1M6-16-X-2 | .390 [9.91]  | PT-1-24-10-29     | TP-24 |
| -56                                         | T-1M6-16-X-2 | .405 [10.29] | PT-1-24-10-29     | TP-24 |
| -57                                         | T-1M6-16-X-2 | .430 [10.92] | PT-1-24-03-71     | TP-24 |
| -58                                         | N/A          | .485 [12.32] | N/A               | N/A   |
| -59                                         | N/A          | .535 [13.59] | N/A               | N/A   |
| -60                                         | N/A          | .605 [15.37] | N/A               | N/A   |
| -53, -54, -55, -56, -57-60 (W / PAD OPTION) | N/A          | N/A          | PT-1-24-03-71     | TP-09 |





FIG 1

FTR-1XX-XX-X-S SHOWN

\* REF FOR OAL PIN LENGTH

| TABLE 2         |              |
|-----------------|--------------|
| TERMINAL LENGTH | * "L"        |
| -04             | .505 [12.83] |
| -05             | .705 [17.91] |
| -13             | .625 [15.88] |
| -15             | .755 [19.18] |
| -16             | .825 [20.96] |

F:\DWG\MISC\MKTG\FTR-1XX-XX-X-S-XX-MKT.SLDDRW

## FTR-1XX-XX-XX-S-XX-XX

No OF POSITIONS  
-02 THRU -40LEAD STYLE  
SEE TABLE 1

## PLATING SPECIFICATION

(VALUES GIVEN ARE IN MICRO-INCHES)  
 -G: GOLD, 10 Au / 50 Ni MIN ON CONTACT, 3 Au / 50 Ni MIN ON TAIL  
 -T: MATTE TIN CONTACT AND TAIL  
 -S: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL  
 -F: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL (LEAD STYLE SPEC -01 ONLY)  
 -SM: SELECTIVE, 30 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL  
 -TM: MATTE TIN CONTACT AND TAIL  
 -FM: FLASH SELECTIVE, 3 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL  
 -L: LIGHT SELECTIVE, 10 Au / 50 Ni MIN ON CONTACT, MATTE TIN TAIL

## ROW SPECIFICATION



-S: SINGLE (USE HTMS-50-S)

## OPTION

-P: PICK & PLACE PAD  
(USE PPP-11, SEE FIG 2)  
 -TR: TAPE & REEL  
(4 POS MIN)

## OPTION

-XX: -POLARIZING SPECIFICATION  
(XX INDICATES POS. TO BE OMITTED)



## NOTES:

1. ⬢ REPRESENTS A CRITICAL DIMENSION.
2. MAXIMUM CUT FLASH: .010[.25].
3. MINIMUM PUSHOUT FORCE: 2 LB.
4. MAXIMUM PIN ROTATION IN BODY: 2°.
5. MAXIMUM ALLOWABLE BOW AFTER ASSEMBLY: .005[.13] INCH/INCH
6. SHEAR TAILS TO DIMENSION SHOWN.
7. MAXIMUM BURR ALLOWANCE: .003[.08]
8. MEASURED AT BEND RADIUS.
9. TUBE POSITIONS -05 THRU -50 ONLY FOR THIS LEAD STYLE.

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE:

DECIMALS ANGLES  
 .XX: ±.01 [.3] 2°  
 .XXX: ±.005 [.13]  
 .XXXX: ±.0020 [.051]

MATERIAL: DO NOT SCALE DRAWING

INSULATOR: LCP, UL 94 VO  
 COLOR: BLACK  
 TERMINAL : PHOS BRONZE

SHEET SCALE: 2.5:1

## \* PROPRIETARY NOTE \*

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

**samtec**

520 PARK EAST BLVD, NEW ALBANY, IN 47150  
 PHONE: 812-944-6733 FAX: 812-948-5047  
 e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:  
 HI-TEMP TERMINAL MICRO-STRIP (SINGLE ROW)

DWG. NO. FTR-1XX-XX-XX-S-XX-XX

BY: BRATCHER 7-10-95

SHEET 1 OF 2

"N" = USE MEASURED DIMENSION  
"Q" = { ("N" - .400 [10.16]) / 2 } ±.020 [.51]




FIG 2

-P: PICK AND PLACE PAD  
AVAILABLE ON 08 - 40 POSITIONS ONLY

• PROPRIETARY NOTE •  
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 2.5:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail: info@SAMTEC.com code 55322

DESCRIPTION:  
HI-TEMP TERMINAL MICRO-STRIP (SINGLE ROW)

DWG. NO. FTR-1 XX-XX-XX-S-XX-XX

BY: BRATCHER 7-10-95 SHEET 2 OF 2