



15CTQ...
15CTQ...S
15CTQ... -1

SCHOTTKY RECTIFIER

15 Amp

$I_{F(AV)} = 15\text{Amp}$ $V_R = 35 \text{ to } 45\text{V}$

Major Ratings and Characteristics

Characteristics	15CTQ	Units
$I_{F(AV)}$ Rectangular waveform	15	A
V_{RRM} range	35 to 45	V
I_{FSM} @ tp=5 μ s sine	810	A
V_F @ 7.5 Apk, $T_J = 125^\circ\text{C}$ (per leg)	0.51	V
T_J range	-55 to 150	$^\circ\text{C}$

Description/Features

The 15CTQ center tap Schottky rectifier series has been optimized for very low forward voltage drop, with moderate leakage. The proprietary barrier technology allows for reliable operation up to 150 $^\circ\text{C}$ junction temperature. Typical applications are in switching power supplies, converters, free-wheeling diodes, and reverse battery protection.

- 175 $^\circ\text{C}$ T_J operation
- Center tap TO-220 package
- Low forward voltage drop
- High purity, high temperature epoxy encapsulation for enhanced mechanical strength and moisture resistance
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability

Case Styles		
15CTQ...  TO-220	15CTQ...S  D²PAK	15CTQ... -1  TO-262

Voltage Ratings

Part number	15CTQ035	15CTQ040	15CTQ045
V_R Max. DC Reverse Voltage (V)	35	40	45
V_{RWM} Max. Working Peak Reverse Voltage (V)			

Absolute Maximum Ratings

Parameters		15CTQ	Units	Conditions		
$I_{F(AV)}$	Max. Average Forward Current * See Fig. 5	15	A	50% duty cycle @ $T_C = 123^{\circ}\text{C}$, rectangular wave form		
I_{FSM}	Max. Peak One Cycle Non-Repetitive Surge Current (Per Leg) * See Fig. 7	810	A	5 μs Sine or 3 μs Rect. pulse	Following any rated load condition and with rated V_{RRM} applied	
		145		10ms Sine or 6ms Rect. pulse		
E_{AS}	Non-Repetitive Avalanche Energy (Per Leg)	10	mJ	$T_J = 25^{\circ}\text{C}$, $I_{AS} = 1.20$ Amps, $L = 11.10$ mH		
I_{AR}	Repetitive Avalanche Current (Per Leg)	1.5	A	Current decaying linearly to zero in 1 μsec Frequency limited by T_J max. $V_A = 1.5 \times V_R$ typical		

Electrical Specifications

Parameters		15CTQ	Units	Conditions	
V _{FM}	Max. Forward Voltage Drop (Per Leg) * See Fig. 1 (1)	0.55	V	@ 7.5A	T _J = 25 °C
		0.70	V	@ 15A	
		0.51	V	@ 7.5A	T _J = 125 °C
		0.65	V	@ 15A	
I _{RM}	Max. Reverse Leakage Current (Per Leg) * See Fig. 2 (1)	0.8	mA	T _J = 25 °C	V _R = rated V _R
		32	mA	T _J = 125 °C	
C _T	Max. Junction Capacitance (Per Leg)	400	pF	V _R = 5V _{DC} ; (test signal range 100Khz to 1Mhz) 25°C	
L _S	Typical Series Inductance (Per Leg)	8.0	nH	Measured lead to lead 5mm from package body	
dv/dt	Max. Voltage Rate of Change (Rated V _R)	10,000	V/ μs		

(1) Pulse Width < 300 μs , Duty Cycle < 2%

Thermal-Mechanical Specifications

Parameters	15CTQ	Units	Conditions
T_J Max. Junction Temperature Range	-55 to 150	$^\circ\text{C}$	
T_{stg} Max. Storage Temperature Range	-55 to 150	$^\circ\text{C}$	
R_{thJC} Max. Thermal Resistance Junction to Case (Per Leg)	3.50	$^\circ\text{C/W}$	DC operation * See Fig. 4
R_{thJC} Max. Thermal Resistance Junction to Case (Per Package)	1.75	$^\circ\text{C/W}$	DC operation
R_{thCS} Typical Thermal Resistance, Case to Heatsink	0.50	$^\circ\text{C/W}$	Mounting surface, smooth and greased
wt Approximate Weight	2 (0.07)	g (oz.)	
T Mounting Torque	Min. 6 (5)	Kg-cm (lbf-in)	
	Max. 12 (10)		




Fig. 1 - Max. Forward Voltage Drop Characteristics (PerLeg)




Fig. 2 - Typical Values Of Reverse Current Vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance Vs. Reverse Voltage (Per Leg)




Fig. 4 - Max. Thermal Impedance Z_{thJC} Characteristics (PerLeg)




Fig. 5 - Max. Allowable Case Temperature Vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Max. Non-Repetitive Surge Current (Per Leg)







Fig. 8 - Unclamped Inductive Test Circuit

Outline Table



Outline Table



Ordering Information Table

Device Code					
15	C	T	Q	045	-1
1	2	3	4	5	6
1	Essential Part Number				
2	Common Cathode				
3	T = TO-220				
4	Q = Schottky Q Series				
5	Voltage Rating				
6	S = D ² Pak				
	-1 = TO-262				

035 = 35V

040 = 40V

045 = 45V