





| PERFORMANCE SPECIFICATION                        | MIN  | TYP  | MAX  | UNITS              |
|--------------------------------------------------|------|------|------|--------------------|
| Lower Frequency:                                 |      |      | 1930 | MHz                |
| Upper Frequency:                                 | 1990 |      |      | MHz                |
| Tuning Voltage:                                  | 0.5  |      | 4.5  | VDC                |
| Supply Voltage:                                  | 4.75 | 5.0  | 5.25 | VDC                |
| Output Power:                                    | 0    | +2.5 | +5.0 | dBm                |
| Supply Current:                                  |      | 15   | 20   | mA                 |
| Harmonic Suppression (2 <sup>nd</sup> Harmonic): |      | -15  | -10  | dBc                |
| Pushing:                                         |      | 1.0  | 2.0  | MHz/V              |
| Pulling, all Phases:                             |      | 11.0 | 13.0 | MHz pk-pk          |
| Tuning Sensitivity:                              |      | 25   |      | MHz/V              |
| Phase Noise @ 10kHz offset:                      |      | -105 | -101 | dBc/Hz             |
| Phase Noise @ 100kHz offset:                     |      | -122 | -118 | dBc/Hz             |
| Load Impedance:                                  |      | 50   |      | $\Omega$           |
| Input Capacitance:                               |      |      | 33   | pF                 |
| Operating Temperature Range:                     | -40  |      | +70  | $^{\circ}\text{C}$ |
| Storage Temperature Range:                       | -45  |      | +90  | $^{\circ}\text{C}$ |

### Phase Noise (1 Hz BW, Typical)




### Tuning Curve (Typical)





**TAPE AND REEL**



**Product Control:**

|                      |                    |               |             |
|----------------------|--------------------|---------------|-------------|
| Crystek Part Number: | CVCO55BE-1930-1990 | Release Date: | 12-March-08 |
| Revision Level:      | E                  | Responsible:  | C. Vales    |

Specification is subject to change without notice

