

## Flush-type connector - SACC-DSI-M12FS-12CON-M16/0,5 - 1419713

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sensor/actuator flush-type socket, 12-pos., M12 SPEEDCON, rear/screw mounting with M16 thread, with 0.5 m halogen-free TPE litz wire, 12 x 0.14 mm<sup>2</sup>



### Key commercial data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 1      |
| Weight per Piece (excluding packing) | 40.0 GRM |
| Custom tariff number                 | 85444290 |
| Country of origin                    | Germany  |

### Technical data

#### Dimensions

|                 |       |
|-----------------|-------|
| Length of cable | 0.5 m |
|-----------------|-------|

#### Ambient conditions

|                                 |                                  |
|---------------------------------|----------------------------------|
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |
| Degree of protection            | IP67                             |

#### General

|                        |                               |
|------------------------|-------------------------------|
| Rated current at 40°C  | 1.5 A                         |
| Rated voltage          | 30 V                          |
| Number of positions    | 12                            |
| Contact resistance     | ≤ 3 mΩ                        |
| Insulation resistance  | ≥ 100 MΩ                      |
| Coding                 | A - standard                  |
| Standards/regulations  | M12 connector IEC 61076-2-101 |
| Status display         | No                            |
| Surge voltage category | II                            |

# Flush-type connector - SACC-DSI-M12FS-12CON-M16/0,5 - 1419713

## Technical data

### General

|                   |                                       |
|-------------------|---------------------------------------|
| Pollution degree  | 3                                     |
| Connection method | Individual wires                      |
| Mounting type     | Rear mounting M16 x 1.5 With flat nut |

### Material

|                                         |                              |
|-----------------------------------------|------------------------------|
| Inflammability class according to UL 94 | V0                           |
| Contact material                        | CuZn                         |
| Contact surface material                | Au                           |
| Contact carrier material                | PA 66                        |
| Material, knurls                        | Zinc die-cast, nickel-plated |
| Sealing material                        | NBR                          |

### Cable

|                                 |                                              |
|---------------------------------|----------------------------------------------|
| Cable type                      | TPE litz wire                                |
| Conductor cross section         | 0.14 mm <sup>2</sup>                         |
| AWG signal line                 | 26                                           |
| Wire colors                     | Color-coded DIN 47100                        |
| Material conductor insulation   | TPE                                          |
| Conductor material              | Tin-plated Cu litz wires                     |
| Ambient temperature (operation) | -25 °C ... 85 °C (cable, fixed installation) |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140815 |
| eCl@ss 4.1 | 27140815 |
| eCl@ss 5.0 | 27143423 |
| eCl@ss 5.1 | 27143423 |
| eCl@ss 6.0 | 27279220 |
| eCl@ss 7.0 | 27440103 |
| eCl@ss 8.0 | 27440103 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001297 |
| ETIM 3.0 | EC002061 |
| ETIM 4.0 | EC002061 |
| ETIM 5.0 | EC002061 |

## Flush-type connector - SACC-DSI-M12FS-12CON-M16/0,5 - 1419713

### Classifications

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 31251501 |
| UNSPSC 7.0901 | 31251501 |
| UNSPSC 11     | 31251501 |
| UNSPSC 12.01  | 31251501 |
| UNSPSC 13.2   | 39121413 |

### Approvals

#### Approvals

#### Approvals

UL Recognized / GOST / GOST

#### Ex Approvals

#### Approvals submitted

### Approval details

|                                                                                                   |       |
|---------------------------------------------------------------------------------------------------|-------|
| UL Recognized  |       |
| mm²/AWG/kcmil                                                                                     | 26-20 |
| Nominal current I <sub>N</sub>                                                                    | 1.5 A |
| Nominal voltage U <sub>N</sub>                                                                    | 30 V  |


|                                                                                          |
|------------------------------------------------------------------------------------------|
| GOST  |
|------------------------------------------------------------------------------------------|

|                                                                                          |
|------------------------------------------------------------------------------------------|
| GOST  |
|------------------------------------------------------------------------------------------|

### Drawings


# Flush-type connector - SACC-DSI-M12FS-12CON-M16/0,5 - 1419713

Dimensioned drawing




Housing cutout for M16 fastening thread, mounting panel with thread

Dimensioned drawing




Housing cutout for M16 fastening thread, mounting panel with feed-through hole (alternatively with surface as protection against rotation)

Schematic diagram




Pin assignment M12, 12-pos., female side view

Dimensioned drawing



Circuit diagram



Contact assignment of the M12 socket