





- 1 PHOSPHOR BRONZE PER ASTM-B-139
- 2 CARBON STEEL
- 3 BRASS PER MIL-C-50
- 4 BRASS PER QQ-B-626
- 5 SILICONE RUBBER PER ZZ-R-765
- 6 POLYMETHYLPENTENE: GENERAL PURPOSE
- 7 ZINC DIE CAST PER QQ-Z-363
- 8 GOLD PLATING PER ASTM-B-488
0.38 μ m [.000015] MIN THICKNESS
- 9 NICKEL PLATING PER QQ-N-290
2.54 μ m [.000100] MIN THICKNESS
- 10 NICKEL PLATING PER QQ-N-290
3.81 μ m [.000150] MIN THICKNESS
- 11 NICKEL PLATING PER QQ-N-290
4.45 μ m [.000175] MIN THICKNESS
- 12. USE INSTRUCTION SHEET 408-6996



RECOMMENDED STRIP LENGTH

		RG-59/U		5.49 [.216]		5414265-3	
		CABLE		A		PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. HAVENER 02NOV2005		tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK J. HAVENER 02NOV2005					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. LIPPERT 02NOV2005		NAME	
		0 PLC ± -		PLUG ASSEMBLY, 50 OHM,			
		1 PLC ± -		TWIST-ON, BNC			
		2 PLC ± 0.51 [.020]		-			
		3 PLC ± -					
		4 PLC ± -					
		ANGLES ± -					
MATERIAL		FINISH		WEIGHT		SIZE	
SEE NOTES		SEE NOTES		-		CAGE CODE	
						DRAWING NO	
						RESTRICTED TO	
				A2		00779	
				CUSTOMER DRAWING		C=5414265	
						SCALE	
						4:1	
						SHEET	
						1 of 1	
						REV	
						A	