




NOTES:

1) MATERIALS:

HOUSING: GLASS FILLED LCP (LIQUID CRYSTAL POLYMER),
UL 94V-0, COLOR: BLACK.
MOLDED STICK: GLASS FILLED LCP (LIQUID CRYSTAL POLYMER),
UL 94V-0, COLOR: BLACK.
MALE TERMINAL: PHOSPHOR BRONZE
OUTER SHELL: DEEP DRAWN STEEL.

2) PLATING :

TERMINAL: .000030/(0.000762) MINIMUM GOLD IN SELECTIVE AREA;
.000100/(0.00254) MINIMUM TIN IN SELECTIVE AREA;
OVER NICKEL UNDERPLATE OVERALL.

OUTER SHELL: .000150/(0.00381) MINIMUM TIN
OVER .000050/(0.00127) MINIMUM NICKEL
OVER COPPER FLASH OVERALL (OPTIONAL).



3) CONFORMS TO PRODUCT SPECIFICATION PS-70928.

4) PARTS TO BE PACKAGED IN TUBES.

5) THREAD GAUGE MAY REQUIRE UP TO 1 IN.-LB. OF TORQUE DURING GAUGING PROCESS.

NOTE FOR LEAD FREE CONVERSION:

THE PRIMARY SHIPPING CARTON WILL BE
LABELED "COMPLIANT TO RoHS DIRECTIVE
2002/95/EC AND ELV ANNEX II OF
DIRECTIVE 2000/53/EC". CARTONS
WITHOUT THIS LABEL MAY CONTAIN
PRODUCT WITH LEAD.



PART NUMBER	ENGINEERING NUMBER	DIM. 'A'
015-92-2250	70929-0001	.092±.012
015-92-2253	70929-0002	.104±.012

DIMENSIONS SHOWN (METRIC) INCH UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		REVISE ONLY ON CAD SYSTEM																					
<table border="1"> <tr> <th></th> <th>INCH</th> <th>METRIC</th> </tr> <tr> <td>3 PLACE</td> <td>± ---</td> <td>---</td> </tr> <tr> <td>2 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>--- ±</td> <td>---</td> </tr> </table>			INCH	METRIC	3 PLACE	± ---	---	2 PLACE	± ---	± ---	1 PLACE	--- ±	---	<table border="1"> <tr> <th>2</th> <th>F1</th> </tr> <tr> <td>1</td> <td>G</td> </tr> </table>		2	F1	1	G				
	INCH	METRIC																					
3 PLACE	± ---	---																					
2 PLACE	± ---	± ---																					
1 PLACE	--- ±	---																					
2	F1																						
1	G																						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		<table border="1"> <tr> <th>MFG.</th> <th>SH.</th> <th>REV.</th> <th>LTR.</th> <th>REVISIONS</th> </tr> <tr> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </table>		MFG.	SH.	REV.	LTR.	REVISIONS															
MFG.	SH.	REV.	LTR.	REVISIONS																			
<table border="1"> <tr> <th>DRWG.</th> <th>BY</th> <th>CHK'D.</th> <th>BY</th> </tr> <tr> <td>MOS</td> <td>CAB</td> <td></td> <td></td> </tr> <tr> <th>APPR'D.</th> <th>BY</th> <th>SCALE</th> <th></th> </tr> <tr> <td>CAB</td> <td></td> <td>4: 1</td> <td></td> </tr> </table>		DRWG.	BY	CHK'D.	BY	MOS	CAB			APPR'D.	BY	SCALE		CAB		4: 1		<table border="1"> <tr> <th>PART NO.</th> <th>DRWG. NO.</th> </tr> <tr> <td>SEE CHART</td> <td>SDA-70929-0001</td> </tr> </table>		PART NO.	DRWG. NO.	SEE CHART	SDA-70929-0001
DRWG.	BY	CHK'D.	BY																				
MOS	CAB																						
APPR'D.	BY	SCALE																					
CAB		4: 1																					
PART NO.	DRWG. NO.																						
SEE CHART	SDA-70929-0001																						
<table border="1"> <tr> <th>FILE NAME</th> <th>DATE</th> </tr> <tr> <td>570929X1</td> <td>12/17/90</td> </tr> </table>		FILE NAME	DATE	570929X1	12/17/90	<table border="1"> <tr> <th>SHEET NO.</th> <th>DATE</th> </tr> <tr> <td>1 OF 2</td> <td>12/17/90</td> </tr> </table>		SHEET NO.	DATE	1 OF 2	12/17/90												
FILE NAME	DATE																						
570929X1	12/17/90																						
SHEET NO.	DATE																						
1 OF 2	12/17/90																						
<table border="1"> <tr> <th>MOLEX INCORPORATED</th> <th>U.S.A.</th> </tr> <tr> <td>60532</td> <td></td> </tr> </table>		MOLEX INCORPORATED	U.S.A.	60532		<table border="1"> <tr> <th>THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.</th> </tr> </table>		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.															
MOLEX INCORPORATED	U.S.A.																						
60532																							
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.																							

