

SKiiP® 3

2-pack-integrated intelligent Power System

Power section

SKiiP 2013GB122-4DL


Data

Power section features

- SKiiP technology inside
- SPT (Soft Punch Trough) IGBTs
- CAL diode technology
- Integrated current sensor
- Integrated temperature sensor
- Integrated heat sink
- IEC 60721-3-3 (humidity) class 3K3/IE32 (SKiiP® 3 System)
- IEC 60068-1 (climate) 40/125/56
- UL recognized File no. E63532

1) with assembly of suitable MKP capacitor per terminal


8) AC connection busbars must be connected by the user; copper busbars available on request



Absolute Maximum Ratings		$T_s = 25^\circ\text{C}$ unless otherwise specified	
Symbol	Conditions	Values	Units
IGBT			
V_{CES}	Operating DC link voltage	1200	V
$V_{CC}^{1)}$		900	V
V_{GES}		± 20	V
I_C	$T_s = 25 (70)^\circ\text{C}$	2000 (1500)	A
Inverse diode			
$I_F = -I_C$	$T_s = 25 (70)^\circ\text{C}$	1760 (1340)	A
I_{FSM}	$T_j = 150^\circ\text{C}$, $t_p = 10\text{ ms}$; sin.	13500	A
I^2t (Diode)	Diode, $T_j = 150^\circ\text{C}$, 10 ms	911	kA^2s
$T_j, (T_{stg})$	rms, AC, 1 min, main terminals to heat sink per AC terminal, rms, $T_s = 70^\circ\text{C}$, $T_{terminal} < 115^\circ\text{C}$	- 40 ... + 150 (125)	$^\circ\text{C}$
V_{isol}		3000	V
$I_{AC-terminal}$		400	A

Characteristics		$T_s = 25^\circ\text{C}$ unless otherwise specified			
Symbol	Conditions	min.	typ.	max.	Units
IGBT					
V_{CEsat}	$I_C = 1200\text{ A}$, $T_j = 25 (125)^\circ\text{C}$; measured at terminal		2,3 (2,5)	2,6	V
V_{CEO}	$T_j = 25 (125)^\circ\text{C}$; at terminal		1,1 (1)	1,3 (1,2)	V
r_{CE}	$T_j = 25 (125)^\circ\text{C}$; at terminal		1 (1,2)	1,1 (1,4)	$\text{m}\Omega$
I_{CES}	$V_{GE} = 0\text{ V}$, $V_{CE} = V_{CES}$, $T_j = 25 (125)^\circ\text{C}$		4,8 (144)		mA
$E_{on} + E_{off}$	$I_C = 1200\text{ A}$, $V_{CC} = 600\text{ V}$ $T_j = 125^\circ\text{C}$, $V_{CC} = 900\text{ V}$		360		mJ
			635		mJ
$R_{CC+EE'}$	terminal chip, $T_j = 25^\circ\text{C}$		0,13		$\text{m}\Omega$
L_{CE}	top, bottom		3		nH
C_{CHC}	per phase, AC-side		6,8		nF
Inverse diode					
$V_F = V_{EC}$	$I_F = 1200\text{ A}$, $T_j = 25 (125)^\circ\text{C}$ measured at terminal		1,95 (1,7)	2,1	V
V_{TO}	$T_j = 25 (125)^\circ\text{C}$		1,1 (0,8)	1,2 (0,9)	V
r_T	$T_j = 25 (125)^\circ\text{C}$		0,7 (0,8)	0,8 (0,9)	$\text{m}\Omega$
E_{rr}	$I_C = 1200\text{ A}$, $V_{CC} = 600\text{ V}$		96		mJ
	$T_j = 125^\circ\text{C}$, $V_{CC} = 900\text{ V}$		122		mJ
Mechanical data					
M_{dc}	DC terminals, SI Units	6		8	Nm
M_{ac}	AC terminals, SI Units	13		15	Nm
w	SKiiP® 3 System w/o heat sink		3,1		kg
w	heat sink		9,7		kg
Thermal characteristics (PX 16 heat sink with fan SKF 16B-230-1); "s" reference to heat sink; "r" reference to built-in temperature sensor					
$R_{th(j-s)I}$	per IGBT			0,015	K/W
$R_{th(j-s)D}$	per diode			0,029	K/W
Z_{th}	R_i (mK/W) (max. values)	$\tau_{th}(s)$			
	1 2 3 4	1	2	3	4
$Z_{th(j-r)I}$	5,6 6 6,4 0	363	0,18	0,04	1
$Z_{th(j-r)D}$	10 8,4 14,8 14,8	50	5	0,25	0,04
$Z_{th(r-a)}$	3,1 17,3 3,7 0,9	230	78	13	0,4

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.



2-pack-integrated intelligent Power System

2-pack integrated gate driver SKiiP 2013GB122-4DL

Data

Gate driver features

- CMOS compatible inputs
- Wide range power supply
- Integrated circuitry to sense phase current, heat sink temperature and DC-bus voltage (option)
- Short circuit protection
- Over current protection
- Over voltage protection (option)
- Power supply protected against under voltage
- Interlock of top/bottom switch
- Isolation by transformers
- Fibre optic interface (option for GB-types only)
- IEC 60068-1 (climate) 40/85/56
- UL recognized file no. 242581


Absolute Maximum Ratings		$T_a = 25^\circ\text{C}$ unless otherwise specified	
Symbol	Conditions	Values	Units
V_{S2}	unstabilized 24 V power supply	30	V
V_i	input signal voltage (high)	$15 + 0,3$	V
dv/dt	secondary to primary side	75	kV/ μs
V_{isolIO}	input / output (AC, rms, 2s)	3000	V
V_{isolPD}	partial discharge extinction voltage, rms, $Q_{PD} \leq 10 \text{ pC}$;	1170	V
V_{isol12}	output 1 / output 2 (AC, rms, 2s)	1500	V
f_{sw}	switching frequency	8	kHz
f_{out}	output frequency for $I_{peak(1)} = I_C$	8	kHz
$T_{op} (T_{stg})$	operating / storage temperature	$- 40 \dots + 85$	$^\circ\text{C}$

Characteristics		$(T_a = 25^\circ\text{C})$			
Symbol	Conditions	min.	typ.	max.	Units
V_{S2}	supply voltage non stabilized	13	24	30	V
I_{S2}	$V_{S2} = 24 \text{ V}$	$324 + 39 \cdot f / \text{kHz} + 0,00011 \cdot (I_{AC} / \text{A})^2$			mA
V_{iT+}	input threshold voltage (High)			12,3	V
V_{iT-}	input threshold voltage (Low)	4,6			V
R_{IN}	input resistance		10		k Ω
C_{IN}	input capacitance		1		nF
$t_{d(on)IO}$	input-output turn-on propagation time		1,3		μs
$t_{d(off)IO}$	input-output turn-off propagation time		1,3		μs
$t_{pERRRESET}$	error memory reset time		9		μs
t_{TD}	top / bottom switch interlock time		3,3		μs
$I_{analogOUT}$	max. 5mA; 8 V corresponds to 15 V supply voltage for external components		2000		A
I_{s1out}	max. load current			50	mA
I_{TRIPSC}	over current trip level ($I_{analog OUT} = 10 \text{ V}$)		2500		A
T_{tp}	over temperature protection	110		120	$^\circ\text{C}$
$U_{DCTRIPO}$	U_{DC} -protection ($U_{analog OUT} = 9 \text{ V}$); (option for GB types)		not implemented		V

For electrical and thermal design support please use SEMISEL.

Access to SEMISEL is via SEMIKRON website <http://www.semikron.com>.

* The specifications of our components may not be considered as an assurance of component characteristics. Components have to be tested for the respective application. Adjustments may be necessary. The use of SEMIKRON products in life support appliances and systems is subject to prior specification and written approval by SEMIKRON. We therefore strongly recommend prior consultation of our personal.



Case S43