


## Base strip - MDSTBV 2,5/ 4-G1-5,08 - 1736755

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



The figure shows a 10-pos. version with 20 contacts

Header, Nominal current: 10 A, Rated voltage (III/2): 320 V, Number of positions: 4, Pitch: 5.08 mm, Color: green, Contact surface: Tin, Assembly: Soldering, In combination with MVSTB or FKCV plug components, both an MVSTBW (or FKCVW) and an MVSTBR plug (or FKCVR) must be used. Combination with TMSTBP plug components is not possible!

### Product Features

- ✓ MDSTBW 2,5/...-G with stand-off
- ✓ Add-on ejectors for high-pos. connectors should be mounted to the left and right
- ✓ G1 types without offset levels, for flush installation on the front of devices



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| GTIN                                 | <br>4 017918 027919 |
| Weight per Piece (excluding packing) | 7.26 GRM                                                                                                |
| Custom tariff number                 | 85366990                                                                                                |
| Country of origin                    | Poland                                                                                                  |

### Technical data

#### Dimensions

|                |          |
|----------------|----------|
| Length         | 22 mm    |
| Pitch          | 5.08 mm  |
| Dimension a    | 15.24 mm |
| Pin dimensions | 1 x 1 mm |
| Hole diameter  | 1.4 mm   |

#### General

|                   |                  |
|-------------------|------------------|
| Range of articles | MDSTBV 2,5/..-G1 |
|-------------------|------------------|

## Base strip - MDSTBV 2,5/ 4-G1-5,08 - 1736755

### Technical data

#### General

|                                         |        |
|-----------------------------------------|--------|
| Insulating material group               | I      |
| Rated surge voltage (III/3)             | 4 kV   |
| Rated surge voltage (III/2)             | 4 kV   |
| Rated surge voltage (II/2)              | 4 kV   |
| Rated voltage (III/3)                   | 250 V  |
| Rated voltage (III/2)                   | 320 V  |
| Rated voltage (II/2)                    | 630 V  |
| Connection in acc. with standard        | EN-VDE |
| Nominal current $I_N$                   | 10 A   |
| Maximum load current                    | 10 A   |
| Insulating material                     | PA     |
| Inflammability class according to UL 94 | V0     |
| Color                                   | green  |
| Number of positions                     | 4      |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002637 |
| ETIM 5.0 | EC002637 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |
| UNSPSC 12.01  | 39121409 |
| UNSPSC 13.2   | 39121409 |

## Base strip - MDSTBV 2,5/ 4-G1-5,08 - 1736755

### Approvals

#### Approvals

#### Approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / IECCEB Scheme / GOST / CCA / cULus Recognized

#### Ex Approvals

#### Approvals submitted

#### Approval details

|                                                                                        |       |       |
|----------------------------------------------------------------------------------------|-------|-------|
| CSA  |       |       |
|                                                                                        | B     | D     |
| Nominal current I <sub>N</sub>                                                         | 10 A  | 10 A  |
| Nominal voltage U <sub>N</sub>                                                         | 300 V | 300 V |

|                                                                                                   |       |       |
|---------------------------------------------------------------------------------------------------|-------|-------|
| UL Recognized  |       |       |
|                                                                                                   | B     | D     |
| Nominal current I <sub>N</sub>                                                                    | 12 A  | 10 A  |
| Nominal voltage U <sub>N</sub>                                                                    | 300 V | 300 V |

|                                                                                                                             |       |
|-----------------------------------------------------------------------------------------------------------------------------|-------|
| VDE Gutachten mit Fertigungsüberwachung  |       |
| Nominal current I <sub>N</sub>                                                                                              | 10 A  |
| Nominal voltage U <sub>N</sub>                                                                                              | 250 V |

## Base strip - MDSTBV 2,5/ 4-G1-5,08 - 1736755

### Approvals

|                                                                                                  |       |       |
|--------------------------------------------------------------------------------------------------|-------|-------|
| cUL Recognized  |       |       |
|                                                                                                  | B     | D     |
| Nominal current I <sub>N</sub>                                                                   | 12 A  | 10 A  |
| Nominal voltage U <sub>N</sub>                                                                   | 300 V | 300 V |

|                                                                                        |
|----------------------------------------------------------------------------------------|
| GOST  |
|----------------------------------------------------------------------------------------|

|                                                                                                   |       |
|---------------------------------------------------------------------------------------------------|-------|
| IECEE CB Scheme  |       |
|                                                                                                   |       |
| Nominal current I <sub>N</sub>                                                                    | 10 A  |
| Nominal voltage U <sub>N</sub>                                                                    | 250 V |

|                                                                                          |
|------------------------------------------------------------------------------------------|
| GOST  |
|------------------------------------------------------------------------------------------|


|                                |       |
|--------------------------------|-------|
| CCA                            |       |
|                                |       |
| Nominal current I <sub>N</sub> | 10 A  |
| Nominal voltage U <sub>N</sub> | 250 V |

|                                                                                                      |  |
|------------------------------------------------------------------------------------------------------|--|
| cULus Recognized  |  |
|------------------------------------------------------------------------------------------------------|--|

### Drawings

## Base strip - MDSTBV 2,5/ 4-G1-5,08 - 1736755

Drilling diagram



Dimensioned drawing

