

6

6



FCIconnect.com

Copyright FCI

PLATING

- 1 = 0.76µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
4 = 2µm TIN MIN FULL PLATED
5 = 0.25µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
8 = 0.38µm GOLD/GXT ON CONTACT AREA, 2µm TIN MIN ON TAIL
G = 0.76µm FULL GXT
S = 0.38µm FULL GXT
- 1.27µm NICKEL MIN UNDERLAYER FOR ALL PLATING VERSIONS

PRODUCT SPECIFICATIONS

PIN	STYLE	MATING	SOLDER	DIM "C"
01		5.72	2.57	1.5
02		5.72	5.11	1.5
07		5.72	5.11	3.9
13		5.72	3.45	1.5
18		5.84	3.05	1.5
22		11.71	3.2	1.5
24		6.75	2.85	1.5
25		8.07	3.05	1.5
26		8.2	12.6	1.5
27		5	3.9	1.5
28		3.1	3.1	1.5
29		9.7	2.90	1.5
30		8.30	4.40	1.5
31		11.70	2.80	1.5
32		8.90	3.05	1.5
33		10.20	3.05	1.5
34		10.00	3.25	1.5
35		5.72	12.73	1.5
36		N/A		
37		N/A		
38		8.51	5.51	1.5
39		9.80	9.30	1.5
40		8.13	2.54	3.90
41		14.20	3.05	1.5
42		9.00	7.20	1.5
43		8.08	2.79	1.5
44		15.70	2.79	1.5

mat'l. code SEE NOTES				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection mm	product family BERGSTIK		
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title		
AG	F12-0095	LMU	12.10.25	angles	linear		UNSHR.HEADER		
AH	B-15093	JCO	13.06.28				RA SR TMT		
AJ	B-15388	LMU	13.07.31			scale 5:1			
AK	B-16178	JCO	13.10.31	dr	D.LE	01.01.24	FCI	dwg no	sheet 2 of 2 size
AL	B-17109	JCO	14.03.06	enr	JM.C	01.01.24		77315	A3
AM	B-18916	LMU	14.09.26	chr	JM.C	01.01.24			
				appd	JF.N	01.01.24		type	CUSTOMER Drawing
sheet index	revision sheet								