

DLRO10HD

10 Amp Digital Low Resistance Ohmmeter



- High or low output power selection for condition diagnosis
- Rechargeable battery or line power supply, continuous operation, even with dead battery
- 10 A for 60 seconds, less time waiting to cool, great for charging inductance
- High input protection to 600 V, inadvertent connection to line or UPS voltage will not blow a fuse
- Heavy duty case: IP 65 lid closed, IP54 operational (battery operation only)
- Rotary switch selects one of five test modes, including auto start on connection, giving ease of use

DESCRIPTION

Augmenting Megger's DLRO10 and 10X range the DLRO10HD combines ultimate simplicity of operation with a rugged IP65 case designed for stable ground and bench operation.

The unit is powered from either its rechargeable battery or line power making it suitable for continuous testing in production line/repetitive use environments.

Rotary switch controls are simple and easy to operate in all weather conditions and with gloved hands. A large, clear, backlit LCD display is easy to read from a distance.

The DLRO10HD provides significantly enhanced compliance and is capable of delivering 10 A into measurements up to 250 mΩ and 1A into measurements up to 2.5 Ω. The duration of each test may be up to 60 seconds.

The DLRO10HD is rated CAT III 300 V. A range of test leads is available to suit the application.

The DLRO10HD provides five test modes each of which is selected through a simple rotary control.

ADDITIONAL FEATURES AND BENEFITS

- Rugged case well suited to transportation with shoulder strap and lead set pouch
- Removable lid facilitates easy test lead connection
- Operational ingress protection is IP 54 (battery power only) ensuring protection from the elements

- 7Ah lead acid battery provides extended operation and can be charged whilst operating from line power
- Rotary mode switch with bidirectional (current reversal with averaging cancels thermal EMFs), unidirectional, automatic, continuous and inductive modes
- Large, clear LCD display with backlight and contrast adjustment
- Auto power off function conserves battery

APPLICATIONS

The DLRO10HD measures low resistance values in applications ranging from railways and aircraft to resistance of components in industry.

Any metallic joint can be measured but users must be aware of measurement limitations depending on application. For example, if a cable manufacturer plans to make resistive measurements on a thin wire, a low test current should be selected to prevent heating the wire thereby changing its resistance.

Measurements on electric motors and generators will be inductive and require the user to understand the inductive mode and charging process before a correct result is achieved.

The DLRO10HD is well suited to measuring thick conductors, bonds and quality of welding because of its 10 A range for resistance values up to 250 mΩ.

Electromagnetic noise induced into the leads can interfere with a reading. A noise symbol alerts the user and prevents a measurement when the instrument detects noise above its threshold.

When dissimilar metals are joined a thermocouple effect is created. Users should select a bidirectional mode to ensure cancellation of this effect. The instrument measures with current flowing in both directions and averages the result.

Normal mode is initiated by pressing the 'Test' button after connecting the test leads to the unit under test. Continuity of all four connections is checked. Current is applied in both forward and reverse direction following which measurement is displayed.

Automatic mode is started as soon as the probes make contact. Forward and reverse current measurements are made and the average value is displayed. This mode is ideal when working with the supplied DH4 handspikes. Each time the probes are removed and reconnected to the load a new test will be performed without the need to press the test button.

TEST MODES

Automatic unidirectional mode applies current in one direction only to speed up the measurement process. However thermal EMF resulting from dissimilar metal bonds can cause lower accuracy. Test starts automatically when probes are connected.

Continuous mode allows repeated measurements to be made on the same sample. Simply connect the test leads and press the test button. The measurement is updated every three seconds until the circuit is broken.

Inductive mode is selected when measuring resistance on, for example, motors and generators. When measuring inductive loads it is necessary to wait for the voltage to stabilise as the inductive element is charged. Test leads are firmly connected to the device under test and the 'Test' button pressed. The instrument will pass the selected current through the sample continuously in one direction only and take repetitive readings that will gradually decrease to the true value as the voltage stabilises. The operator decides when the result is stable and presses the 'Test' button to terminate the test.

ELECTRICAL SPECIFICATIONS

Resistance/Current Ranges

The green resistance ranges on the keypad indicate low output power (<0.25 W) outputs. Red ranges indicate higher 2.5 W (1 A) and 25 W (10 A) power outputs.

Resolution and Accuracy

Test current accuracy $\pm 10\%$

Voltmeter input impedance >200 k Ω

Test Current	Resistance Range	Resolution	Accuracy*	Full Scale Voltage	Max. Power Output
0.1 mA	0 to 2500.0 Ω	100 m Ω	$\pm 0.2\%$ ± 200 m Ω	25 mV	2.5 μ W
0.1 mA	0 to 250.00 Ω	10 m Ω	$\pm 0.2\%$ ± 20 m Ω	25 mV	2.5 μ W
1 mA	0 to 25.000 Ω	1 m Ω	$\pm 0.2\%$ ± 2 m Ω	25 mV	25 μ W
10 mA	0 to 2500.0 m Ω	100 $\mu\Omega$	$\pm 0.2\%$ ± 200 $\mu\Omega$	25mV	250 μ W
100 mA	0 to 250.00 m Ω	10 $\mu\Omega$	$\pm 0.2\%$ ± 20 $\mu\Omega$	25 mV	2.5 mW
1 A	0 to 25.000 m Ω	1 $\mu\Omega$	$\pm 0.2\%$ ± 2 $\mu\Omega$	25 mV	25 mW
10 A	0 to 2500.0 $\mu\Omega$	0.1 $\mu\Omega$	$\pm 0.2\%$ ± 0.2 $\mu\Omega$	25 mV	0.25 W
1 A	0 to 2500.0 m Ω	100 $\mu\Omega$	$\pm 0.2\%$ ± 200 $\mu\Omega$	2.5 V	2.5 W
10 A	0 to 250.00 m Ω	10 $\mu\Omega$	$\pm 0.2\%$ ± 20 $\mu\Omega$	2.5 V	25 W

* The accuracy stated assumes forward and reverse measurements.

Inductive mode or unidirectional mode will introduce an undefined error if an external EMF is present.

GENERAL SPECIFICATIONS

Temperature Coefficient

< 0.01% per $^{\circ}\text{C}$, from 5 $^{\circ}\text{C}$ to 40 $^{\circ}\text{C}$

Maximum Altitude

2000 m (6562 ft) to full safety specifications

Display size/type

Main 5 digit + 2 x 5 digit secondary displays

Battery type

6 V, 7Ah sealed lead acid

Voltage input range

90 - 264 V, 50-60 Hz

Charge time

8 hours

Backlight

LED backlight

Battery life

1000 Auto (3 sec) tests

Auto power down

300s

Mode Selection

Rotary switch

Range selection

Rotary switch

Weight

14.7 lb (6.7 kg)

Case dimensions

12 in. L x 11 in. W x 7 in. H

(315 mm L x 285 mm W x 181 mm H)

Pouch for test leads

Yes (lid mounted)

Test leads

DH4 lead set included

IP rating

IP65 case closed, IP54 battery operation

Safety rating

In accordance with IEC61010-1, CATIII 300 V when used with

DH7 leads

Operating temperature and humidity

+5°C to +45°C (41°F to 113°F) at full specification, -10°C to +50°C (14°F to 122°F) at reduced accuracy of $\pm 0.5\%$, <90% RH

Storage temperature and humidity

-25°C to +60°C, <90%RH

EMC

In accordance with IEC61326-1 (heavy industrial)

Noise rejection

Less than 1% ± 20 digits additional error with 100 mV peak 50/60 Hz on the potential leads. Warning will show if hum or noise exceeds this level.

Maximum lead resistance

100 m Ω total for 10 A operation irrespective of battery condition.

ORDERING INFORMATION

Item (Qty)	Order No.	Item (Qty)	Order No.
DLRO10HD Low Resistance Ohmmeter	1000-348	Straight Duplex Handspikes (2)	
Included accessories		heavy-duty with fixed contacts	
DH4 duplex handspike 1.2m	6111-503	2m/7ft	242002-7
Test lead pouch (lid mounted)	1000-036	5.5m/18ft	242002-18
DLRO10HD user guide CD	2000-869	9m/30ft	242002-30
Optional Accessories at extra cost		Duplex heavy-duty 5 cm (2 in.)	
Calibration Shunt, 10 Ω , current rating 1 mA	249000	C-Clamps (2)	
Calibration Shunt, 1 Ω , current rating 10 mA	249001	2m/7ft	242004-7
Calibration Shunt, 100 m Ω current rating 1 A	249002	5.5m/18ft	242004-18
Calibration Shunt, 10 m Ω current rating 10 A	249003	9m/30ft	242004-30
Certificate of Calibration for Shunts, NIST	YCERT-NIST	Duplex handspikes with	
Replacement tips for DH4, DH5 and DH7 handspikes		replaceable needle points	
Needle point	25940-012	2m/7ft	242003-7
Serrated end	25940-014	Duplex 1.27 cm (.5 in.)	
Optional Test Leads at extra cost		Kelvin clips (2) gold plated	
Duplex Leads		2m/7ft	241005-7
DH5 straight duplex handspikes (2)		silver plated	
One has indicator lights	2.5m/8ft	2m/7ft	242005-7
DH7 Duplex handspikes (2) suitable		Duplex 3.8 cm (1.5 in.)	
for working on 600 V systems	2.5m/8ft	Kelvin clips (2)	
Duplex Handspikes (2) with spring		2m/7ft	242006-7
loaded helical contacts	2m/7ft	5.5m/18ft	242006-18
DH1	2.5m/8ft	9m/30ft	242006-30
	5.5m/18ft	Single Leads	
only 1 lead supplied	DH2	Single handspike (1) for	
	6m/20ft	potential measurement	
	9m/30ft	2m/7ft	242021-7
DH3	9m/30ft	5.5m/18ft	242021-18
	6111-024	9m/30ft	242021-30
		Current clip (1) for	
		current connections	
		2m/7ft	242041-7
		5.5m/18ft	242041-18
		9m/30ft	242041-30

Note: For more details of optional leadsets see separate test lead datasheet DLRO_TL_DS_USen_V04.pdf

MeterCenter

2046 W. Peninsula Circle

Chandler, Az 85248

Telephone: (480) 659-8351 Toll Free: (800) 230-6008

Fax: (480) 659-8361

Email: sales@MeterCenter.com

Registered to ISO 9001:2000 Cert. no. Q 09290

Registered to ISO 14001-1996 Cert. no. EMS 61597

DLRO10HD_DS_USen_V01

www.BiddleMegger.com

Megger is a registered trademark