

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

COPYRIGHT BY - Taipei, Taiwan

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

D

ECR-13-004090

06MAR13'

KL

WK

NOTES (UNLESS OTHERWISE SPECIFIED)

- REFER TO MICROSOFT DOC H02325 FOR CABLE AND ASSEMBLY SPECIFICATIONS
- REFERENCE THE FOLLOWING DOCUMENTS FOR INSPECTION AND ACCEPTANCE CRITERIA
 - MICROSOFT RESTRICTED SUBSTANCES FOR HARDWARE PRODUCTS (H00594)
 - MICROSOFT XBOX PLASTIC WORMANSHOP (D00015)
 - MICROSOFT RESTRICTED SUBSTANCE MANGEMENT SYSTEM (H00642)
- BAG AND TAG WITH THE FOLLOWING INFORMATION:

MICROSOFT
CUSTOMER P/N REV.*
WYYY
OVERMOLD PVC
94V-0
MADE IN ****

— COPYRIGHT NOTATION
— CUST. P/N & REV.
— DATE CODE
— MATERIAL
— UL FLAMABILITY RATING
— COUNTRY ORIGIN


- THE FOLLOWING INFORMATION TO BE MOLDED INTO PART THE LOCATION INDICATED:
 - CAVITY ID
 - SUPPLIER INITIALSALL CHARACTERS SHALL BE STANDING PROUD 0.1 MM MAX. CHARACTER HEIGHT TO BE 1.0 TO 5.0 MM. SIZED TO FIT AVAILABLE SPACE

- VENDOR SHALL SUPPLY A CERTIFICATE OF REGULATORY COMPLIANCE WITH EACH SHIPMENT THAT INCLUDES THE FOLLOWING INFORMATION:
 - NAME OF THE MOLDER
 - MOLDING DATE
 - UL MOLDER'S FILE NUMBER
 - MATERIAL MANUFACTURER'S NAME OR TRADE NAME AND MATERIAL DESIGNATION.
 - FLAMMABILITY RATING
 - NAME OF THE COMPANY BUYING THE PRODUCT
 - PART NUMBER AND REVISION LEVEL
 - PURCHASE ORDER NUMBER
 - SHIPMENT DATE
 - QUALITY OF PARTS SHIPPED
 - MANUFACTURER REPRESENTATIVE'S NAME, SIGNATURE OR FUNCTION TO ATTEST TO THE ACCURACY OF THE INFORMATION.
- INDICATES A CRITICAL DIMENSION. NO CPK REQUIREMENT FOR CABLE LENGTH.
- PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TEC-138-702.
- STAMP UL LABEL ON CARTON.

- THE FOLLOWING INFORMATION TO BE PRINTED ON CABLE AT THE LOCATION INDICATED:
 - PRODUCTION DATE CODE.
 - CURRENT REVISION LEVEL(Microsoft).TO BE PRINTED IN CONTRASTING COLOR, IN YYYY-MM-DD REV.* FORMAT, CHARACTER TO BE 1.6 MM.


- SOLDERING AFTER CRIMPING.

CONN 1



CONN 2

WIRING PATTERN:



TE P/N: 2006644-1

CUSTOMER P/N: X852618-001 REV.G

AR	MR	INNER MOLD PE.	4
AR	MR	MOLD PVC 40P, 94V-0, COLOR: BLACK.	3
AR	MR	SATA CABLE UL2725 SOLID TYPE (30AWG*2C+DRAIN*2+AL/MYLAR)*2F, COLOR: BLUE	2
2	PC	SATA, 7P, FEMALE, CRIMP TYPE, CONTACT: PHOSPHOR BRONZE, 15U" GOLD OVER NICKEL, INSULATION: BLACK.	1
QTY	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± 3°
MATERIAL SEE NOTE	FINISH SEE NOTE

DWN K. LIN 06MAR2013	CHK S. CHIEN 06MAR2013	APVD W. KODAMA 06MAR2013
PRODUCT SPEC	QUALIFICATION TEST REPORT	WEIGHT
CUSTOMER DRAWING		



TE Connectivity

NAME			
CABLE ASSY, ODD SATA			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=2006644	MSFT
SCALE		SHEET	REV
1 OF 1		D	