








LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			AL1	REVISED PER ECR-17-008392	26JUN2017	BW	KR



1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
2. RECOMMENDED PANEL THICKNESS 0.76 – 2.29.
3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
4. OPTIONAL FOR KEYING HOUSING IN PANEL.
5. CIRCUIT NUMBER 1 LOCATION.
6. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
7. FOUR RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION. NO RIBS OR SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION, OPTIONAL.
8. UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE EACH ON SIDE OF HOUSING.
9. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED PANEL CUT OUT




6.35	.250	—	—
4.45	.175	27.43	1.080
2.79	.110	26.43	1.041
2.54	.100	25.91	1.020
2.29	.090	20.70	.815
0.76	.030	20.32	.800
0.38	.015	12.19	.480
0.25	.010	8.13	.320
0.13	.005	6.99	.275
MM	IN	MM	IN





CONVERSION TABLE

9 SUPERSEDED BY 1-480707-0	9 OBSOLETE	BLACK	1-480707-9
		GRAY	1-480707-8
		BLUE	1-480707-6
		GREEN	1-480707-5
		YELLOW	1-480707-4
		ORANGE	1-480707-3
		RED	1-480707-2
		BROWN	1-480707-1
		NATURAL	1-480707-0
		COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: K. WHITAKER 29JUL04 DRW: S. RIDGILL 29JUL04 APVD: S. RIDGILL 29JUL04		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.13 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± 0°30'		NAME: CAP. 9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE: CAGE CODE: DRAWING NO: RESTRICTED TO:	
MATERIAL: NYLON, UL94V-2 FINISH: —		WEIGHT:		A1 00779 C=480707	
CUSTOMER DRAWING				SCALE: 4:1 SHEET 1 of 2 REV: A1	



1. STAMP NUMBERS 3.18 HIGH AT WIRE END OF HOUSING (12 POINT DAVID TYPE);CLARIFICATION MARKS UNDER THE 6 & 9.
2. CHARACTERS TO BE STAMPED ON HOUSING IN A MANNER AS TO BE READ FROM WIRE END ONLY.
3. VIOLET,BLACK,BROWN,AND BLUE COLORED BLOCKS TO BE STAMPED WITH WHITE CHARACTERS. ALL OTHER COLORED BLOCKS TO BE STAMPED WITH BLACK CHARACTERS.



5.08	.200	-	-
4.70	.185	27.43	1.080
3.18	.125	25.91	1.020
0.38	.015	20.70	.815
0.25	.010	20.32	.800
0.13	.005	8.13	.320
MM	IN	MM	IN

CONVERSION TABLE

NATURAL	2-480707-0
COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER	29JUL04	TE Connectivity	
		CHK S. RIDGILL	29JUL04		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD S. RIDGILL	29JUL04	NAME	
		PRODUCT SPEC		CAP, 9 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)	
	0. PLC ± - 1. PLC ± - 2. PLC ± 0.13 3. PLC ± - 4. PLC ± - ANGLES ± 0°30'	APPLICATION SPEC		SIZE	CAGE CODE
		WEIGHT		DRAWING NO	RESTRICTED TO
MATERIAL NYLON, UL94V-2	FINISH -	CUSTOMER DRAWING		A100779	480707
		SCALE	4:1	SHEET	2 OF 2
				REV	AL1