

# VAL-US-120/65/1+1-FM - Surge protection device



2910356

<https://www.phoenixcontact.com/us/products/2910356>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge protective device, UL Listed type 1 and IEC type 2, two channel with remote indicator contact for 120 V AC, 2-wire plus ground.

## Your advantages

- With floating remote indication contact
- UL open terminal listed SPD
- Thermal disconnect device for each individual plug
- Mechanical coding of all slots
- Optical, mechanical status indication for the individual arresters
- Pluggable
- Secure hold of plugs in the event of high lightning current loads and strong vibrations thanks to new latching

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 2910356       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | CL17          |
| Product key                          | CL115U        |
| GTIN                                 | 4055626444963 |
| Weight per piece (including packing) | 302 g         |
| Weight per piece (excluding packing) | 277 g         |
| Customs tariff number                | 85363030      |
| Country of origin                    | DE            |

# VAL-US-120/65/1+1-FM - Surge protection device



2910356

<https://www.phoenixcontact.com/us/products/2910356>

## Technical data

### Product properties

|                                |                                              |
|--------------------------------|----------------------------------------------|
| Product type                   | Surge protection for NEMA power supply units |
| Product family                 | VALVETRAB US                                 |
| IEC test classification        | I / II                                       |
|                                | T1 / T2                                      |
| EN type                        | T1 / T2                                      |
| IEC power supply system        | TN-S                                         |
|                                | TT                                           |
| Type                           | DIN rail module, two-section, divisible      |
| Number of positions            | 2                                            |
| Surge protection fault message | Optical, remote indicator contact            |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Pollution degree     | 2   |

### Electrical properties

|                         |               |
|-------------------------|---------------|
| Nominal frequency $f_N$ | 50 Hz (60 Hz) |
|-------------------------|---------------|

### Indicator/remote signaling

|                    |                                |
|--------------------|--------------------------------|
| Connection name    | Remote fault indicator contact |
| Switching function | Changeover contact             |
| Operating voltage  | 5 V AC ... 250 V AC            |
|                    | 30 V DC                        |
| Operating current  | 5 mA AC ... 1.5 A AC           |
|                    | 1 A DC                         |

### Connection data

|                                  |                                                      |
|----------------------------------|------------------------------------------------------|
| Connection method                | Screw connection                                     |
| Screw thread                     | M5                                                   |
| Tightening torque                | 4.5 Nm (1.5 mm <sup>2</sup> ... 16 mm <sup>2</sup> ) |
|                                  | 4.5 Nm (25 mm <sup>2</sup> ... 35 mm <sup>2</sup> )  |
| Stripping length                 | 16 mm                                                |
| Conductor cross-section flexible | 1.5 mm <sup>2</sup> ... 25 mm <sup>2</sup>           |
| Conductor cross-section rigid    | 1.5 mm <sup>2</sup> ... 35 mm <sup>2</sup>           |
| Conductor cross-section AWG      | 15 ... 2                                             |

### Remote fault indicator contact

|                                  |                                              |
|----------------------------------|----------------------------------------------|
| Connection method                | Screw connection                             |
| Screw thread                     | M2                                           |
| Tightening torque                | 0.25 Nm                                      |
| Stripping length                 | 7 mm                                         |
| Conductor cross-section flexible | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |

# VAL-US-120/65/1+1-FM - Surge protection device




2910356

<https://www.phoenixcontact.com/us/products/2910356>

|                               |                                              |
|-------------------------------|----------------------------------------------|
| Conductor cross-section rigid | 0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> |
| Conductor cross-section AWG   | 28 ... 16                                    |

## Dimensions

|                     |                                                                                    |
|---------------------|------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 35.6 mm                                                                            |
| Height              | 96.8 mm                                                                            |
| Depth               | 77.5 mm (incl. DIN rail 7.5 mm)                                                    |
| Horizontal pitch    | 2 Div.                                                                             |

## Material specifications

|                                        |                  |
|----------------------------------------|------------------|
| Color                                  | black (RAL 9005) |
| Flammability rating according to UL 94 | V-0              |
| CTI value of material                  | 600              |
| Insulating material                    | PA 6.6/PBT       |
| Material group                         | I                |
| Housing material                       | PA 6.6<br>PBT    |

## Mechanical properties

### Mechanical data

|                 |    |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

## Protective circuit

|                                                       |                 |
|-------------------------------------------------------|-----------------|
| Mode of protection                                    | L-N             |
|                                                       | L-PE            |
|                                                       | N-PE            |
| Direction of action                                   | 1L-N & N-GND    |
| Nominal voltage $U_N$                                 | 120 V AC (TN-S) |
|                                                       | 120 V AC (TT)   |
| Nominal frequency $f_N$                               | 50 Hz (60 Hz)   |
| Maximum continuous operating voltage $U_C$ (L-N)      | 175 V AC        |
| Maximum continuous operating voltage $U_C$ (N-PE)     | 264 V AC        |
| Rated load current $I_L$                              | 80 A            |
| Protective conductor current $I_{PE}$                 | $\leq 5 \mu A$  |
| Nominal discharge current $I_n$ (8/20) $\mu s$ (L-N)  | 12.5 kA         |
| Nominal discharge current $I_n$ (8/20) $\mu s$ (L-PE) | 12.5 kA         |
| Nominal discharge current $I_n$ (8/20) $\mu s$ (N-PE) | 50 kA           |
| Maximum discharge current $I_{max}$ (8/20) $\mu s$    | 65 kA           |
| Total discharge current $I_{Total}$ (10/350) $\mu s$  | 25 kA           |

# VAL-US-120/65/1+1-FM - Surge protection device



2910356

<https://www.phoenixcontact.com/us/products/2910356>

|                                                 |                                        |
|-------------------------------------------------|----------------------------------------|
| Follow current interrupt rating $I_{fi}$ (N-PE) | 100 A                                  |
| Short-circuit current rating $I_{SCCR}$         | 25 kA                                  |
| Voltage protection level $U_p$ (L-N)            | $\leq 0.8$ kV                          |
| Voltage protection level $U_p$ (L-PE)           | $\leq 2$ kV                            |
| Voltage protection level $U_p$ (N-PE)           | $\leq 1.7$ kV                          |
| Residual voltage $U_{res}$ (L-N)                | $\leq 0.8$ kV (at $I_n$ )              |
|                                                 | $\leq 0.75$ kV (at 10 kA)              |
|                                                 | $\leq 0.65$ kV (at 5 kA)               |
|                                                 | $\leq 0.6$ kV (at 3 kA)                |
| Residual voltage $U_{res}$ (L-PE)               | $\leq 2$ kV (at $I_n$ )                |
|                                                 | $\leq 1.5$ kV (at 10 kA)               |
|                                                 | $\leq 1.4$ kV (at 5 kA)                |
|                                                 | $\leq 1.3$ kV (at 3 kA)                |
| Residual voltage $U_{res}$ (N-PE)               | $\leq 0.6$ kV (at $I_n$ )              |
|                                                 | $\leq 0.5$ kV (at 10 kA)               |
|                                                 | $\leq 0.5$ kV (at 5 kA)                |
|                                                 | $\leq 0.4$ kV (at 3 kA)                |
| TOV behavior at $U_T$ (L-N)                     | 208 V AC (5 s / withstand mode)        |
|                                                 | 240 V AC (120 min / safe failure mode) |
| TOV behavior at $U_T$ (N-PE)                    | 1200 V AC (200 ms / withstand mode)    |
| Response time $t_A$ (L-N)                       | $\leq 25$ ns                           |
| Response time $t_A$ (L-PE)                      | $\leq 100$ ns                          |
| Response time $t_A$ (N-PE)                      | $\leq 100$ ns                          |
| Max. backup fuse with V-type through wiring     | 80 A (gG)                              |
| Max. backup fuse with branch wiring             | 160 A (gG)                             |

## Environmental and real-life conditions

### Ambient conditions

|                                         |                                                           |
|-----------------------------------------|-----------------------------------------------------------|
| Degree of protection                    | IP20 (only when all terminal points are used)             |
| Ambient temperature (operation)         | -40 °C ... 80 °C                                          |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C                                          |
| Altitude                                | $\leq 2000$ m (amsl)                                      |
| Permissible humidity (operation)        | 5 % ... 95 %                                              |
| Shock (operation)                       | 30g (Half-sine / 11 ms / 3x $\pm X$ , $\pm Y$ , $\pm Z$ ) |
| Vibration (operation)                   | 7.5g (10 ... 500 Hz / 2.5 h / X, Y, Z)                    |

## Approvals

### UL specifications

|                                                 |          |
|-------------------------------------------------|----------|
| Maximum continuous operating voltage MCOV (L-N) | 175 V AC |
| Maximum continuous operating voltage MCOV (L-G) | 175 V AC |
| Maximum continuous operating voltage MCOV (N-G) | 264 V AC |
| Short-circuit current rating (SCCR)             | 200 kA   |
| Voltage protection rating VPR (L-N)             | 700 V    |

# VAL-US-120/65/1+1-FM - Surge protection device



2910356

<https://www.phoenixcontact.com/us/products/2910356>

|                                     |                         |
|-------------------------------------|-------------------------|
| Voltage protection rating VPR (L-G) | 1500 V                  |
| Voltage protection rating VPR (N-G) | 1200 V                  |
| UL type                             | type 1                  |
| Nominal discharge current $I_n$     | 20 kA                   |
| Maximum Surge Current per Phase     | 65 kA (acc. IEC61643-1) |
|                                     | 80 kA (acc. NEMA LS1)   |
| Mode of protection                  | L-N                     |
|                                     | L-G                     |
|                                     | N-G                     |
| Nominal voltage                     | 120 V AC                |
| Power distribution system           | Single phase            |
| Nominal frequency                   | 50/60 Hz                |
| SPD Type                            | 1                       |

## UL indicator/remote signaling

|                      |          |
|----------------------|----------|
| Operating voltage    | 125 V AC |
| AC operating current | 1 A AC   |

## UL connection data

|                             |                         |
|-----------------------------|-------------------------|
| Tightening torque           | 30 lb <sub>F</sub> ·in. |
| Conductor cross-section AWG | 14 ... 2                |

## Standards and regulations

### Air clearances and creepage distances

|                          |                          |
|--------------------------|--------------------------|
| Standards/regulations    | EN 60664-1 / EN 61643-11 |
| Standards/specifications | IEC 61643-11             |
| Note                     | 2011                     |
| Standards/specifications | EN 61643-11              |
| Note                     | 2012                     |

## Mounting

|               |                 |
|---------------|-----------------|
| Mounting type | DIN rail: 35 mm |
|---------------|-----------------|

# VAL-US-120/65/1+1-FM - Surge protection device


2910356

<https://www.phoenixcontact.com/us/products/2910356>




## Drawings

Dimensional drawing



Circuit diagram



# VAL-US-120/65/1+1-FM - Surge protection device



2910356

<https://www.phoenixcontact.com/us/products/2910356>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2910356>



**UL Listed**

Approval ID: FILE E 330181



**cUL Listed**

Approval ID: FILE E 330181

# VAL-US-120/65/1+1-FM - Surge protection device



2910356

<https://www.phoenixcontact.com/us/products/2910356>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27171202 |
| ECLASS-15.0 | 27171202 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000941 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121600 |
|-------------|----------|

# VAL-US-120/65/1+1-FM - Surge protection device



2910356  
<https://www.phoenixcontact.com/us/products/2910356>

## Environmental product compliance

|                                         |                                          |
|-----------------------------------------|------------------------------------------|
| EU RoHS                                 |                                          |
| Fulfills EU RoHS substance requirements | Yes, No exemptions                       |
| China RoHS                              |                                          |
| Environment friendly use period (EFUP)  | EFUP-E                                   |
|                                         | No hazardous substances above the limits |
| EU REACH SVHC                           |                                          |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%               |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)